



Mini-Circuits®



QUICK-CONNECT

Test Cable

CBL6NMQ-SM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male

FEATURES

- Wideband coverage, DC to 18 GHz
- Extra rugged construction with strain relief for longer life
- Stainless steel connectors for long mating-cycle life
- Useful over temperature range, -55°C to +105°C
- Triple shield cable for excellent shielding effectiveness
- Flexible for easy connection & bend radius
- Superior stability of insertion loss, VSWR & phase vs. flexing
- 6 month guarantee*



Generic photo used for illustration purposes only

Model No.	CBL6NMQ-SM+
Case Style	GM1105-6
Connectors	SMA-Male ² to N-Male

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- High volume production test stations
- Research & development labs
- Environmental & temperature test chambers
- Replacement for OEM test port cables
- Field RF testing
- Cellular infrastructure site testing

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency range		DC		18	GHz
Length ¹		6			FT
Insertion Loss	DC - 2.5	—	1.2	1.4	dB
	2.5 - 6	—	2.0	2.35	
	6 - 12	—	3.0	3.55	
	12 - 18	—	3.8	4.55	
Return Loss	DC - 2.5	23	30	—	dB
	2.5 - 6	20	30	—	
	6 - 12	17	27	—	
	12 - 18	17	22	—	

1. Custom sizes available, consult factory.

2. Quick-turn connector, 1½T to mate on one side only (marking: 1T)

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
Shielding Effectiveness	>100 dB
Power Handling at +25°C	891W Max. at 0.4 GHz
	539W Max. at 1 GHz
	363W Max. at 2 GHz
	180W Max. at 6 GHz
	117W Max. at 12 GHz
	88W Max. at 18 GHz

Permanent damage may occur if any of these limits are exceeded.

Product Guarantee*

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.





Mini-Circuits




QUICK-CONNECT

Test Cable


CBL6NMQ-SM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male

CABLE CONSTRUCTION



OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch mm)

A		B	C	D	E	T		wt
Feet	Meters					Feet	Meters	grams
6	1.83	0.42	0.312	0.88	.750	0.18	0.05	173
		10.67	7.92	22.35	19.05			





Mini-Circuits



QUICK-CONNECT

Test Cable


CBL6NMQ-SM+

50Ω 6FT DC to 18 GHz SMA-Male to N-Male


TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		SMA-Male	SMA-Male
50.00	0.16	64.77	47.86
100.00	0.22	49.15	51.38
1000.00	0.72	31.81	31.75
2000.00	1.03	28.95	28.91
2500.00	1.18	36.62	36.19
4000.00	1.54	38.15	35.38
5000.00	1.74	38.97	36.05
6000.00	1.94	40.85	28.69
7000.00	2.09	28.84	32.34
8000.00	2.26	28.21	35.97
9000.00	2.43	24.28	29.74
12000.00	2.88	25.22	26.87
14000.00	3.24	26.88	30.04
15000.00	3.35	28.22	30.07
18000.00	3.67	23.02	28.77

CBL6NMQ-SM+
INSERTION LOSS



CBL6NMQ-SM+
RETURN LOSS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[CBL6NMQ-SM+](#)