



Mini-Circuits

MMIC SURFACE MOUNT


X2 Frequency Multiplier

CY2-44+

50Ω Output 12.4 to 40 GHz

THE BIG DEAL

- Wideband, output 12.4 to 40 GHz
- Low conversion loss, 14 dB typ.
- Good fundamental & harmonic suppression, F1, 26 dBc typ.; F3, 34 dBc typ.; F4, 18 dBc typ.
- Miniature size 3 x 3 x 0.89mm
- Aqueous washable

*Generic photo used for illustration purposes only*

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Synthesizers
- Local Oscillators
- 5G

PRODUCT OVERVIEW

Mini-Circuits' CY2-44+ is an ultra-wideband MMIC frequency doubler, converting input frequencies from 6.2 to 20 GHz into output frequencies from 12.4 to 40 GHz. Its wide output range makes this model suitable for broadband systems as well as a wide variety of narrowband applications. Utilizing GaAs HBT technology, the multiplier comes housed in a tiny 3 x 3 x 0.89mm MCLP package and offers excellent repeatability, low inductance, and good thermal efficiency.

KEY FEATURES

Features	Advantages
Broadband, 12.4 to 40 GHz output	With an output frequency range spanning 12.4 to 40 GHz, this multiplier supports broadband applications such as defense and instrumentation as well as a wide range of narrowband system requirements including 5G.
Low conversion loss, 14 dB typ.	With a low conversion loss, CY2-44+ produces higher output power, reducing the need for post amplification.
Excellent fundamental and harmonic suppression: • F1, 26 dBc • F3, 34 dBc • F4, 18 dBc	Reduces spurious signals and the need for additional filtering.
Wide input power range, +12 to +18 dBm	Wide input power signal range accommodates different input signal levels while still maintaining a low conversion loss.
3 x 3 mm, 12 lead MCLP package	Low inductance, repeatable transitions, and excellent thermal contact to the PCB





Mini-Circuits

MMIC SURFACE MOUNT

X2 Frequency Multiplier

CY2-44+

50Ω Output 12.4 to 40 GHz

ELECTRICAL SPECIFICATIONS¹ AT 25°C

Parameter	Input Frequency (GHz)	Min.	Typ.	Max.	Unit
Multiplier Factor		2			
Frequency Range, Input (F1)		6.2 16	— —	16 20	GHz
Frequency Range, Output (F2)		12.4 32	— —	32 40	GHz
Input Power		12	—	18	dBm
Conversion Loss	6.2 - 16 16 - 20	— —	14 17	20 23	dB
Harmonic Output ²	F1 16 - 20	— —	26 27	— —	dBc
	F3 16 - 16.5	— —	34 36	— —	
	F4 6.2 - 12.4	— —	18 —	— —	

1. At +15 dBm input power measured on Mini-Circuits test board TB-973-CY244C+

2. Harmonics of input frequency below the power of F2. Harmonics are measured to 50 GHz.

MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C
RF Input Power	+21 dBm

Permanent damage may occur if any of these limits are exceeded.

PAD CONNECTIONS

INPUT	5
OUTPUT	11
GROUND	4,6,10,12 & paddle
NO CONNECTIONS	all others

PRODUCT MARKING



Marking may contain other features or characters for internal lot control





MMIC SURFACE MOUNT





X2 Frequency Multiplier

CY2-44+

50Ω Output 12.4 to 40 GHz

TYPICAL PERFORMANCE DATA

INPUT RF= +12 dBm					INPUT RF= +18 dBm			
Input Frequency (MHz)	Conversion Loss (dB)	Harmonic Output Below F2 (-dBc)			Conversion Loss (dB)	Harmonic Output Below F2 (dBc)		
	F2	F1	F3	F4		F2	F1	F4
6.2	20.37	26.58	27.20	9.39	18.61	26.66	25.51	8.08
7.1	13.50	25.58	39.57	12.90	15.44	27.37	38.72	14.16
8.0	11.33	27.21	42.66	17.66	13.82	29.04	36.39	20.60
9.3	11.16	30.41	45.42	18.03	13.38	30.27	33.66	20.59
10.2	13.02	31.54	39.54	18.47	14.21	29.19	33.03	18.01
11.1	13.64	33.98	31.83	24.01	13.97	29.69	25.06	17.13
12.4	14.76	19.14	28.12	40.58	14.54	16.51	20.62	21.92
13.2	16.03	16.73	23.09	--	14.80	19.28	19.93	--
14.1	16.76	13.82	29.15	--	14.89	18.22	22.54	--
15.0	16.02	16.86	41.46	--	15.20	23.34	21.59	--
16.0	16.69	17.67	33.38	--	15.27	28.60	34.91	--
17.2	17.64	18.84	--	--	16.45	38.61	--	--
18.0	17.17	21.18	--	--	16.34	35.08	--	--
20.0	20.53	14.71	--	--	18.27	23.01	--	--





Mini-Circuits

MMIC SURFACE MOUNT

X2 Frequency Multiplier

CY2-44+

50Ω Output 12.4 to 40 GHz


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500 or 1K devices
Suggested Layout for PCB Design	PL-541
Evaluation Board	TB-973-CY244C+
Environmental Ratings	ENV08T2

ESD RATING

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with ANSI/ESD 5.1-2007

MSL TEST FLOW CHART



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[CY2-44+](#)