


50Ω    10 dB    6 to 26.5 GHz

## The Big Deal

- Wideband, 6-26.5 GHz
- Excellent coupling flatness 10±1.5 dB typ.
- Highly repeatable performance (GaAs based design)
- Small Size, 4 x 4 mm
- No external termination required



CASE STYLE: DG1847

## Product Overview

Mini-Circuits' EDC10-273+ is a 10 dB directional coupler that operates from 6 to 26.5 GHz packaged in MCLP 4 x 4mm, 24-lead package. It provides excellent coupling flatness over a broad bandwidth and good return loss. This coupler also provides a quadrature phase shift between the signal at the through port and coupler port. Manufacturing using GaAs Technology, this model results in relatively high repeatability in performance.

## Key Features

Feature	Advantages
Wideband, 6-26.5 GHz	EDC10-273+ can be used in many applications, saving component count. Also ideal for wide-band applications such as military and instrumentation.
Excellent coupling flatness	Excellent coupling flatness yields higher accuracy.
Small size, 4x4 MCLP package.	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.

# MMIC Surface Mount Directional Coupler

## EDC10-273+

50Ω 10 dB 6 to 26.5 GHz

### Features

- low mainline loss, 1.4 dB typ.
- excellent coupling flatness,  $\pm 1.5$  dB
- small size, 4x4 mm
- highly repeatable performance (GaAs based design)
- no external termination required.

### Applications

- satellite communications
- wireless infrastructure
- test and measurements



Generic photo used for illustration purposes only

CASE STYLE: DG1847

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications<sup>1</sup> at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		6000		26500	MHz
Mainline Loss	6000 - 10000	—	1.0	2.2	dB
	10000 - 18000	—	1.4	2.3	
	18000 - 23000	—	1.5	3.2	
	23000 - 26500	—	1.8	—	
Nominal Coupling	6000 - 10000	9.2	10.3	12.5	dB
	10000 - 18000	9.5	10.4	11.9	
	18000 - 23000	9.8	11.4	13.3	
	23000 - 26500	8.6	10.1	13.0	
Coupling Flatness( $\pm$ )	6000 - 26500	—	1.5	—	dB
Directivity	6000 - 10000	10	16	—	dB
	10000 - 18000	8.9	15	—	
	18000 - 23000	8.5	14	—	
	23000 - 26500	—	11	—	
Return Loss (Input)	6000 - 10000		24		dB
	10000 - 18000		17		
	18000 - 23000		15		
	23000 - 26500		15		
Return Loss (Output)	6000 - 10000		22		dB
	10000 - 18000		16		
	18000 - 23000		16		
	23000 - 26500		19		
Return Loss (Coupled)	6000 - 10000		24		dB
	10000 - 18000		16		
	18000 - 23000		14		
	23000 - 26500		14		

1. Measured on Mini-Circuits Characterization test board TB-EDC10-273+ with testboard loss deducted.

### Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Input Power	28 dBm (5 minute max.) 25 dBm (continuous)
Power at internal termination	19 dBm (5 minute max.) 16 dBm (continuous)

Permanent damage may occur if any of these limits are exceeded.


### Pad Connections

Function	Pad Number
INPUT	5
COUPLED	2
OUTPUT	14
GROUND	Paddle
NC (GROUND EXTERNALLY)	1,3,4,6-13,15-24

### Electrical Schematic



## Product Marking



## Additional Detailed Technical Information


additional information is available on our dash board. To access this information [click here](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1847 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 or 1K devices
Suggested Layout for PCB Design	PL-614
Evaluation Board	TB-EDC10-273+
Environmental Ratings	ENV08T2

## ESD Rating

Human Body Model (HBM): Class 1B (Pass 500V) in accordance with ANSI/ESD STM 5.1 - 2001

## MSL Test Flow Chart



## Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[EDC10-273+](#)