



Mini-Circuits®



# Test Cable

50Ω 2FT DC to 18 GHz

**CBL-2FT-NMNM+**

## FEATURES

- RoHS compliant
- Wideband coverage, DC to 18 GHz
- Extra rugged construction with strain relief for longer life
- Stainless steel N-Male connectors for long mating-cycle life
- Useful over temperature range, -55°C to 105°C
- Triple shield cable for excellent shielding effectiveness
- Flexible for easy connection & bend radius
- Superior stability of insertion loss, VSWR & phase vs. flexing
- 6 month guarantee\*

## APPLICATIONS

- High volume production test stations
- Research & development labs
- Environmental & temperature test chambers
- Replacement for OEM test port cables
- Field RF testing
- Cellular infrastructure site testing

*Generic photo used for illustration purposes only*

|            |               |              |
|------------|---------------|--------------|
| Model No.  | CBL-2FT-NMNM+ |              |
| Case Style | GM1106        |              |
| Connectors | 2.92 mm Male  | 2.92 mm Male |

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Product Guarantee\*

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.

## ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter           | Frequency (GHz) | Min. | Typ. | Max. | Units |
|---------------------|-----------------|------|------|------|-------|
| Frequency range     |                 | DC   |      | 18   | GHz   |
| Length <sup>1</sup> |                 |      | 2    |      | FT    |
| Insertion Loss      | DC - 2.5        | —    | 0.4  | 0.6  | dB    |
|                     | 2.5 - 6         | —    | 0.7  | 1.0  |       |
|                     | 6 - 12          | —    | 1.1  | 1.4  |       |
|                     | 12 - 18         | —    | 1.4  | 1.8  |       |
| Return Loss         | DC - 2.5        | 23   | 30   | —    | dB    |
|                     | 2.5 - 6         | 20   | 30   | —    |       |
|                     | 6 - 12          | 17   | 27   | —    |       |
|                     | 12 - 18         | 17   | 27   | —    |       |

1. Custom sizes available, consult factory.

## MAXIMUM RATINGS

| Parameter               | Ratings              |
|-------------------------|----------------------|
| Operating temperature   | -55°C to 105°C       |
| Storage temperature     | -55°C to 105°C       |
| Shielding Effectiveness | >100 dB              |
| Power Handling at 25°C  | 891W Max. at 0.4 GHz |
|                         | 539W Max. at 1 GHz   |
|                         | 363W Max. at 2 GHz   |
|                         | 180W Max. at 6 GHz   |
|                         | 117W Max. at 12 GHz  |
|                         | 88W Max. at 18 GHz   |

Permanent damage may occur if any of these limits are exceeded.

REV. K  
ECO-012138  
CBL-2FT-NMNM+  
MCL NY  
220217






Mini-Circuits



# Test Cable

**CBL-2FT-NMNM+**


## OUTLINE DRAWING



## OUTLINE DIMENSIONS (Inch/mm)

| A    |        | B   | C    | D   | E    | T    |        | wt    |
|------|--------|-----|------|-----|------|------|--------|-------|
| Feet | Meters |     |      |     |      | Feet | Meters | grams |
| 2    | 0.61   | .88 | .750 | .88 | .750 | 0.06 | 0.02   | 137   |

## CABLE CONSTRUCTION



- Connectors:
- Passivated stainless steel
  - Captive contact
  - Thick wall interface (SMA)
  - Gold plated beryllium copper center contacts
  - PTFE dielectric





Mini-Circuits





# Test Cable

CBL-2FT-NMNM+

## TYPICAL PERFORMANCE DATA

| Frequenc<br>(MHz) | Insertion Loss<br>(dB) | Return Loss<br>(dB) |        |
|-------------------|------------------------|---------------------|--------|
|                   |                        | N-MALE              | N-MALE |
| 10.00             | 0.02                   | 46.90               | 48.19  |
| 1000.00           | 0.25                   | 34.23               | 34.05  |
| 2000.00           | 0.36                   | 44.02               | 42.33  |
| 2500.00           | 0.41                   | 31.04               | 30.69  |
| 4000.00           | 0.53                   | 39.42               | 42.54  |
| 5000.00           | 0.60                   | 35.77               | 35.09  |
| 6000.00           | 0.67                   | 31.47               | 32.50  |
| 7000.00           | 0.73                   | 42.39               | 49.29  |
| 8000.00           | 0.81                   | 24.81               | 24.62  |
| 9000.00           | 0.86                   | 28.95               | 28.81  |
| 10000.00          | 0.92                   | 26.67               | 24.70  |
| 12000.00          | 1.04                   | 27.85               | 26.07  |
| 13000.00          | 1.10                   | 42.47               | 32.28  |
| 15000.00          | 1.26                   | 21.60               | 20.55  |
| 18000.00          | 1.52                   | 17.42               | 17.43  |



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[CBL-2FT-NMNM+](#)