

Surface Mount Directional Coupler

DBTC16-282LX+

50Ω, 16dB coupling, 5 to 2850 MHz

Features

- very flat coupling
- very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- cellular
- PCS
- DECT/PHS
- GSM
- PCN
- GPS



Generic photo used for illustration purposes only

CASE STYLE: AT1642

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost		
Reel Size	Devices/Reel	
7"	20, 50, 100, 200, 500	
13"	1000, 2000	

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		2850	MHz
Mainline Loss	5-50	—	0.8	1.2	dB
	50-1000	—	0.8	1.10	
	1000-2850	—	1.8	2.4	
Nominal Coupling	5-2850	—	16.8	—	dB
Coupling Flatness(±)	5-1000	—	0.3	0.6	dB
	1000-2850	—	0.6	0.9	
Directivity	5-50	13	15	—	dB
	50-1000	15	18	—	
	1000-2850	6	15	—	
Return Loss (Input)	5-50	18	20	—	dB
	50-1000	18	22	—	
	1000-2850	15	18	—	
Return Loss (Output)	5-50	18	22	—	dB
	50-1000	16	24	—	
	1000-2850	14	18	—	
Return Loss (Coupled)	5-50	13	15	—	dB
	50-1000	14	18	—	
	1000-2850	7	10	—	
Input Power	5-100	—	—	0.5	W
	100-2850	—	—	1.0	

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pad Number
INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
ISOLATE (DO NOT USE)	6

Product Marking



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
M167093
DBTC16-282LX+
WP/CP/AM
180517
Page 1 of 2

DBTC16-282LX+


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.166	.150	.155	.050	.037	.025
4.22	3.81	3.94	1.27	0.94	0.64
G	H	J	K	L	wt
.012	.060	.184	.030	.004	grams
0.30	1.52	4.67	0.76	0.10	0.10

Demo Board MCL P/N: TB-278
Suggested PCB Layout (PL-150)






NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl
5	0.75	16.56	16.18	22.13	24.33	17.45
40	0.68	16.38	16.96	25.73	30.78	19.85
100	0.69	16.40	17.23	26.07	31.31	20.09
1000	0.88	16.71	40.10	27.01	27.73	17.77
1500	1.03	16.85	19.30	28.14	27.82	13.91
1800	1.15	16.85	15.58	27.71	25.52	12.00
2000	1.24	16.83	13.77	27.46	24.45	10.95
2500	1.53	16.71	10.18	29.02	22.34	8.95
2850	1.82	16.58	8.06	32.68	21.73	7.72



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[DBTC16-282LX+](#)