# Gain Equalizers

# **EQY-SERIES**

50 $\Omega$  DC to 6 GHz



#### CASE STYLE: MC1631-1

# **The Big Deal**

- Excellent Return Loss, 20dB typ.
- Wide bandwidth, DC 6 GHz
- Small Size, 2 mm x 2 mm

# **Product Overview**

EQY series of absorptive Gain Equalizers are fabricated using highly repetitive GaAs IPD\* MMIC process incorporating resistors, capacitors and inductors having negative insertion loss slope. EQYs are available with nominal attenuation slope of 1,2,3,4,5,6,8 & 10 dB. They are packaged in tiny 2 x 2 mm 8-Lead MCLP™ package.

# **Key Features**

Feature	Advantages
Negative Insertion Loss Slope vs. Frequency	Useful for compesating negative gain slope of amplifiers, receivers, transmitters to achieve flat gain versus frequency.
Wide range of values 1,2,3,4,5,6,8 & 10 dB	Enables circuit designer to change nominal insertion loss values without mother-board redesign making the EQY series ideal for select at test application.
Wideband operation, DC to 6 GHz	Supports a wide array of applications including wireless cellular, microwave communications, satellite, defense and aerospace, medical broadband and optic applications.
Excellent Power Handling Capability 31/32 dBm	Enables its use at the output of a variety of amplfiers
Small Size and simple to use (2 mm x 2 mm)	As a single chip solution, the EQY series occupies less board space than a lumped element approach, minimizes component count and ensures repeatable performance over wide frequency range.

<sup>\*</sup>GaAs IPD (Gallium Arsenide Integrated Passive Device)

**EQY-4-63+** 

 $50\Omega$  4dB DC to 6 GHz

#### **Product Features**

- 4.2 dB Slope
- Small Package 2 x 2 mm MCLP
- Wide Bandwidth, DC-6 GHz
- Excellent Return Loss, 20 dB typ.

## **Typical Applications**

- Cellular
- PCS
- Communications
- Radar
- Defense



Generic photo used for illustration purposes only


CASE STYLE: MC1631-1

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **General Description**

EQY-4-63+ is an absorptive Gain Equalizer fabricated using highly repetitive GaAs IPD MMIC process incorporating resistors, capacitors and inductors having negative insertion loss slope. EQY-4-63+ has a nominal attenuation slope of 4.2 dB and is packaged in tiny 2 x 2 mm, 8-Lead MCLP™ package.

#### simplified schematic & pad description



		TOP VIEW		
GND	[1]	<i>(</i> )	8	GND
RF-IN	2		7	RF-OUT
NC	3		6	NC
NC	4]	C	5_	NC

Function	Pad Number	Description	
RF-IN	2	RF-Input pad	
RF-OUT	7	RF-Output pad	
GND	1,8 & Paddle	Ground	
NC	3-6	No connection, ground externally	

## Electrical Specifications $^{1}$ at 25 $^{\circ}\text{C},\,50\Omega,\,$ unless otherwise noted.

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		DC		6	GHz
Insertion Loss	0.01	4.4	4.8	5.2	dB
	1	_	4.5	_	
	2	_	3.6	_	
	3	2.3	2.7	3.0	
	4	_	1.9	_	
	5	0.6	1.1	1.5	
	6	_	0.6	_	
VSWR	0.01 -1	_	1.07	_	:1
	1 - 2	_	1.11	_	
	2 - 3	_	1.16	_	
	3 - 4	_	1.19	_	
	4 - 5	_	1.25	_	
	5 - 6	_	1.32	_	

<sup>1.</sup> Measured on Mini-Circuits Characterization Test Board TB-1041-4-63+. See Characterization Test Circuit (Fig. 1)

#### Absolute Maximum Ratings<sup>2</sup>

Operating Case Temperature	-40°C to 85°C	
Storage Temperature	-65°C to 150°C	
RF Input Power	31 dBm	

<sup>2.</sup> Permanent damage may occur if any of these limits are excedeed.

### **Characterization Test Circuit**





Fig 1. Block Diagram of Test Circuit used for characterization. Test Board TB-1041-4-63+ Conditions: Attenuation & Return Loss Pin=0 dBm


## **Product Marking**




Marking may contain other features or characters for internal lot control

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Input VSWR (:1)	Output VSWR (:1)
10	4.80	1.07	1.07
50	4.81	1.07	1.07
100	4.81	1.07	1.07
500	4.73	1.07	1.07
1000	4.47	1.09	1.08
1200	4.33	1.10	1.09
1700	3.92	1.12	1.11
2200	3.46	1.14	1.14
2700	2.99	1.18	1.16
3000	2.72	1.19	1.18
3200	2.54	1.20	1.19
4000	1.87	1.24	1.23
4500	1.49	1.25	1.27
5000	1.15	1.27	1.29
5500	0.86	1.30	1.32
6000	0.63	1.31	1.33






Additional Detailed Technical Information additional information is available on our dash board. To access this information click here		
Performance Data	Data Table	
	Swept Graphs	
Case Style	MC1631-1 Plastic package, Lead finish: Matte-tin	
Tape & Reel F66		
Standard quantities available on reel	7" reels with 20, 50, 100, 200, 500,1K or 2K devices	
Suggested Layout for PCB Design	PL-576	
Evaluation Board	TB-1041-4-63+	
Environmental Ratings	ENV08T1	

## **ESD Rating**

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001 Machine.

#### **MSL Test Flow Chart**



#### **Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mini-Circuits: EQY-4-63+