



Mini-Circuits

CERAMIC


## High Pass Filter

HFCN-3800D+

50Ω 4250 to 10000 MHz

## THE BIG DEAL

- Small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Hermetically sealed
- LTCC construction
- Low cost
- Protected by US Patent 7,760,485



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

## +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Sub-harmonic rejection
- Transmitters/receivers

ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT 25°C

| Parameter | Frequency (MHz) | Min.       | Typ. | Max. | Units |
|-----------|-----------------|------------|------|------|-------|
| Stop Band | Rejection Loss  | 2500       | —    | 30   | dB    |
|           |                 | 3200       | 20   | —    |       |
|           | Freq. Cut-Off   | 3800       | —    | 3.0  | dB    |
|           | VSWR            | 2500-3200  | —    | 20   |       |
| Pass Band | Insertion Loss  | 4250-10000 | —    | 2.0  | dB    |
|           |                 | 4500-9000  | —    | 1.5  |       |
|           | VSWR            | 3950-10000 | —    | 1.5  | :1    |

1. DC Resistance to ground is 100 Mohms min.


2. Measured on Mini-Circuits Characterization Test Board TB-285.

## MAXIMUM RATINGS


| Parameter                   | Ratings         |
|-----------------------------|-----------------|
| Operating temperature       | -55°C to +100°C |
| Storage temperature         | -55°C to +100°C |
| RF Power Input <sup>3</sup> | 7W max.at 25°C  |
| Max. DC Voltage at pins 1&3 | 25 VDC          |

3. Passband rating, derate linearly to 3W at 100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## TYPICAL FREQUENCY RESPONSE



## FUNCTIONAL SCHEMATIC



REV. E  
ECO-012367  
HFCN-3800D+  
RAV/CP/AM  
230822

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 3



Mini-Circuits®

CERAMIC

## High Pass Filter


HFCN-3800D+

## PIN CONNECTIONS

|        |         |
|--------|---------|
| RF IN  | 1       |
| RF OUT | 3       |
| GROUND | 2,4,5,6 |

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-285  
SUGGESTED PCB LAYOUT (PL-158)




- NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350 WITH DIELECTRIC THICKNESS: .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.




DENOTES PCB COPPER LAYOUT

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

## OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F     |
|------|------|------|------|------|-------|
| .126 | .063 | .035 | .024 | .022 | .011  |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28  |
| G    | H    | J    | K    |      | wt    |
| .039 | .024 | .042 | .123 |      | grams |
| 0.99 | 0.61 | 1.07 | 3.12 |      | .020  |

## TAPE &amp; REEL INFORMATION: F75



Mini-Circuits


CERAMIC

# High Pass Filter

HFCN-3800D+

## TYPICAL PERFORMANCE DATA AT 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 50.00           | 55.55               | 352.78    |
| 500.00          | 36.00               | 329.74    |
| 1500.00         | 31.71               | 104.95    |
| 3200.00         | 25.64               | 23.24     |
| 3400.00         | 25.91               | 14.49     |
| 3500.00         | 16.74               | 10.30     |
| 3800.00         | 3.55                | 2.30      |
| 4000.00         | 1.50                | 1.34      |
| 4250.00         | 0.97                | 1.31      |
| 4500.00         | 0.78                | 1.29      |
| 5000.00         | 0.70                | 1.31      |
| 5500.00         | 0.66                | 1.44      |
| 6000.00         | 0.61                | 1.48      |
| 6400.00         | 0.59                | 1.42      |



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[HFCN-3800D+](#)