



DESIGNER'S KIT K1-UNAT-A+

Fixed Attenuators



Mini-Circuits

50Ω DC to 6 GHz



FEATURES

- Wideband, 50Ω
- 3, 6, 10, 15, 20 dB attenuation
- Type-N male & female connectors
- Rugged Unibody construction
- Small size 2.1"
- Very low cost

MINI-CIRCUITS DESIGNER'S KITS
SPEED UP
THE SOLUTION



PRODUCT OVERVIEW

K1-UNAT-A+ is a designer's kit consisting of five different attenuator models in the UNAT-A+ family. There are two units per model for a total of ten units. Mini-Circuits' UNAT-A series are fixed attenuators operating from DC to 6000 MHz with excellent attenuation flatness. This attenuator series supports testing and measurement applications. Precise performance, excellent VSWR and rugged unibody construction makes these models an ideal solution for systems requiring precise attenuation.

K1-UNAT-A+ ELECTRICAL SPECIFICATIONS

(5 models, 2 of each, 10 total)

Model No. ¹	Frequency (GHz) f_L - f_U	Attenuation ² Flatness ³ (dB)					VSWR (:1)			Input Power ⁵ (W) Max.
		Nom. ⁴	DC-3 GHz	3-4.5 GHz	4.5-6 GHz	DC-6 GHz	DC-3 GHz	3-4.5 GHz	4.5-6 GHz	
			Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	
UNAT-3A+	DC-6	3 ± 0.3	0.20	0.15	0.15	0.40	1.22	1.22	1.50	2.0
UNAT-6A+	DC-6	6 ± 0.3	0.20	0.15	0.15	0.50	1.20	1.20	1.50	1.6
UNAT-10A+	DC-6	10 ± 0.3	0.20	0.15	0.20	0.40	1.20	1.20	1.30	1.7
UNAT-15A+	DC-6	15 ± 0.3	0.30	0.30	0.30	0.60	1.20	1.20	1.30	1.4
UNAT-20A+	DC-6	20 ± 0.3	0.40	0.40	0.40	0.75	1.20	1.20	1.20	0.8

1. See individual model data sheets for more info.

2. Attenuation varies by 0.3 dB max over temperature.

3. Flatness = variation over band divided by 2.

4. Nominal attenuation at 10 MHz.

5. RF Power at 25°C. Check individual model data sheet for derated power at 85°C.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-015321
K1-UNAT-A+
MCL NY
221010

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[K1-UNAT-A+](#)