



DESIGNER'S KIT K1-VAT2+

Fixed Attenuators

50Ω DC to 6 GHz



FEATURES

- Wideband, 50 Ω
- Input power 2W max.
- 3, 6, 10, 20 and 30 dB attenuation
- Rugged Unibody construction
- SMA Male and Female connectors
- Length less than 1.5"
- Low cost

MINI-CIRCUITS DESIGNER'S KITS
SPEED UP
THE SOLUTION



K1-VAT2+ ELECTRICAL SPECIFICATIONS

(5 models, 1 of each, 5 total)

Model	Freq. (GHz)	Attenuation² (dB)					VSWR (:1)					Input Power (W)
	f _L -f _U	Flatness¹										
		Nom.	DC-3 GHz Typ.	3-5 GHz Typ.	5-6 GHz Typ.	DC-6 GHz Typ.	DC-3 GHz Typ.	Max.	3-5 GHz Typ.	Max.	5-6 GHz Max.	
VAT-3W2+	DC-6	3±0.3	0.20	0.15	0.15	0.45	1.05	1.20	1.30	1.40	1.45	2
VAT-6W2+	DC-6	6±0.3	0.20	0.10	0.20	0.45	1.10	1.20	1.30	1.45	1.50	2
VAT-10W2+	DC-6	10±0.3	0.10	0.20	0.15	0.35	1.15	1.25	1.35	1.60	1.60	2
VAT-20W2+	DC-6	20±0.3	0.50	0.45	0.20	1.05	1.35	1.55	1.70	1.95	1.95	2
VAT-30W2+	DC-6	30±0.3	0.70	0.45	0.20	1.30	1.25	1.35	1.45	1.70	1.60	2

1. Flatness = variation over band divided by 2.

2. Attenuation varies by 0.3 dB max. over temperature.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[K1-VAT2+](#)