

8 Way-0° 75Ω 10 to 850 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.875W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections


SUM PORT	1
PORT 1	3
PORT 2	4
PORT 3	5
PORT 4	6
PORT 5	9
PORT 6	10
PORT 7	11
PORT 8	12
GROUND	2,7,8,13,14

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.870	.800	--	.100	.250	.100	.100
22.10	20.32	--	2.54	6.35	2.54	2.54
H	J	K	L		wt	
.047	.065	.065	.890		grams	
1.19	1.65	1.65	22.61		4.0	

Demo Board MCL P/N: TB-136
Suggested PCB Layout (PL-074)

- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
4. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 10 to 850 MHz
- aqueous washable
- shielded metal case
- J-leads for good solderability & strain relief
- good isolation, 25 dB typ.

Applications

- VHF/UHF
- CATV
- instrumentation
- cellular

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 9.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
f_L - f_U	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
10-850	34	20	25	15	20	15	0.7	1.5	1.0	2.0	1.8	3.0	—	—	—	0.6	0.7	1.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)						Amplitude Unbalance (dB)	Isolation (dB)				VSWR		
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-7	3-4	5-7	S	1	8
6.51	9.64	9.65	9.65	9.65	9.64	9.64	0.01	35.25	37.15	36.09	36.31	1.37	1.14	1.19
10.76	9.63	9.64	9.65	9.64	9.63	9.63	0.02	35.05	37.50	35.94	36.20	1.36	1.13	1.18
30.01	9.67	9.66	9.67	9.68	9.66	9.68	0.02	34.07	37.58	34.88	35.91	1.35	1.13	1.17
49.61	9.69	9.70	9.70	9.70	9.71	9.70	0.02	32.79	37.77	33.27	35.11	1.34	1.12	1.17
50.66	9.70	9.72	9.71	9.70	9.69	9.71	0.02	32.66	37.63	33.21	34.96	1.35	1.13	1.17
83.73	9.76	9.78	9.76	9.77	9.76	9.77	0.02	30.66	37.77	30.72	32.73	1.34	1.12	1.16
141.31	9.84	9.82	9.83	9.82	9.81	9.83	0.03	27.71	38.12	27.27	29.61	1.33	1.12	1.15
233.55	9.96	9.94	9.93	9.90	9.91	9.91	0.06	24.47	38.25	23.80	26.17	1.29	1.11	1.12
386.01	10.29	10.23	10.17	10.14	10.10	10.13	0.20	21.66	38.59	20.71	22.71	1.23	1.10	1.09
446.93	10.45	10.36	10.28	10.26	10.22	10.25	0.24	21.10	38.35	20.02	21.74	1.20	1.11	1.09
651.48	10.76	10.66	10.51	10.55	10.51	10.57	0.27	21.31	36.46	19.89	19.90	1.19	1.21	1.19
693.71	10.79	10.70	10.54	10.60	10.56	10.64	0.26	21.71	35.75	20.30	19.77	1.20	1.25	1.22
738.68	10.75	10.71	10.53	10.63	10.59	10.66	0.22	22.27	34.72	20.90	19.66	1.21	1.28	1.25
786.56	10.77	10.75	10.56	10.68	10.68	10.75	0.22	22.78	33.58	21.79	19.75	1.22	1.32	1.29
855.26	10.65	10.71	10.50	10.70	10.70	10.77	0.36	22.52	32.02	22.87	19.96	1.21	1.38	1.34

1. Total Loss = Insertion Loss + 9dB splitter loss.



electrical schematic



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[JCPS-8-850-75+](#)