

Miniature Surface Mount Fixed Attenuator

50Ω 0.5W 30dB DC to 1000 MHz

LAT-30+



Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	4
OUTPUT	2
GROUND	1,3

Features

- wideband, DC to 1000 MHz
- excellent VSWR, through entire band
- miniature size, SOT143 package
- aqueous washable

CASE STYLE: MMM168
PRICE: \$1.95 ea. QTY (20)

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Applications


- cellular
- PCS
- ISM
- VHF/UHF



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 2000, 3000

Outline Drawing




Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K
.045	.055	.105	.120	.047	.005	.083	.104	.070	.080
1.14	1.40	2.67	3.05	1.19	0.13	2.11	2.64	1.78	2.03
L	M	N	P	Q	R	S	T		
.018	.024	.030	.036	.015	.021	.023	.005		wt
0.46	0.61	0.76	0.91	0.38	0.53	0.58	0.13		grams

Demo Board MCL P/N: TB-39

Suggested PCB Layout (PL-225)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Electrical Specifications at 25°C


FREQ. RANGE (MHz)	ATTENUATION (dB) Flatness, Max.	VSWR (:1) Max.		MAX. INPUT POWER ¹ (W)
		DC-0.5 GHz	DC-1 GHz	
$f_L - f_U$	Nom.			
DC-1000	30±1.7	0.5	1.2	0.5

1. RF power at 25°C case temperature: 1/2 Watt. Derate linearly to 0.2 Watt at 85°C.
2. Flatness= variation over band divided by 2


Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
0.50	30.07	1.04
100.00	30.08	1.04
200.00	30.13	1.04
300.00	30.21	1.06
400.00	30.33	1.08
500.00	30.48	1.09
650.00	30.78	1.11
750.00	31.04	1.13
850.00	31.32	1.14
1000.00	31.87	1.17

LAT-30+
ATTENUATION



LAT-30+
VSWR



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[LAT-30+](#)