

Surface Mount

# Monolithic Amplifier

DC-8 GHz

## Product Features

- DC-8 GHz
- Output power, 10.6 dBm typ.
- Internally Matched to 50 Ohms
- Excellent package for heat dissipation, exposed metal bottom
- Flat output power to 10 GHz
- Aqueous washable
- Protected by US Patent 6,943,629



Generic photo used for illustration purposes only

## LEE-29+

CASE STYLE: FG873

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Typical Applications

- Cellular
- PCS
- Communication receivers & transmitters
- Satellite communication, military

## General Description

LEE-29+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a 3X3mm MCLP molded plastic package. Expected MTBF is 2,000 years at 85°C case temperature.

## simplified schematic and pin description



| Function         | Pin Number | Description  |
|------------------|------------|--|
| RF IN            | 1          | RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.  |
| RF-OUT and DC-IN | 3          | RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit". |
| GND              | 2,4        | Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.  |

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. K  
M151107  
ED-10757/2  
LEE-29+  
RS/YB/FL  
201016  
Page 1 of 4

## Electrical Specifications at 25°C and 40mA, unless noted

| Parameter   |                | Min. | Typ. | Max. | Units |
|---|----------------|------|------|------|-------|
| Frequency Range*                                  |                | DC   |      | 8    | GHz   |
| Gain  | f=0.1 GHz      | —    | 15.5 | —    | dB    |
|   | f=1 GHz        | —    | 15.4 | —    |       |
|   | f=2 GHz        | 13.3 | 15.4 | —    |       |
|   | f=4 GHz        | —    | 14.9 | —    |       |
|   | f=5 GHz        | —    | 14.1 | —    |       |
|   | f=8 GHz        | —    | 12.5 | —    |       |
|   | f=10 GHz       | —    | 10.6 | —    |       |
| Input Return Loss                                 | f= DC to 3 GHz |      | 15.5 |      | dB    |
|   | f= 3 to 8 GHz  |      | 17.5 |      |       |
| Output Return Loss                                | f= DC to 3 GHz |      | 17.5 |      | dB    |
|   | f= 3 to 8 GHz  |      | 12.5 |      |       |
| Output Power @ 1 dB compression                   | f= 2 GHz       | 10.6 | 11.9 | —    | dBm   |
|   | f= 8 GHz       | 10.0 | 11.5 | —    |       |
| Output IP3  |                |      | 25.5 |      | dBm   |
| Noise Figure                                      |                |      | 5.5  |      | dB    |
| Recommended Device Operating Current              |                |      | 40   |      | mA    |
| Device Operating Voltage                          |                | 3.2  | 3.6  | 4.0  | V     |
| Device Voltage Variation vs. Temperature at 40 mA |                |      | -1.9 |      | mV/°C |
| Device Voltage Variation vs. Current at 25°C      |                |      | 8.6  |      | mV/mA |
| Thermal Resistance, junction-to-case <sup>1</sup> |                |      | 120  |      | °C/W  |

\*Guaranteed specification DC-8 GHz. Low frequency cut off determined by external coupling capacitors.

## Absolute Maximum Ratings

| Parameter              | Ratings        |
|------------------------|----------------|
| Operating Temperature* | -45°C to 85°C  |
| Storage Temperature    | -65°C to 150°C |
| Operating Current      | 55mA           |
| Input Power            | 15dBm          |

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation.

<sup>1</sup>Case is defined as ground leads.

\*Based on typical case temperature rise 5°C above ambient.

## Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

## Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

## Performance data, graphs, s-parameter data set (.zip file)

## Case Style: FG873

Plastic package, exposed paddle, lead finish: tin-silver over nickel

Tape & Reel: F68

7" Reels with 20, 50, 100, 200, 500, 1K devices


13" Reels with 2K, 3K, 4K devices

## Suggested Layout for PCB Design: PL-252

## Evaluation Board: TB-413-29+

## Environmental Ratings: ENV08T2

## Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

| R BIAS |   |
|--------|---|
| Vcc    | "1%" Res. Values<br>(ohms)<br>for Optimum Biasing |
| 7      | 88.7  |
| 8      | 113   |
| 9      | 137   |
| 10     | 162   |
| 11     | 187   |
| 12     | 215   |
| 13     | 237   |
| 14     | 261   |
| 15     | 287   |
| 16     | 316   |
| 17     | 340   |
| 18     | 365   |
| 19     | 392   |
| 20     | 412   |

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**ESD Rating**

Human Body Model (HBM): Class 1A (250v to &lt; 500v) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (&lt; 100v) in accordance with ANSI/ESD STM 5.2 - 1999

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

| No. | Test Required                   | Condition   | Standard                       | Quantity |
|-----|---------------------------------|---|--------------------------------|----------|
| 1   | Visual Inspection               | Low Power Microscope<br>Magnification 40x   | MIP-IN-0003<br>(MCT spec)      | 45 units |
| 2   | Electrical Test                 | Room Temperature  | SCD<br>(MCL spec)              | 45 units |
| 3   | SAM Analysis                    | Less than 10% growth in term of<br>delamination   | J-Std-020C<br>(Jedec Standard) | 45 units |
| 4   | Moisture Sensitivity<br>Level 1 | Bake at 125°C for 24 hours<br>Soak at 85°C/85%RH for 168 hours<br>Reflow 3 cycles at 260°C peak | J-Std-020C<br>(Jedec Standard) | 45 units |

**MSL Test Flow Chart****Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[LEE-29+](#)