Ceramic Low Pass Filter

50Ω

DC⁽¹⁾ to 3000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		
RF Power Input*	10W max. at 25°C		

* Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	1
RF OUT	3
GROUND	2,4


Outline Drawing



Outline Dimensions (inch)

	、						
	G	F	E	D	С	В	Α
	.169	.009	.032	.020	.037	.063	.126
	4.29	0.23	0.81	0.51	0.94	1.60	3.20
wt	Р	N	M	L	K	J	н
grams	.071	.012	.087	.024	.122	.024	.087
.020	1.80	0.30	2.21	0.61	3.10	0.61	2.21
.020	1.80	0.30	2.21	0.61	3.10	0.61	2.21

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



Features

- excellent power handling, 10W
- small size
- 7 sections
- temperature stable
- LTCC construction
- protected by U.S. Patent 6,943,646

Applications

- harmonic rejection
- VHF/UHF transmitters/receivers
- lab use

LFCN-3000+




Generic photo used for illustration purposes only CASE STYLE: FV1206

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications ^(1,2) at 25°C							
Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC-3000	_	_	1.2	dB
Pass Band	Freq. Cut-Off	F2	3600	—	3.0	—	dB
	VSWR	DC-F1	DC-3000	—	1.2	—	:1
		F3	4550	20	—	—	dB
Cton Bond	Rejection Loss	F4-F5	4780-7500	—	30	—	dB
Stop Band		F6	10000	—	20	—	dB
	VSWR	F3-F6	4550-10000	_	20	_	:1

(1) In Applications where DC isolation to ground is required, coupling capacitors are recommended to avoid DC leakage. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide>100 MOhm isolation to ground. (2) Measured on Mini-Circuits Characterization Test Board TB-270.





Electrical Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.03	1.01
1000	0.29	1.23
1500	0.40	1.34
3000	0.77	1.15
3600	2.96	3.08
4480	25.24	25.19
4780	40.44	29.96
5000	46.26	27.59
6500	36.73	19.98
10000	21.68	18.70
11000	19.41	13.70
13000	13.67	12.99
15000	14.56	11.61
17000	16.94	4.41
20000	24.85	4.88





Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please wisit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. K M173979 LFCN-3000+ EDR-6783/6 RVN/AD/CP/AM 190426

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mini-Circuits: