

Ceramic Active Mixer

Level -3 (LO Power -3 dBm) 750 to 2400 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	100mW
IF Current	40mA
LO Power	10mW


Pin Connections

LO	10
RF	5
IF	3
DC	7
GROUND	1,2,4,6,8,9

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.30	.250	.105	.266	.050	.050	.012
7.62	6.35	2.67	6.76	1.27	1.27	0.30
H	J	K	L	M	wt	
.029	.004	.085	.296	.030	grams	
0.74	0.10	2.16	7.52	0.76	0.3	

Demo Board MCL P/N: TB-403
Suggested PCB Layout (PL-145)



- CAPACITOR C1: 1000 pF, 0402 SIZE
FILTER F1: LFCN-490+, FV1206 CASE STYLE
- NOTE: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low conversion loss, 6.1 dB typ.
- wide bandwidth, 750 to 2400 MHz
- LTCC double balanced mixer with LO amplifier
- aqueous washable
- low profile
- low cost
- protected by U.S. Patent 7,027,795

Applications

- PCN
- defense & weather radar
- cellular
- UHF TV

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		DC POWER		IP3 at center band (dBm)
		$\bar{X}$	σ	Max.	Typ.	Min.	Typ.	Min.	Volt	Current (mA) Max.	
750-2400	DC-500	6.1	0.1	9.8	20	4	55	28	5	110	18


1 dB Compr. +10 dBm typ.

*Conversion Loss at IF= 30 MHz.

Typical Performance Data


Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO -3dBm	LO -3dBm	LO -3dBm	LO -3dBm	LO -3dBm
740.00	710.00	5.98	25.78	32.91	2.60	2.24
800.00	770.00	6.25	21.44	40.53	2.61	2.11
900.00	870.00	9.01	21.78	51.64	6.73	1.96
1000.00	970.00	7.39	15.99	36.56	4.55	1.90
1100.00	1070.00	6.51	11.39	46.11	2.40	1.60
1200.00	1170.00	8.22	14.01	56.21	4.95	1.45
1300.00	1270.00	7.75	23.06	62.69	4.48	1.25
1400.00	1370.00	6.35	19.72	65.30	2.44	1.10
1500.00	1470.00	6.15	17.29	69.44	2.06	1.42
1600.00	1570.00	5.22	12.57	71.04	1.36	1.53
1700.00	1670.00	5.23	8.87	61.70	1.21	1.49
1800.00	1770.00	5.58	14.87	58.23	1.65	1.38
1900.00	1870.00	5.41	18.11	54.22	1.34	1.29
2000.00	1970.00	6.16	17.88	52.30	1.37	1.16
2100.00	2070.00	8.05	14.77	52.20	2.70	1.24
2140.00	2110.00	7.81	16.43	53.26	2.87	1.33
2200.00	2170.00	7.37	15.65	57.24	3.02	1.45
2300.00	2270.00	6.90	16.43	60.29	2.90	1.72
2340.00	2310.00	6.79	17.73	58.64	2.66	1.88
2400.00	2370.00	6.92	22.78	58.59	2.53	2.05

Electrical Schematic



LFCN-490+ is added to improve L-I isolation.

MACA-242H+



Generic photo used for illustration purposes only

CASE STYLE: DZ1034

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications











Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
MACA-242H
ED10457/8
DJ/CP/AM/QL
220930



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[MACA-242H+](#)