

High IP3

Frequency Mixer WIDE BAND

Level 13 (LO Power+13 dBm) 500 to 3500 MHz

MCA-35MH+



Generic photo used for illustration purposes only

CASE STYLE: DZ883

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200 mW
IF Current	40 mA

Pin Connections

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

Features

- wide bandwidth, 500 to 3500 MHz
- excellent L-R isolation, 32 dB typ. (1800-2500 MHz)
- good matching 2:1 VSWR typ. (over 1800-2800 MHz)
- small size 0.25"x0.3"x0.2"
- aqueous washable
- triple balanced mixer
- protected by US Patent 6,917,796

Applications

- cellular
- PHS
- PCN
- WiMAX
- PDC
- DECT

Electrical Specifications (T_{AMB}=-55°C to 100°C)

FREQUENCY (MHz)		CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f _L -f _U	IF	$\bar{X}$	σ	Max.	Typ.	Min.	Typ.	Min.	
500-3500	10-1500	6.9	0.1	8.7					
500-800	10-300	6.3	0.1	7.7	18	11	29	23	19
800-1000	10-200	6.5	0.1	7.7	24	17	28	20	22
1000-1800	10-800	6.6	0.1	8.7	29	20	28	20	20
1800-2000	10-200	6.3	0.1	7.7*	32	25	29	23	19
1800-2500	10-700	5.8	0.1	7.9	32	22	27	20	19
2000-3500	10-1500	6.5	0.1	8.7	29	17	23	15	19

1 dB COMP. +9 dBm typ.


*Conversion loss tested at 30 MHz IF

see individual band specs


Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
460.00	490.00	6.07	14.89	31.56	1.65	1.44
820.00	850.00	6.55	22.74	28.78	2.86	1.11
1000.00	1030.00	6.52	27.75	27.75	3.40	1.27
1400.00	1430.00	6.99	32.26	26.14	2.21	1.75
1800.00	1830.00	6.07	32.12	30.09	1.92	1.57
1992.00	2022.00	5.92	33.68	28.32	1.70	1.54
2097.00	2127.00	5.70	32.52	28.29	1.55	1.38
2202.00	2232.00	5.82	31.97	28.76	1.54	1.34
2395.00	2425.00	6.15	30.82	26.29	1.67	1.35
2500.00	2530.00	5.95	30.44	26.01	1.87	1.37
2600.00	2630.00	6.13	31.78	26.48	2.20	1.30
2700.00	2730.00	6.47	30.50	26.37	2.54	1.28
2800.00	2830.00	6.75	30.68	25.93	2.82	1.34
2900.00	2930.00	6.94	30.99	25.14	3.05	1.49
3000.00	3030.00	6.74	28.34	24.21	3.53	1.62
3100.00	3130.00	6.80	29.07	23.03	3.88	1.83
3200.00	3230.00	6.80	28.43	21.62	3.85	2.01
3300.00	3330.00	6.81	27.62	22.07	3.63	2.12
3400.00	3430.00	6.53	27.00	21.28	3.23	2.19
3500.00	3530.00	6.35	24.71	20.83	2.77	2.20

Outline Drawing



PCB Land Pattern




Suggested L layout, Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.30	.250	.190	.266	.050	.050	.012
7.62	6.35	4.83	6.76	1.27	1.27	0.30
H	J	K	L	M	wt	
.029	.004	.085	.296	.030	grams	
0.74	0.10	2.16	7.52	0.76	0.5	

Demo Board MCL P/N: TB-144

Suggested PCB Layout (PL-045)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS, TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- ▨ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp











www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. H
M151107
ED-9595B/1
MCA-35MH+
DJ/TD/CP/AM
200604

Performance Charts

MCA-35MH+



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[MCA-35MH+](#)