

FIXED ATTENUATORS

Designer's Kit K3-VAT2+

MINI-CIRCUITS DESIGNER'S KITS
SPEED UP
THE SOLUTION!



DC to 6 GHz

VAT-W2+ Features

- Wideband, 50 Ω
- Input power 2 W max.
- 3, 6 and 10 dB attenuation
- Rugged Unibody construction
- SMA Male & Female connectors
- Length less than 1.5"
- Low cost



All models are
RoHS compliant

Kit K3-VAT2+ Electrical specifications of each model (3 models, 2 of each, 6 total)

Model	Frequency (GHz)	Attenuation ¹ (dB)					VSWR (:1)				Input Power (W)	
		Flatness ²										
		Nom.	DC-3 GHz Typ.	3-5 GHz Typ.	5-6 GHz Typ.	DC-6 GHz Typ.	DC-3 GHz Typ.	Max.	3-5 GHz Typ.	Max.	5-6 GHz Typ.	Max.
VAT-3W2+	DC-6	3±0.3	0.20	0.15	0.15	.45	1.05	1.20	1.30	1.40	1.45	2
VAT-6W2+	DC-6	6±0.3	0.20	0.10	0.20	.45	1.10	1.20	1.30	1.45	1.50	2
VAT-10W2+	DC-6	10±0.3	0.10	0.20	0.15	.35	1.15	1.25	1.35	1.60	1.60	2

1. Attenuation varies by 0.3 dB max. over temperature.

2. Flatness=variation over band divided by 2.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For quick access to product information see MINI-CIRCUITS CATALOG & WEB SITE

RF/IF & MICROWAVE COMPONENTS

REV. A
M110332
K3-VAT2+

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[K3-VAT2+](#)