

Mini-Circuits®

CERAMIC BALUN

RF Transformer

NCS1-222-75+

75Ω 950 to 2200 MHz 1:1 Ratio

FEATURES

- Wideband, 950 to 2000 MHz
- Low phase unbalance, 5 deg. and amplitude unbalance, 0.9 dB typ.
- Miniature size, 0.079"x0.049"x0.033"
- LTCC construction
- Low cost
- Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-1

APPLICATIONS

- WCDMA
- PCS
- GPS

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio		1			
Frequency Range		950		2200	MHz
Insertion Loss ¹	950 - 2200	—	1.0	1.5	dB
Amplitude Unbalance	950 - 2200	—	0.9	1.4	dB
Phase Unbalance ²	950 - 2200	—	5	8	Degree

1. Insertion Loss is referenced to mid-band loss, 0.7 dB. Reference Demo Board TB-626+


2. Relative to 180°

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	3W at 25°C

Permanent damage may occur if any of these limits are exceeded.

CONFIGURATION R




Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
ECO-010109
NCS1-222-75+
MCL NY
211013

PAGE 1 OF 3



Mini-Circuits

CERAMIC BALUN


RF Transformer

NCS1-222-75+

PAD CONNECTIONS

PRIMARY DOT (Unbalanced Port)	2
PRIMARY (GND)	1,3
SECONDARY DOT (Balanced)	4
SECONDARY (Balanced)	6
NO CONNECTION	5


OUTLINE DRAWING



*Shape of index marking may vary

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-626+ SUGGESTED PCB LAYOUT (PL-348)



NOTES:


1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F
.079	.049	.033	.014	.012	.012
2.01	1.24	0.84	0.36	0.30	0.30
G	H	J	K		wt
.026	.014	.039	.110		grams
0.66	0.36	1.00	2.80		.008




TAPE & REEL INFORMATION: F74



TYPICAL PERFORMANCE DATA³

Frequency (MHz)	Insertion Loss (dB)	Input Return Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (deg)
950	0.90	13.69	0.68	4.34
1100	0.79	16.77	0.14	0.02
1300	0.76	19.79	0.02	2.81
1400	0.76	20.85	0.04	3.48
1600	0.79	22.77	0.26	1.16
1800	0.84	23.40	0.57	2.73
1900	0.88	23.04	0.69	1.86
2000	0.92	22.48	0.82	0.74
2100	0.96	21.90	0.88	0.82
2200	1.01	21.77	0.88	2.44

3. Measured with Agilent E5071B network analyzer using impedance conversion and port extension.



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[NCS1-222-75+](#)