

Plug-In Low Pass Filter

PLP-2.5+

50Ω DC to 2.5 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7
CASE GROUND	2,3,4,5,6,7

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

Features

- rugged welded case, hermetic
- other standard and custom PLP models available with wide selection of fco

Applications

- test equipment
- lab use
- transmitters/receivers
- military/hi-rel applications



Generic photo used for illustration purposes only

CASE STYLE: A01

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Pass Filter Electrical Specifications


PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-2.5	2.75	3.8-5.0 5.0-200	1.7 18

1 dB compression at +13 dBm input power

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
0.10	0.06	0.00	1.00	321.99
0.40	0.08	0.01	1.06	323.09
0.80	0.10	0.01	1.12	327.26
1.10	0.12	0.00	1.18	330.19
1.40	0.17	0.01	1.25	332.28
1.80	0.24	0.01	1.32	334.96
2.10	0.28	0.04	1.40	338.56
2.50	0.45	0.07	1.48	341.36
2.75	1.34	0.45	1.56	346.34
3.00	5.99	1.21	1.65	352.96
3.20	11.74	1.32	1.74	360.97
3.30	14.61	1.31	1.84	372.10
3.50	19.96	1.23	1.94	385.34
3.60	22.44	1.20	2.05	402.77
3.80	27.02	1.14	2.17	422.48
4.00	31.16	1.09	2.29	449.68
4.20	34.94	1.06	2.42	492.19
4.40	38.42	1.03	2.50	530.37
4.60	41.65	1.00	2.75	689.14
4.80	44.65	0.98	2.86	697.89
5.00	47.46	0.98	3.02	582.03
5.20	50.11	0.99	3.19	410.17
29.60	89.73	3.84	3.37	280.46
53.90	87.32	1.38	3.56	201.19
78.30	89.67	4.26	3.80	145.71
102.60	86.70	3.08	3.98	119.20
127.00	88.19	4.27	4.20	96.41
151.30	90.79	3.34	4.44	79.41
175.70	90.31	4.10	4.74	65.38
200.00	93.47	9.35	5.01	55.83



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
PLP-2.5+
200402

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[PLP-2.5+](#)