

Low Pass Filter

50Ω DC to 264 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

RF IN	2
RF OUT	6
GROUND	1, 3, 4, 5, 7, 8

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R		
.050	.040	.195	.390	.120	.390	.070		wt.
1.27	1.02	4.95	9.91	3.05	9.91	1.78		grams
								0.25

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



Features

- high rejection
- sharp insertion loss roll off
- excellent VSWR, 1.2:1 typ. @ passband
- aqueous washable

Applications

- wireless communications
- receivers / transmitters



Generic photo used for illustration purposes only
CASE STYLE: GP731

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000


Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)	VSWR (:1)
(Loss < 2dB)	(Loss 3dB)	(Loss > 20dB) (Loss > 40dB)	Passband Typ. Stopband Typ.
DC - 264	288	365 - 425 425 - 1500	1.2 20

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
$\bar{x}$	σ			
0.5	0.08	0.07	3.0	2.90
50.0	0.19	0.07	5.0	2.56
80.0	0.26	0.07	10.0	2.51
125.0	0.38	0.07	30.0	2.50
150.0	0.45	0.07	50.0	2.54
202.0	0.58	0.07	70.0	2.55
264.0	1.09	0.08	90.0	2.68
276.0	1.52	0.10	100.0	2.67
288.0	3.07	0.21	120.0	2.79
300.0	6.45	0.33	140.0	2.92
311.0	10.57	0.37	160.0	3.06
335.0	19.87	0.37	190.0	3.44
365.0	30.57	0.37	200.0	3.60
425.0	51.05	0.76	220.0	4.05
500.0	76.32	8.01	240.0	4.64
1000.0	71.79	6.79	250.0	5.03
1250.0	66.32	2.76	264.0	6.07
1500.0	73.26	6.64	275.0	7.83



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[RLP-264+](#)