

Frequency Mixer

Level 13 (LO Power +13 dBm) 5 to 2500 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded	

Pin Connections

LO	1
RF	4
IF	5
GROUND	2,3,6


Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F
.250	.31	.20	.100	.050	.055
6.35	7.87	5.08	2.54	1.27	1.40
G	H	J	K		wt
.040	.070	.270	.050		grams
1.02	1.78	6.86	1.27		0.50

Demo Board MCL P/N: TB-03
Suggested PCB Layout (PL-052)



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.iso

Features

- excellent L-R isolation, 32 dB typ.
- conversion loss, 7.0 dB typ.
- small size, 0.25"x0.31"x0.2"

Applications

- cellular
- satellite distribution
- GPS

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)						IP3 at center band (dBm)
LO/Rf	IF					L		M		U		L		M		U		
f_L - f_U		$\bar{X}$	σ	Max.	Total Range Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.
5-2500	5-1500	7.0	.20	8.5	9.8	54	28	32	23	32	20	34	23	32	25	28	17	17


1 dB COMP.: +9 dBm typ.

L = low range [f_L to $10 f_L$]
M = mid band [$2f_L$ to $f_U/2$]
U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13 dBm	LO +13 dBm	LO +13 dBm	LO +13 dBm	LO +13 dBm
5.00	35.00	6.60	43.66	31.16	1.43	2.14
10.10	40.10	6.47	48.02	33.66	1.42	2.07
20.18	50.18	6.42	53.20	34.80	1.42	2.09
33.51	63.51	6.47	56.82	34.60	1.42	2.09
49.03	79.03	6.46	59.20	34.63	1.42	2.08
81.42	111.42	6.50	57.10	34.59	1.42	2.06
135.23	165.23	6.58	52.43	34.78	1.45	2.08
224.60	194.60	6.60	46.08	35.72	1.52	2.08
373.01	343.01	6.77	40.43	37.11	1.71	1.95
480.71	450.71	6.88	38.16	36.46	1.86	1.92
545.72	515.72	6.82	37.54	35.91	1.95	1.80
798.38	768.38	6.92	36.87	32.89	2.23	1.71
906.34	876.34	6.92	37.27	31.38	2.32	1.62
1168.03	1138.03	7.19	36.90	30.53	2.35	1.61
1250.00	1220.00	7.10	38.52	31.35	2.37	1.62
1505.28	1475.28	6.78	39.76	30.96	2.27	1.65
1800.00	1770.00	6.85	31.84	27.67	2.24	1.57
2000.00	1970.00	7.07	28.62	28.09	2.19	1.62
2200.00	2170.00	7.09	25.62	28.13	2.18	1.77
2500.00	2470.00	7.52	22.96	26.44	1.95	1.99

Electrical Schematic









Generic photo used for illustration purposes only

CASE STYLE: TT240

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[RMS-25MH+](#)