Coaxial **Bandpass Filter**

50Ω 140 to 160 MHz

The Big Deal

- High rejection
- · Good VSWR, 1.3:1 typ.@ passband
- Rugged unibody construction
- Connectorized package

Product Overview

SBP-150+ is a 50Ω bandpass filter in a connectorized package. This bandpass filter covers from 140 to 160 MHz, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages			
High rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.			
Good VSWR, 1.3:1 typ.@ passband	This provides well matched input and output ports.			
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.			

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits



SBP-150+



Coaxial Bandpass Filter

50Ω 140 to 160 MHz

Features

- High rejection
- Good VSWR, 1.3:1 typ.@ passband
- Rugged unibody construction
- Connectorized package

Applications

- Fixed applications
- Amateur satellite
- Mobile communication

Functional Schematic



Typical Frequency Response



The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center frequency	-	-	-	150	-	MHz
Pass Band	Insertion Loss	F1-F2	140 - 160	-	2.2	3.0	dB
	VSWR	F1-F2	140 - 160	-	1.3	1.8	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 100	40	53	-	dB
		F3-F4	100 - 120	20	27	-	dB
Stop Band, Upper	Insertion Loss	F5-F6	190 - 250	20	32	-	dB
		F6-F7	250 - 2000	40	55	-	dB

Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	0.5 W max.		

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	96.06	43.68	140	34.25
10	77.22	38.82	141	32.86
100	53.87	100.21	142	31.75
118	31.39	52.98	143	30.84
120	28.26	43.79	144	30.06
124	21.31	26.10	145	29.41
134	3.14	1.45	146	28.87
140	1.96	1.21	147	28.43
145	1.79	1.22	148	28.12
150	1.75	1.20	149	27.91
155	1.85	1.11	150	27.80
160	2.12	1.18	151	27.77
164	3.31	1.77	152	27.79
178	20.98	18.53	153	27.88
190	31.93	33.19	154	28.03
250	59.36	91.76	155	28.27
500	93.20	235.95	156	28.64
1000	88.44	209.34	157	29.19
1500	62.14	126.54	158	30.00
2000	55.51	86.66	160	32.42





SBP-150+ INSERTION LOSS

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's transforms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A ECO-005139 SBP-150+ EDU3158 URJ 201127 Page 2 of 3





Generic photo used for illustration purposes only CASE STYLE: FF99

Model

SBP-150+

Connectors

SMA



Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

в	D	Е	Wt.
.70	1.98	.312	grams
17.78	50.29	7.92	42.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mini-Circuits:

SBP-150+