

Surface Mount High Pass Filter

50Ω 18 to 200 MHz

Maximum Ratings

Operating Temperature -40°C to 85°C


Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

RF IN	1
OUTPUT	8
GROUND	2,3,4,5,6,7

Outline Drawing



PCB Land Pattern




Outline Dimensions (inch)

A	B	C	D	E	F	G
0.75	0.38	0.28	0.01	0.05	0.02	0.2
19.05	9.65	7.11	0.25	1.27	0.51	5.08

H	J	K	M	N	P	wt
0.075	0.6	0.45	0.47	0.1	0.15	grams
1.91	15.24	11.43	11.94	2.54	3.81	1.60

Demo Board MCL P/N: TB-187+ Suggested PCB Layout (PL-049)



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low pass band insertion loss
- custom models available


Applications

- HF/VHF
- lab use
- transmitters/receivers


High Pass Filter Electrical Specifications

STOP BAND (MHz)	f _{co} , MHz Nom. (loss 3 dB) Typ.	PASSBAND (MHz)	VSWR (:1)		POWER INPUT (W)
			Stopband Typ.	Passband Typ.	
DC-9 (loss > 40 dB)	9-13 (loss > 20 dB)	16.5	18	1.25	0.5

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.99	85.38	1737.18
8.96	50.79	217.15
10.00	43.91	124.09
12.01	30.33	69.49
13.00	23.71	48.26
14.96	11.00	16.11
15.96	4.97	55.54
17.04	1.38	1.76
17.46	0.92	1.30
18.00	0.70	1.11
24.96	0.35	1.09
30.10	0.33	1.26
40.00	0.26	1.17
60.06	0.21	1.03
70.09	0.21	1.06
90.17	0.22	1.10
100.22	0.22	1.11
119.85	0.23	1.12
160.59	0.25	1.13
200.00	0.26	1.14



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
SCHF-17
EDR-3754/1
RAV
200811

SCHF-17+
SCHF-17



Generic photo used for illustration purposes only

CASE STYLE: YY161

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SCHF-17+](#)