

Low Pass Filter

50Ω DC to 22 MHz

Maximum Ratings

Operating Temperature -40°C to 85°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W Max.

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

INPUT 1

OUTPUT 8

GROUND 2, 3, 4, 5, 6, 7

Outline Drawing







Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	gr
.040	.660	.200	.470	.055	.060	
1.02	16.76	5.08	11.94	1.40	1.52	

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368

Suggested PCB Layout (PL-230)



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Features

- high rejection
- sharp cut-off
- shielded package
- aqueous washable
- low cost

Applications

- defense communications
- receivers / transmitters
- harmonic rejection

SXLP-21.4+

Generic photo used for illustration purposes only
CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)	VSWR (:1)
(Loss < 1dB)	(Loss 3dB)	(Loss > 20dB) (Loss > 40dB)	Passband Typ. Stopband Typ.
DC - 22	24.5	32 - 41 41 - 2000	1.3 18

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
$\bar{x}$	σ			
0.5	0.04	0.01	0.5	34.48
2.5	0.08	0.01	2.0	36.18
11.0	0.16	0.01	4.0	36.18
19.0	0.33	0.01	6.0	36.53
22.0	0.47	0.01	8.0	37.40
23.5	0.95	0.04	10.0	38.72
24.0	1.53	0.09	12.0	39.90
24.5	2.46	0.14	14.0	41.60
25.5	5.35	0.26	16.0	44.45
27.5	12.69	0.38	18.0	48.34
32.0	26.80	0.44	20.0	53.79
41.0	46.58	0.58	21.0	58.29
70.0	85.52	4.91	21.4	61.06
100.0	83.48	4.91	21.8	64.61
300.0	93.44	3.07	22.0	66.39
500.0	88.28	4.20	23.0	78.07
1000.0	66.04	2.86	23.5	83.86
1500.0	55.48	1.81	24.0	87.44
2000.0	58.00	3.29	25.0	84.33

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SXLP-21.4+](#)