

Frequency Mixer WIDE BAND

SIM-43MH+

Level 13 (LO Power +13 dBm) 824 to 4200 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
For extended temperature range, consult factory.	
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	8
RF	4
IF	2
GROUND	1,3,5,6,7


Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G
.200	.180	.087	.025	.050	.028	.043
5.08	4.57	2.2098	0.64	1.27	0.71	1.09
H	J	K	L	M	N	wt
.050	.030	.043	.204	.127	0.065	grams
1.27	0.76	1.09	5.18	3.23	1.65	0.08

Demo Board MCL P/N: TB-382 Suggested PCB Layout (PL-239)



- NOTES:
- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020 ± .0015"; COPPER: 1/2 OZ. EACH SIDE.
 - FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Features

- wide bandwidth, 824 to 4200 MHz
- low conversion loss, 6.1 dB typ.
- excellent L-R isolation, 35 dB typ.
- LTCC double balanced mixer
- tiny size, low profile, 0.08"
- useable as up and down converter
- aqueous washable
- protected by US patent 7,027,795

Applications

- cellular
- defense & weather radar
- defense communications
- PCN
- WCDMA
- WIFI
- blue tooth
- VSAT
- ISM

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f_L - f_U	IF	Typ.	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
824-4200	DC-1500								
824-2500		6.3	0.1	8.3	37	26	24	10	20
2500-4200		5.7	0.1	9.8	30	22	20	14	22


1 dB Compression: +9 dBm typ.

* Conversion loss at 30 MHz IF. σ is a measure of repeatability from unit to unit.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
750.00	780.00	7.46	39.30	22.20	2.30	8.86
825.00	855.00	6.69	35.94	23.10	1.81	4.77
900.00	930.00	6.56	35.28	23.61	1.86	3.65
975.00	1005.00	6.87	37.48	24.51	2.51	2.65
1050.00	1080.00	6.25	41.33	27.47	2.83	2.12
1125.00	1155.00	5.97	45.94	29.67	3.08	1.81
1200.00	1230.00	5.82	52.76	31.04	3.25	1.53
1275.00	1305.00	6.05	46.72	31.39	3.41	1.29
1350.00	1380.00	6.05	42.28	35.10	3.60	1.13
1425.00	1455.00	5.78	39.40	38.15	3.29	1.19
1500.00	1530.00	5.68	37.98	39.15	2.91	1.37
1800.00	1830.00	5.78	37.32	21.79	2.22	1.67
2100.00	2130.00	5.75	34.21	14.00	2.30	1.88
2400.00	2430.00	5.36	31.94	17.74	1.93	2.36
2700.00	2730.00	5.77	30.66	23.65	2.44	2.04
3000.00	3030.00	5.61	29.22	29.71	2.26	1.72
3360.00	3390.00	5.94	28.61	24.35	2.37	1.80
3540.00	3570.00	6.60	26.65	22.73	3.15	2.36
4080.00	4110.00	7.87	26.87	19.22	4.15	4.21
4260.00	4290.00	8.69	27.67	19.60	5.02	5.88

Electrical Schematic



Generic photo used for illustration purposes only

CASE STYLE: HV1195

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200, 500









Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-000060
SIM-43MH+
ED-12399/13
DJ/RS/CP/QL
200821



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SIM-43MH+](#)