

Frequency Mixer

Level 7 (LO Power +7 dBm) 1 to 2500 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded	

Pin Connections

LO	2
RF	1
IF	3
GROUND	4,5,6


Outline Drawing



Outline Dimensions ()

A	B	C	D	E	F	G	H	J	K
.38	.50	.23	.020	.075	.250	.425	.187	.050	.050
9.65	12.70	5.84	0.51	1.91	6.35	10.80	4.75	1.27	1.27
L	M	N	P	Q	R	S	T		wt.
.070	.270	.540	.060	.095	.445	.208	.415		grams
1.78	6.86	13.72	1.52	2.41	11.30	5.28	10.54		0.8

Demo Board MCL P/N: TB-12
Suggested PCB Layout (PL-079)



NOTE:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. THE USE OF SOLDER MASK IS RECOMMENDED TO PROTECT THE UNIT AS SHOWN IS RECOMMENDED TO PREVENT POTENTIAL SHORTING. IF USER CHOOSES TO EXPOSE METAL UNDER THE ENTIRE UNIT, SOLDER MASK MUST BE APPLIED UNDER EACH GROUND PAD. A SOLDER MASK DAM BE APPLIED AROUND EACH GROUND PAD TO ENSURE FILLET AND CONNECTION AT GROUND PADS.
 3. BOTTOM SIDE OF THE BOARD IS THE SOLDER PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER), SEE NOTE 2.

■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A.** Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 1 to 2500 MHz.
- low conversion loss, 6.5 dB typ.
- high L-R isolation, 50 dB typ.

Applications

- ISM/GPS
- PCS
- cellular
- satellite distribution

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)						IP3 at center band (dBm)
LO/RF f _L -f _U	IF	Mid-Band m			Total Range Max.	L		M		U		L		M		U		
		$\overline{X}$	σ	Max.		Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.			
																	Typ.	
1-2500	DC-500	6.5	.10	8.5	9.8	70	50	50	25	36	20	60	45	30	10	16	8	12


1 dB COMP: +1 dBm typ.

L = low range [f_L to 10 f_L]
M = mid band [2f_L to f_U/2]
U = upper range [f_U/2 to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
1.01	31.01	5.40	68.55	78.07	1.24	2.88
2.01	32.01	5.24	68.93	76.05	1.18	2.74
5.84	35.84	5.13	70.25	70.86	1.17	2.63
9.42	39.42	5.12	70.04	68.23	1.17	2.50
20.90	50.90	5.12	68.86	62.17	1.17	2.52
54.42	84.42	5.17	67.37	57.12	1.20	2.44
102.99	72.99	5.17	63.40	53.83	1.22	2.41
194.90	164.90	5.28	58.63	46.88	1.33	2.33
507.42	477.42	5.59	56.42	36.76	1.69	1.97
960.27	930.27	6.94	43.41	19.21	2.59	1.30
1126.30	1096.30	7.08	37.71	17.79	3.14	1.12
1250.00	1220.00	7.57	35.73	18.03	3.60	1.10
1400.00	1370.00	7.99	35.56	18.61	3.63	1.27
1549.41	1519.41	8.23	34.63	17.85	2.87	1.45
1600.00	1570.00	8.20	34.82	17.62	2.69	1.52
1800.00	1770.00	8.17	34.21	16.19	2.25	1.77
2000.00	1970.00	7.97	34.66	16.53	1.93	1.96
2200.00	2170.00	7.83	38.26	17.68	1.46	2.01
2400.00	2370.00	7.93	40.77	17.10	1.10	1.86
2500.00	2470.00	8.18	43.10	16.95	1.83	1.71

Electrical Schematic



Generic photo used for illustration purposes only

CASE STYLE: TTT167







+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SYM-2500+](#)