

Low Pass Filter

50Ω DC to 15 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- good attenuation rate, 1.35 typ. 20dB/ 3dB BW ratio
- rugged shielded case
- other SLP models available with wide selection of cut-off frequencies

Applications

- lab use
- test equipment
- video equipment

SLP-15+



Generic photo used for illustration purposes only

CASE STYLE: FF99

Connectors Model
SMA SLP-15+


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-15	17	23-32 32-200	1.7 18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
1.00	0.21	0.04	1.00	48.07
3.00	0.26	0.04	1.10	47.91
5.00	0.30	0.04	1.30	48.21
7.00	0.33	0.05	1.40	47.67
9.00	0.38	0.05	1.60	48.07
11.00	0.47	0.07	1.80	47.68
13.00	0.58	0.07	2.00	48.30
15.00	0.81	0.06	2.30	48.44
17.00	2.32	0.37	2.50	48.37
19.00	8.82	0.63	2.90	48.63
19.80	12.25	0.57	3.20	48.63
20.60	15.66	0.53	3.60	48.80
21.40	18.93	0.50	4.00	48.88
22.20	22.02	0.48	4.60	49.48
23.00	24.94	0.48	5.10	49.49
23.80	27.72	0.47	5.80	50.43
25.40	32.87	0.50	6.50	50.77
27.10	37.90	0.60	7.30	51.87
28.70	42.24	0.70	8.20	53.05
30.40	46.55	0.86	9.30	54.47
32.00	50.45	1.02	10.40	56.61
33.60	54.18	1.48	11.70	60.33
54.40	77.82	6.04	13.10	66.08
75.20	77.17	4.69	15.00	80.27
96.00	81.80	4.39	17.00	100.53
116.80	80.95	4.80	18.80	81.42
137.60	80.75	3.87	21.10	43.84
158.40	83.26	4.95	23.00	28.31
179.20	79.58	3.64	26.60	15.72
200.00	80.96	5.21	30.00	10.37



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SLP-15+](#)