

Surface Mount Frequency Mixer

Level 10 (LO Power +10 dBm) 5 to 3000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	2
RF	1
IF	3
GROUND	4,5,6


Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K
.38	.50	.23	.020	.075	.250	.425	.187	.050	.050
9.65	12.70	5.84	0.51	1.91	6.35	10.80	4.75	1.27	1.27
L	M	N	P	Q	R	S	T	wt.	
.070	.270	.540	.060	.095	.445	.208	.415	grams	
1.78	6.86	13.72	1.52	2.41	11.30	5.28	10.54	0.8	

Demo Board MCL P/N: TB-12 Suggested PCB Layout (PL-079)



NOTE:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- THE USE OF SOLDER MASK OVER THE GROUND AREA UNDER THE UNIT AS SHOWN IS RECOMMENDED TO PREVENT POTENTIAL SHORTING. IF USER CHOOSES TO EXPOSE METAL UNDER THE ENTIRE UNIT GROUND PAD FOR IMPROVED GROUNDING, IT IS RECOMMENDED A SOLDER MASK DAM BE APPLIED AROUND EACH GROUND PAD TO ENSURE FILLET AND CONNECTION AT GROUND PADS.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER). SEE NOTE 2. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 5 to 3000 MHz
- good L-R isolation, 36 dB typ.
- excellent L-I isolation, 45 dB typ.
- low conversion loss, 6.5 dB typ.

Applications

- CDMA
- GSM
- DCS
- PCN

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)						IP3* at center band (dBm)
LO/RF f_L - f_U	IF	Mid-Band _m			Total Range Max.	L	M		U		L	M		U				
		$\overline{X}$	σ	Max.			Typ.	Min.	Typ.	Min.		Typ.	Min.	Typ.	Min.	Typ.	Min.	
5-3000	5-1500	6.5	.15	8.4	9.2	36	28	37	29	33	23	41	32	45	37	47	31	19

1 dB COMP: +5 dBm typ.

*IP3 at 800-900 MHz and 1800-1900 MHz

L = low range [f_L to 10 f_L]

m = mid band [$2f_L$ to $f_U/2$]


M = mid range [$10f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm
5.10	35.11	6.58	35.88	38.87	1.13	1.62
100.10	130.11	6.53	36.17	43.33	1.08	1.61
221.15	251.16	6.50	36.39	43.27	1.13	1.60
434.31	464.32	6.51	36.54	43.55	1.26	1.57
647.47	677.48	6.40	36.89	43.37	1.43	1.53
860.63	890.64	6.55	37.21	44.80	1.62	1.50
1073.78	1103.79	6.73	38.11	47.46	1.76	1.46
1215.89	1245.90	6.36	38.74	50.49	1.80	1.44
1429.05	1459.06	6.22	38.31	55.18	1.69	1.37
1600.10	1630.11	6.19	37.88	58.14	1.50	1.33
1815.49	1845.50	6.36	35.43	54.55	1.29	1.22
2030.87	2060.88	6.80	32.79	49.03	1.27	1.13
2246.25	2276.26	7.17	31.15	51.13	1.32	1.04
2353.95	2383.96	7.26	30.54	54.00	1.27	1.01
2461.64	2491.65	7.28	30.28	53.61	1.17	1.07
2569.33	2599.34	7.27	30.13	51.62	1.03	1.15
2677.02	2707.03	7.33	30.10	48.05	1.13	1.24
2784.72	2814.73	7.43	30.14	46.47	1.29	1.33
2892.41	2922.42	7.53	30.39	43.08	1.45	1.43
3000.10	3030.11	7.67	32.41	40.55	1.57	1.51

Electrical Schematic



Generic photo used for illustration purposes only

CASE STYLE: TTT167

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost







Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M151107
SYM-30DLHW
DJ/TD/AM
200813
Page 1 of 2

Performance Charts



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[SYM-30DLHW+](#)