

# Power Splitter/Combiner syps-3-72-75+

 $75\Omega$  3 Way-0° 5 to 700 MHz

### **KEY FEATURES**

- Low Insertion Loss 0.9 dB typ.
- Good Isolation, 24 dB typ.
- Wide Frequency Band, 5 to 700 MHz, usable 5-1000 MHz
- · Low Amplitude Unbalance, 0.2 dB typ.
- · Low Phase Unbalance, 1.3 deg. typ.


## **APPLICATIONS**

- CATV
- VHF/UHF
- · Communication systems



Generic photo used for illustration purposes only

### **FUNCTIONAL DIAGRAM**



### **PRODUCT OVERVIEW**

Mini-Circuits' SYPS-3-72-75+ is a  $75\Omega$  3-way 0° surface mount splitter/combiner covering the 5 to 700 MHz frequency range, supporting bandwidth requirements for communication systems and equipment as well as other broadband applications. This model can handle up to 1W RF input power as a splitter and provides low insertion loss, high isolation, and low phase and amplitude unbalance. It comes housed in a miniature, 8-lead plastic package (0.38 x 0.50 x 0.25") with wrap-around terminations for excellent solderability and gold over nickel plate termination finish.

### **ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C**

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Units
Frequency Range		5	_	700	MHz
Insertion Loss (above 4.8 dB)	5 - 700	_	0.9	1.4	dB
Isolation	5 - 300	21	25	_	dB
	300 - 700	16	23	_	
Phase Unbalance (±)	5 - 700	_	1.3	3.0	Degree
Amplitude Unbalance (±)	5 - 700	_	0.2	0.4	dB
Return Loss (Port S)	5 - 700	18	25	_	dB
Return Loss (Port 1 and Port 2)	5 - 700	15	20	_	dB

 $<sup>1.\,</sup>Bi-directional\,can\,function\,as\,a\,splitter\,or\,as\,a\,combiner.\,Refer\,to\,S-Parameters\,for\,actual\,performance.$ 

# **ABSOLUTE MAXIMUM RATINGS<sup>2</sup>**

Operating Case Temperature		-40° C to +85° C	
Storage Temperature		-55° C to +100° C	
Input Power	as splitter	1 W	
	as combiner per port	0.33 W	
Internal Dissipation		0.15 W	

<sup>2.</sup> Permanent damage may occur if any of these limits are exceeded.

REV. A ECO-023120 SYPS-3-72-75-1 EDU4919 URJ/MCL NY 240920







# Power Splitter/Combiner syps-3-72-75+


 $75\Omega$  3 Way-0° 5 to 700 MHz

### **TYPICAL PERFORMANCE GRAPHS AT +25°C**





Total Loss = Insertion Loss + 4.8dB splitter loss.





# Power Splitter/Combiner syps-3-72-75+

 $75\Omega$  3 Way-0° 5 to 700 MHz

### **FUNCTIONAL DIAGRAM**




Figure 1. SYPS-3-72-75+ Functional Diagram

### PAD DESCRIPTION

Function	Pad Number	Description
Sum Port	8	Connects to Sum Port
Port 1	1	Connects to 1 Port
Port 2	4	Connects to 2 Port
Port 3	5	Connects to 3 Port
GROUND	2,3,6,7	Connects to Ground on PCB (See drawing PL-229)

# **SUGGESTED PCB LAYOUT (PL-229)**





Figure 2. Suggested PCB Layout PL-229

### **CASE STYLE DRAWING**



WT, GRAM: .80 Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

## **PRODUCT MARKING\*: SYPS-3-72-75**

\*Marking may contain other features or characters for internal lot control.



# Power Splitter/Combiner syps-3-72-75+

 $75\Omega$  3 Way-0° 5 to 700 MHz

### ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.

	Data		
Performance Data & Graphs	Graphs		
	S-Parameter (S4P Files) Data Set (.zip file) De-embedded to device pads		
Case Style	AH202 Lead Finish: Gold over Nickel		
RoHS Status	Compliant		
Tape and Reel	F61		
Suggested Layout for PCB Design	PL-229		
Evaluation Board	TB-SYPS-3-7275+		
Evaluation Board	Gerber File		
Environmental Rating	ENV02T1		

#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mini-Circuits:

SYPS-3-72-75+