

# Ultra Low Noise, Medium Current E-PHEMT

## 0.45-6GHz

### Product Features

- Low Noise Figure, 0.5 dB
- Gain, 17 dB at 2 GHz
- High Output IP3, +31 dBm
- Output Power at 1dB comp., +19 dBm
- Low Current, 30mA
- Wide bandwidth
- External biasing and matching required



Generic photo used for illustration purposes only

## TAV-581+

CASE STYLE: FG873

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Typical Applications

- Cellular
- ISM
- GSM
- WCDMA
- WiMax
- WLAN
- UNII and HIPERLAN

### General Description

TAV-581+ is an ultra-low noise, high IP3 transistor device, manufactured using E-PHEMT\* technology enabling it to work with a single positive supply voltage. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding base station applications. We offer these units assembled into a complete module, 50Ω in/out, noise matched and fully specified. For more information please see our TAMP family of models on our web site.

### simplified schematic and pin description



| Function | Pad Number | Description                                   |
|----------|------------|-----------------------------------------------|
| Source   | 2 & 4      | Source terminal, normally connected to ground |
| Gate     | 3          | Gate used for RF input                        |
| Drain    | 1          | Drain used for RF output                      |

\* Enhancement mode Pseudomorphic High Electron Mobility Transistor.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. C  
M151107  
ED-13285  
TAV-581+  
201016  
Page 1 of 11

Electrical Specifications at  $T_{AMB}=25^{\circ}\text{C}$ , Frequency 0.45 to 6 GHz

| Symbol                                                               | Parameter                        | Condition                                                                                                                                                                                                                        | Min.                | Typ.                                             | Max.                              | Units         |
|----------------------------------------------------------------------|----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------------------------------------------------|-----------------------------------|---------------|
| <b>DC Specifications</b>                                             |                                  |                                                                                                                                                                                                                                  |                     |                                                  |                                   |               |
| $V_{GS}$                                                             | Operational Gate Voltage         | $V_{DS}=3\text{V}$ , $I_{DS}=30\text{ mA}$                                                                                                                                                                                       | 0.28                | 0.39                                             | 0.5                               | V             |
| $V_{TH}$                                                             | Threshold Voltage                | $V_{DS}=3\text{V}$ , $I_{DS}=4\text{ mA}$                                                                                                                                                                                        | 0.18                | 0.26                                             | 0.38                              | V             |
| $I_{DSS}$                                                            | Saturated Drain Current          | $V_{DS}=3\text{V}$ , $V_{GS}=0\text{ V}$                                                                                                                                                                                         |                     | 1.0                                              | 5.0                               | $\mu\text{A}$ |
| $G_m$                                                                | Transconductance                 | $V_{DS}=3\text{V}$ , $G_m=\Delta I_{DS}/\Delta V_{GS}$<br>$\Delta V_{GS}=V_{GS1}-V_{GS2}$<br>$V_{GS1}=V_{GS}$ at $I_{DS}=30\text{ mA}$<br>$V_{GS2}=V_{GS1}+0.05\text{V}$                                                         | —<br>230<br>—<br>—  | —<br>327<br>—<br>—                               | —<br>560<br>—<br>—                | mS            |
| $I_{GSS}$                                                            | Gate leakage Current             | $V_{GD}=V_{GS}=-3\text{V}$                                                                                                                                                                                                       |                     |                                                  | 200                               | $\mu\text{A}$ |
| <b>RF Specifications, <math>Z_0=50\text{ Ohms}</math> (Figure 1)</b> |                                  |                                                                                                                                                                                                                                  |                     |                                                  |                                   |               |
| $NF^{(1)}$                                                           | Noise Figure                     | $V_{DS}=3\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$<br>$f=3.9\text{ GHz}$<br>$f=5.8\text{ GHz}$<br><br>$V_{DS}=4\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$ |                     | 0.4<br>0.5<br>0.9<br>1.5<br><br>0.4<br>0.5       | —<br>0.9<br>—<br>—<br><br>—<br>—  | dB            |
| Gain                                                                 | Gain                             | $V_{DS}=3\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$<br>$f=3.9\text{ GHz}$<br>$f=5.8\text{ GHz}$<br><br>$V_{DS}=4\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$ | —<br>15.0<br>—<br>— | 22.9<br>17.3<br>12.1<br>8.8<br><br>22.7<br>17.2  | —<br>18.5<br>—<br>—<br><br>—<br>— | dB            |
| OIP3                                                                 | Output IP3                       | $V_{DS}=3\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$<br>$f=3.9\text{ GHz}$<br>$f=5.8\text{ GHz}$<br><br>$V_{DS}=4\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$ |                     | 28.3<br>30.3<br>33.0<br>34.7<br><br>28.1<br>30.0 |                                   | dBm           |
| $P_{1dB}^{(2)}$                                                      | Power output at 1 dB Compression | $V_{DS}=3\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$<br>$f=3.9\text{ GHz}$<br>$f=5.8\text{ GHz}$<br><br>$V_{DS}=4\text{V}$ , $I_{DS}=30\text{ mA}$<br>$f=0.9\text{ GHz}$<br>$f=2.0\text{ GHz}$ |                     | 17.8<br>18.3<br>18.8<br>19.1<br><br>19.4<br>20.2 |                                   | dBm           |

Absolute Maximum Ratings<sup>(3)</sup>

| Symbol         | Parameter              | Max.       | Units                |
|----------------|------------------------|------------|----------------------|
| $V_{DS}^{(4)}$ | Drain-Source Voltage   | 5          | V                    |
| $V_{GS}^{(4)}$ | Gate-Source Voltage    | -5 to 0.7  | V                    |
| $V_{GD}^{(4)}$ | Gate-Drain Voltage     | -5 to 0.7  | V                    |
| $I_{DS}^{(4)}$ | Drain Current          | 100        | mA                   |
| $I_{GS}$       | Gate Current           | 2          | mA                   |
| $P_{DISS}$     | Total Dissipated Power | 550        | mW                   |
| $P_{IN}^{(5)}$ | RF Input Power         | 17         | dBm                  |
| $T_{CH}$       | Channel Temperature    | 150        | $^{\circ}\text{C}$   |
| $T_{OP}$       | Operating Temperature  | -40 to 85  | $^{\circ}\text{C}$   |
| $T_{STD}$      | Storage Temperature    | -65 to 150 | $^{\circ}\text{C}$   |
| $\Theta_{JC}$  | Thermal Resistance     | 112        | $^{\circ}\text{C/W}$ |

## Notes:


- (1) Includes testboard loss (measured in Mini-Circuits test board TB-154)  
(2) During Compression,  $I_{DS}$  increases to 48mA typ.  
(3) Operation of this device above any one of these parameters may cause permanent damage.  
(4) Assumes DC quiescent conditions.  
(5)  $I_{GS}$  is limited to 2 mA during test.

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Characterization Test Circuit




**Fig 1.** Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Test Board TB-154)

Gain, Output power at 1dB compression ( $P_1$  dB) and output IP3 (OIP3) are measured using R&S Network Analyzer ZVA-24. Noise Figure measured using Agilent's Noise Figure meter N8975A and noise source N4000A.

**Conditions:**

1. Drain voltage (with reference to source,  $V_{DS}$ ) = 3 or 4V as shown.
2. Gate Voltage (with reference to source,  $V_{GS}$ ) is set to obtain desired Drain-Source current ( $I_{DS}$ ) as shown in graphs or specification table.
3. Gain:  $P_{in} = -25$  dBm
4. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.
5. No external matching components used.









**Fig 2.** Test Board used for characterization, Mini-Circuits P/N TB-154 (Material: Rogers 4350, Thickness: 0.02")

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Curves









- (1) Includes test board loss, set-up and conditions per Figure 1.  
 (2) Measured using HP4155B semiconductor parameter analyzer.  
 (3) F Min is minimum Noise Figure.  
 (4) Drain current was allowed to increase during compression measurement.

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






- (1) Includes test board loss, set-up and conditions per Figure 1.  
 (2) Measured using HP4155B semiconductor parameter analyzer.  
 (3) F Min is minimum Noise Figure.  
 (4) Drain current was allowed to increase during compression measurement.

#### Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




GAIN vs FREQUENCY & TEMPERATURE (1)  
@ VDS=3V, IDS=30mA




OIP3 vs FREQUENCY & TEMPERATURE (1)  
@ VDS=3V, IDS=30mA




P1dB vs FREQUENCY & TEMPERATURE (1,4)  
@ VDS=3V, IDS=30mA




NF vs FREQUENCY & TEMPERATURE (1)  
@ VDS=4V, IDS=30mA



GAIN vs FREQUENCY & TEMPERATURE (1)  
@ VDS=4V, IDS=30mA



OIP3 vs FREQUENCY & TEMPERATURE  
@ VDS=4V, IDS=30mA





- (1) Includes test board loss, set-up and conditions per Figure 1.  
 (2) Measured using HP4155B semiconductor parameter analyzer.  
 (3) F Min is minimum Noise Figure.  
 (4) Drain current was allowed to increase during compression measurement.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





- (1) Includes test board loss, set-up and conditions per Figure 1.
- (2) Measured using HP4155B semiconductor parameter analyzer.
- (3) F Min is minimum Noise Figure.
- (4) Drain current was allowed to increase during compression measurement.

### Reference Plane Location for S and Noise Parameters *(see data in pages 8 & 9)*

*(Refer to Application Note AN-60-040)*




Fig 3. Reference Plane Location

#### Notes:

Noise parameters were measured over 0.5 to 6 GHz by Modelithics® using a solid state tuner-based NP noise parameter test system available from Maury Microwave. F Min, optimum source reflection coefficient and noise resistance values are calculated values based on a set of measurements made at approximately 16 different impedances. Some data smoothing was applied to arrive at the presented data set.

S-parameters were measured by Modelithics® on an Anritsu Lightning vector network analyzer over 0.1 to 18GHz using 350um pitch RF probes from GGB industries combined with customized thru-reflect-line (TRL) calibration standards. The reference plane is at the device package leads, as shown in the picture.

#### Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical S-parameters,  $V_{DS}=3V$  and  $I_{DS}=30\text{ mA}$  (Fig. 3)

| Freq.<br>(GHz) | S11  |         | S21   |             |        | S12   |        | S22  |         | MSG/MAG<br>(dB) |
|----------------|------|---------|-------|-------------|--------|-------|--------|------|---------|-----------------|
|                | Mag. | Ang.    | Mag.  | Mag<br>(dB) | Ang.   | Mag.  | Ang.   | Mag. | Ang.    |                 |
| 0.1            | 0.99 | -16.36  | 23.19 | 27.31       | 169.5  | 0.009 | 86.4   | 0.60 | -12.94  | 34.0            |
| 0.5            | 0.88 | -73.63  | 18.30 | 25.25       | 132.3  | 0.037 | 52.2   | 0.47 | -52.76  | 27.0            |
| 0.9            | 0.77 | -112.16 | 13.45 | 22.57       | 108.1  | 0.05  | 36.6   | 0.35 | -79.99  | 24.3            |
| 1.0            | 0.76 | -120.13 | 12.51 | 21.95       | 103.4  | 0.052 | 34.2   | 0.33 | -85.89  | 23.8            |
| 1.5            | 0.70 | -149.97 | 9.11  | 19.19       | 84.2   | 0.059 | 24.0   | 0.25 | -109.19 | 21.9            |
| 1.9            | 0.68 | -167.63 | 7.42  | 17.41       | 72.0   | 0.063 | 19.5   | 0.21 | -124.99 | 20.7            |
| 2.0            | 0.68 | -171.42 | 7.09  | 17.02       | 69.3   | 0.065 | 18.2   | 0.20 | -128.70 | 20.4            |
| 2.5            | 0.67 | -171.27 | 5.80  | 15.27       | 56.2   | 0.07  | 13.5   | 0.17 | -146.31 | 19.2            |
| 3.0            | 0.66 | -156.22 | 4.90  | 13.80       | 44.0   | 0.075 | 8.8    | 0.15 | -163.82 | 18.1            |
| 4.0            | 0.67 | -130.42 | 3.73  | 11.43       | 21.4   | 0.087 | -0.3   | 0.13 | -161.15 | 16.0            |
| 5.0            | 0.68 | -107.77 | 3.02  | 9.59        | 0.0    | 0.099 | -10.8  | 0.14 | -127.97 | 13.2            |
| 6.0            | 0.70 | -86.82  | 2.53  | 8.06        | -20.8  | 0.113 | -22.5  | 0.16 | -98.63  | 11.7            |
| 7.0            | 0.73 | -66.89  | 2.17  | 6.71        | -41.4  | 0.125 | -35.2  | 0.20 | -74.15  | 10.6            |
| 8.0            | 0.75 | -47.68  | 1.88  | 5.49        | -61.7  | 0.136 | -48.6  | 0.26 | -53.20  | 9.7             |
| 9.0            | 0.79 | -28.73  | 1.63  | 4.27        | -81.9  | 0.145 | -63.3  | 0.32 | -34.25  | 9.1             |
| 10.0           | 0.83 | -9.67   | 1.42  | 3.04        | -102.2 | 0.15  | -78.4  | 0.39 | -16.29  | 8.8             |
| 11.0           | 0.86 | -8.89   | 1.23  | 1.77        | -122.3 | 0.151 | -94.0  | 0.47 | -0.68   | 9.1             |
| 12.0           | 0.89 | -26.76  | 1.06  | 0.47        | -142.1 | 0.15  | -109.6 | 0.54 | -17.06  | 8.5             |
| 13.0           | 0.91 | -44.42  | 0.91  | -0.86       | -162.0 | 0.146 | -125.5 | 0.59 | -33.39  | 7.9             |
| 14.0           | 0.93 | -60.99  | 0.77  | -2.25       | -178.8 | 0.139 | -140.9 | 0.65 | -49.07  | 7.5             |
| 15.0           | 0.94 | -73.61  | 0.66  | -3.64       | -163.1 | 0.131 | -153.9 | 0.70 | -61.42  | 7.0             |
| 16.0           | 0.96 | -83.75  | 0.56  | -5.10       | -149.1 | 0.119 | -163.5 | 0.74 | -72.07  | 6.7             |
| 17.0           | 0.96 | -94.86  | 0.47  | -6.51       | -134.2 | 0.109 | -174.6 | 0.77 | -83.99  | 6.4             |
| 18.0           | 0.95 | -106.68 | 0.40  | -7.98       | -118.5 | 0.101 | -174.5 | 0.80 | -97.27  | 6.0             |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE GAIN (MAG) vs. FREQUENCY

Typical Noise Parameters,  $V_{DS}=3V$  and  $I_{DS}=30\text{ mA}$  (Fig. 3)

| Freq.<br>(GHz) | F Min.<br>(dB) | $\Gamma^{Opt}$<br>(Magnitude) | $\Gamma^{Opt}$<br>(Angle) | Rn/50 | Ga<br>Associated<br>Gain (dB) |
|----------------|----------------|-------------------------------|---------------------------|-------|-------------------------------|
| 0.5            | 0.09           | 0.33                          | 16.30                     | 0.07  | 26.6                          |
| 0.7            | 0.12           | 0.33                          | 28.96                     | 0.07  | 24.7                          |
| 0.9            | 0.16           | 0.34                          | 41.34                     | 0.06  | 23.1                          |
| 1.0            | 0.18           | 0.35                          | 47.42                     | 0.06  | 22.4                          |
| 1.9            | 0.34           | 0.38                          | 99.05                     | 0.03  | 17.8                          |
| 2.0            | 0.36           | 0.39                          | 104.44                    | 0.03  | 17.5                          |
| 2.4            | 0.43           | 0.40                          | 125.31                    | 0.03  | 16.3                          |
| 3.0            | 0.54           | 0.42                          | 154.52                    | 0.03  | 14.9                          |
| 3.9            | 0.70           | 0.44                          | -166.36                   | 0.06  | 13.3                          |
| 5.0            | 0.89           | 0.46                          | -126.19                   | 0.11  | 11.8                          |
| 5.8            | 1.04           | 0.47                          | -102.25                   | 0.16  | 10.7                          |
| 6.0            | 1.07           | 0.47                          | -96.96                    | 0.18  | 10.5                          |

## Notes:

F Min.: Minimum Noise Figure  
 $\Gamma^{Opt}$ : Optimum Source Reflection Coefficient  
 Rn: Equivalent noise resistance

## Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





Typical S-parameters,  $V_{DS}=4V$  and  $I_{DS}=30\text{ mA}$  (Fig. 3)

| Freq.<br>(GHz) | S11  |         | S21   |             |        | S12   |        | S22  |         | MSG/MAG<br>(dB) |
|----------------|------|---------|-------|-------------|--------|-------|--------|------|---------|-----------------|
|                | Mag. | Ang.    | Mag.  | Mag<br>(dB) | Ang.   | Mag.  | Ang.   | Mag. | Ang.    |                 |
| 0.1            | 0.99 | -16.62  | 23.16 | 27.30       | 169.5  | 0.009 | 79.4   | 0.61 | -12.06  | 34.0            |
| 0.5            | 0.88 | -73.31  | 18.36 | 25.28       | 132.5  | 0.036 | 52.2   | 0.49 | -50.89  | 27.0            |
| 0.9            | 0.77 | -111.77 | 13.51 | 22.61       | 108.3  | 0.049 | 37.1   | 0.36 | -76.91  | 24.4            |
| 1.0            | 0.76 | -119.67 | 12.58 | 21.99       | 103.5  | 0.051 | 33.7   | 0.34 | -82.55  | 23.9            |
| 1.5            | 0.70 | -149.65 | 9.17  | 19.25       | 84.3   | 0.058 | 24.1   | 0.25 | -104.45 | 22.0            |
| 1.9            | 0.68 | -167.34 | 7.47  | 17.47       | 72.1   | 0.062 | 19.2   | 0.21 | -119.17 | 20.8            |
| 2.0            | 0.67 | -171.13 | 7.14  | 17.07       | 69.3   | 0.063 | 18.4   | 0.20 | -122.66 | 20.5            |
| 2.5            | 0.67 | 171.46  | 5.84  | 15.33       | 56.2   | 0.069 | 13.6   | 0.17 | -139.21 | 19.3            |
| 3.0            | 0.66 | 156.41  | 4.93  | 13.86       | 44.0   | 0.074 | 9.0    | 0.14 | -155.97 | 18.2            |
| 4.0            | 0.67 | 130.52  | 3.75  | 11.49       | 21.4   | 0.085 | 0.0    | 0.12 | -169.62 | 15.9            |
| 5.0            | 0.68 | 107.77  | 3.04  | 9.66        | -0.1   | 0.098 | -10.3  | 0.12 | -134.56 | 13.3            |
| 6.0            | 0.70 | 86.77   | 2.55  | 8.14        | -20.9  | 0.111 | -21.6  | 0.14 | -103.32 | 11.8            |
| 7.0            | 0.72 | 66.87   | 2.19  | 6.79        | -41.6  | 0.123 | -34.4  | 0.18 | -77.45  | 10.7            |
| 8.0            | 0.75 | 47.72   | 1.90  | 5.58        | -61.9  | 0.135 | -47.6  | 0.24 | -55.67  | 9.8             |
| 9.0            | 0.79 | 28.73   | 1.65  | 4.37        | -82.2  | 0.144 | -62.3  | 0.30 | -36.33  | 9.3             |
| 10.0           | 0.83 | 9.64    | 1.44  | 3.15        | -102.6 | 0.15  | -77.4  | 0.38 | -18.12  | 9.1             |
| 11.0           | 0.86 | -8.92   | 1.24  | 1.89        | -122.9 | 0.152 | -93.0  | 0.45 | 0.90    | 9.1             |
| 12.0           | 0.89 | -26.90  | 1.07  | 0.60        | -142.8 | 0.151 | -108.5 | 0.52 | -15.63  | 8.5             |
| 13.0           | 0.91 | -44.62  | 0.92  | -0.73       | -162.9 | 0.147 | -124.8 | 0.58 | -32.08  | 8.0             |
| 14.0           | 0.93 | -61.40  | 0.78  | -2.11       | -177.7 | 0.14  | -140.4 | 0.64 | -47.96  | 7.5             |
| 15.0           | 0.94 | -74.24  | 0.67  | -3.52       | -161.7 | 0.132 | -153.4 | 0.69 | -60.57  | 7.0             |
| 16.0           | 0.96 | -84.49  | 0.56  | -4.99       | -147.6 | 0.121 | -163.2 | 0.74 | -71.29  | 6.7             |
| 17.0           | 0.96 | -95.82  | 0.48  | -6.42       | -132.4 | 0.111 | -174.6 | 0.77 | -83.45  | 6.4             |
| 18.0           | 0.96 | -107.81 | 0.40  | -7.93       | -116.4 | 0.102 | -174.8 | 0.80 | -96.97  | 5.9             |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE  
GAIN (MAG) vs. FREQUENCYTypical Noise Parameters,  $V_{DS}=4V$  and  $I_{DS}=30\text{ mA}$  (Fig. 3)

| Freq.<br>(GHz) | F Min.<br>(dB) | $\Gamma^{Opt}$<br>(Magnitude) | $\Gamma^{Opt}$<br>(Angle) | Rn/50 | Ga<br>Associated<br>Gain (dB) |
|----------------|----------------|-------------------------------|---------------------------|-------|-------------------------------|
| 0.5            | 0.09           | 0.37                          | 16.12                     | 0.08  | 26.6                          |
| 0.7            | 0.12           | 0.37                          | 28.50                     | 0.07  | 24.6                          |
| 0.9            | 0.16           | 0.37                          | 40.63                     | 0.06  | 23.0                          |
| 1.0            | 0.18           | 0.37                          | 46.59                     | 0.06  | 22.3                          |
| 1.9            | 0.34           | 0.39                          | 97.42                     | 0.03  | 17.8                          |
| 2.0            | 0.35           | 0.39                          | 102.75                    | 0.03  | 17.4                          |
| 2.4            | 0.42           | 0.40                          | 123.43                    | 0.03  | 16.3                          |
| 3.0            | 0.53           | 0.41                          | 152.52                    | 0.03  | 14.9                          |
| 3.9            | 0.69           | 0.43                          | -168.14                   | 0.05  | 13.3                          |
| 5.0            | 0.89           | 0.45                          | -127.09                   | 0.10  | 11.8                          |
| 5.8            | 1.03           | 0.46                          | -102.09                   | 0.16  | 10.8                          |
| 6.0            | 1.06           | 0.47                          | -96.48                    | 0.18  | 10.6                          |


Notes:  
 F Min.: Minimum Noise Figure  
 $\Gamma^{Opt}$ : Optimum Source Reflection Coefficient  
 Rn: Equivalent noise resistance

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Product Marking



### Additional Detailed Technical Information

Additional information is available on our web site [www.minicircuits.com](http://www.minicircuits.com). To access this information enter the model number on our web site home page.

#### Performance data, graphs, s-parameter data set (.zip file)

#### Case Style: FG873

Plastic low profile 3mm x 3mm, lead finish: tin/silver/nickel

#### Suggested Layout for PCB Design: PL-301

#### Tape & Reel: F68

#### Characterization Test Board: TB-154+

#### Environmental Ratings: ENV08T2

## ESD Rating


Human Body Model (HBM): Class 1A (250 V to < 500 V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (40 V) in accordance with ANSI/ESD STM 5.2 - 1999

## MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020D

### MSL Test Flow Chart




#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Recommended Application Circuit



| VDS, V (nom)  | 3         | 4         |
|---------------|-----------|-----------|
| IDS, mA (nom) | 30mA      | 30mA      |
| R1            | 4320Ω     | 4320Ω     |
| R2            | 4320Ω     | 4320Ω     |
| R3            | 3570Ω     | 1210Ω     |
| R4            | 68.1Ω     | 33.2Ω     |
| Q1            | MMBT3906* | MMBT3906* |
| Q2            | MMBT3906* | MMBT3906* |
| C1            | 0.01μF    | 0.01μF    |
| C2            | 0.01μF    | 0.01μF    |
| L1**          | 840nH     | 840nH     |
| L2**          | 840nH     | 840nH     |

\* Fairchild Semiconductor™ part number

\*\* Piconics™ part number CC45T47K240G5

## Optimized Amplifier Circuits

For band specific, drop-in modules, and as an alternative to designing circuits, please refer to Mini-Circuits TAMP and RAMP series models which are based upon SAV/TAV E-PHEMT's and include all DC blocking, bias, matching and stabilization circuitry, without need for any external components.

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[TAV-581+](#)