



Mini-Circuits

ULTRA-HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier


TSS-13HLN+

50Ω

1 MHz to 1 GHz

THE BIG DEAL

- Ultra-High IP3, +42.9 dBm typ.
- Gain, 23 dB typ. at 0.5 GHz
- Medium power, +28.4 dBm typ.
- Excellent Noise Figure, 1.4 dB typ.
- Shutdown feature
- Suitable for low phase noise applications



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- CATV
- Cellular

PRODUCT OVERVIEW

TSS-13HLN+ (RoHS compliant) is an advanced wideband amplifier with shutdown feature. It is fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the TSS-13HLN+ has good input and output return loss over a broad frequency range. TSS-13HLN+ is enclosed in a 3x3mm, 12-lead MCLP package and has very good thermal performance.

KEY FEATURES

Feature	Advantages
Broad Band: 1 MHz to 1 GHz	Broadband covering primary wireless communications bands: VHF, UHF, Cellular
Extremely High IP3 +40.6 dBm typical at 1 MHz +42.9 dBm typical at 0.5 GHz	The TSS-13HLN+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being approximately 14-15 dB above the P1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra-High Dynamic range receivers
Shutdown feature	Allow users to turn on and off the amplifier with pulsed signals while keeping the power supply at constant voltage to minimize DC power consumption
Low Noise Figure 1.4 dB at 0.5 GHz	Enables lower system noise figure performance and along with High OIP3 provides high dynamic range
High P1dB, +28.4 dBm at 0.5 GHz	High P1dB, High OIP3, Low NF results in a very dynamic range preventing amplifier saturation under strong interfering signals.
Low additive phase noise, typically -162 dBc/Hz @10 KHz offset	Ideal for low phase noise synthesizer applications





Mini-Circuits®

ULTRA-HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-13HLN+

50Ω 1 MHz to 1 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C & 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	Vd = +8V		Vd = +5V		Vd = +3V		Units
		ON State	OFF State	ON State	OFF State	ON State	OFF State	
Frequency Range		1-1000	1-1000	1-1000	1-1000	1-1000	1-1000	MHz
Noise Figure	1	3	—	3.1	—	3	—	dB
	20	1.4	—	1.1	—	1.1	—	
	250	1.3	—	1.1	—	1.1	—	
	500	1.4	—	1.1	—	1.1	—	
	1000	1.6	—	1.2	—	1.3	—	
Additive Phase Noise 1.0 GHz, 10KHz offset		-162						dBc/Hz
Gain	1	25	-24	24.7	-24	23.9	-24	dB
	20	24.4	-22	24.2	-21	23.5	-22	
	250	23.2	-21	23	-21	22.3	-21	
	500	23	-22	22.8	-22	21.9	-22	
	1000	21.1	-26	20.9	-27	19.5	-27	
Reversed Isolation	1-1000	26	27	26	27	26	27	dB
Input Return Loss	1	11	12	11	12	10	12	dB
	20	16	12	15	12	15	12	
	250	17	12	18	12	19	12	
	500	20	12	21	12	17	12	
	1000	14	10	14	10	10	10	
Output Return Loss	1	11	1	11	1	11	1	dB
	20	19	2	19	2	21	2	
	250	18	2	18	2	21	2	
	500	33	2	25	2	21	2	
	1000	12	2	11	2	10	2	
Output Power @1dB compression AMP-ON	1	25.2	--	+20.3	--	+14.2	--	dBm
	20	26.7	--	+22.4	--	+16.3	--	
	250	28	--	+24.1	--	+19.3	--	
	500	28.4	--	+24.5	--	+19.5	--	
	1000	26.7	--	+23.4	--	+18.3	--	
Output IP3 (Pout = 0dBm/Tone)	1	40.6	--	+38.4	--	+31.6	--	dBm
	20	41.3	--	+40.3	--	+33.2	--	
	250	41.2	--	+39.6	--	+34.4	--	
	500	42.9	--	+39.2	--	+33	--	
	1000	40.8	--	+36.2	--	+29.4	--	
Device Operating Voltage(VDD)		+8	+8	+5	+5	+3	+3	V
Device Operating Current(ID) ⁴		234	7.5	142	5	72	3	mA
Control Voltage (VG)		0	+5	0	+5	0	+5	V
Device Current Variation vs. Temperature ³		-136	--	10	--	33	--	uA/degC
Device Current Variation vs. Voltage		0.025	--	0.025	--	0.033	--	mA/mV
Thermal Resistance		23.3	--	23.3	--	23.3	--	degC/W

1. Measured on Mini-Circuits Characterization test board TB-TSS-13HLN+. See Characterization Test Circuit (Fig. 1)

2. (Current at 95°C — Current at -45°C)/140

ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +95°C
Storage Temperature	-65°C to +150°C
Total Power Dissipation	3.3W
Input Power	+28 dBm (5 minutes max.) +10 dBm (continuous) for 1- 30 MHz +18 dBm (continuous) for 0.03-1 GHz
DC Voltage V _{DD} ⁴ (Pad 7)	+10 V
DC Voltage V _G ⁵ (Pad 1)	+10 V

3 Permanent damage may occur if these limits are exceeded.

4 Measured by keeping VG=0V.

5 Measured by keeping Vdd=8V.

CONTROL VOLTAGE (V_G) FIG. 1

	Min.	Typ.	Max.	Units
Amplifier-ON	—	0	0.7	V
Amplifier-OFF	1.9	5	—	V





Mini-Circuits

ULTRA-HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier



TSS-13HLN+

50Ω 1 MHz to 1 GHz

SWITCHING SPECIFICATIONS

Parameter		Min.	Typ.	Max.	Units
Amplifier ON to Shutdown	OFF TIME (50% Control to 10% RF)	—	5.3	—	μs
	FALL TIME (90 to 10% RF)	—	7.3	—	
Amplifier Shutdown to ON	ON TIME (50% Control to 90% RF)	—	77.7	—	μs
	RISE TIME (10% to 90% RF)	—	54.2	—	
Control Voltage Leakage		—	633.3	—	mV

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	3	RF Input
RF-OUT and DC-IN	7	RF Output and DC Bias
GND	Paddle	Connections to ground.
NC	2, 4-6, 8-12	No connection, grounded externally
VG	1	Control voltage for shutdown (VG)



Mini-Circuits

ULTRA-HIGH DYNAMIC RANGE, SHUTDOWN


Monolithic Amplifier

TSS-13HLN+

50Ω

1 MHz to 1 GHz

CHARACTERIZATION TEST CIRCUIT / RECOMMENDED APPLICATION CIRCUIT



Component	Size	Value	Part Number	Manufacturer
C1	0402	0.1uF	GRM155R71C104KA88D	Murata
C2	0402	1.5pF	GRM1555C1H1R5CA1D	Murata
C3	0603	2.2uF	GRM188C71E225KE11D	Murata
C4	0402	0.1uF	GRM155R71C104KA88D	Murata
C5	0603	2.2uF	GRM188C71E225KE11D	Murata
C6	0402	1000pF	GRM1555C1H102JA01D	Murata
C7	0805	10uF	GRM21BC71E106KE11L	Murata
L1	1210	15uH	LQH32DN150K53L	Murata
L2	0603	5.1nH	0603CS-5N1XJLU	Coilcraft
R1	0402	1.5KOhm	RK73H1ETTP1501F	Koa

Fig 1. Block diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-TSS-13LN+)

Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return Loss: $P_{IN} = -25\text{dBm}$
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +0dBm/tone at output.
3. Switching Time
RF Signal: $P_{IN} = -25\text{ dBm}$, $f_{RF} = 500\text{ MHz}$.
 $V_{DD} = 8\text{V DC}$, $V_G = \text{Pulse signal at } 1\text{ KHz with } V_{HIGH} = 5\text{V}, V_{LOW} = 0\text{V}, 50\% \text{ duty cycle.}$

PRODUCT MARKING



Marking may contain other features or characters for internal lot control





Mini-Circuits

ULTRA-HIGH DYNAMIC RANGE, SHUTDOWN

Monolithic Amplifier

TSS-13HLN+

50Ω 1 MHz to 1 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: Matte-Tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices
Suggested Layout for PCB Design	PL-623
Evaluation Board	TB-TSS-13HLN+
Environmental Ratings	ENV08T9

ESD RATING

Human Body Model (HBM): Class 1A (Pass 250 V) in accordance with ANSI/ESD STM 5.1 - 2001

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[TSS-13HLN+](#)