

Coaxial

N-Type Fixed Attenuator

50Ω 1W 4dB DC to 6000 MHz

UNAT-4+

Maximum Ratings

Operating Temperature -45°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Features

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- off-the-shelf availability
- very low cost

Applications

- impedance matching
- signal level adjustment



Generic photo used for illustration purposes only


CASE STYLE: FF779

Connectors	Model
N-Type	UNAT-4+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch/mm)

B	D	E	wt
.68	2.11	.718	grams
17.27	53.59	18.24	72.5

Electrical Specifications



FREQ. RANGE (MHz)	ATTENUATION * (dB) Flatness **						VSWR (:1)					MAX. INPUT POWER (W)
	DC-3 GHz		3-4.5 GHz	4.5-6 GHz		DC-6 GHz	DC-3 GHz		3-4.5 GHz	4.5-6 GHz		
	Nom.	Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	
DC-6000	4±0.3	0.15	0.15	0.10	0.40		1.05	1.20	1.10	1.43	1.50	1.0

* Attenuation varies by 0.3 dB max. over temperature.

** Flatness= variation over band divided by 2.

Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10	4.00	1.00
50	4.02	1.01
100	4.04	1.01
500	4.07	1.03
1000	4.10	1.04
1600	4.17	1.04
2000	4.19	1.03
2500	4.22	1.02
3000	4.26	1.04
3500	4.32	1.07
4000	4.35	1.12
4500	4.39	1.18
5000	4.47	1.27
5500	4.55	1.42
6000	4.62	1.63



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
 M151107
 ED-10269
 UNAT-4+
 UR/LC/CP/AM
 200522
 Page 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[UNAT-4+](#)