

High Pass Filter

50Ω 6300 to 15000 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input* 7W max. at 25°C

*Passband rating, derate linearly to 3W at 100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged uni-body construction, small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Low cost

Applications

- Point to point radio
- Sub-harmonic rejection and DC blocking
- Transmitters/Receivers
- Lab use

VHF-6010+




CASE STYLE: FF704

Connectors	Model
SMA	VHF-6010+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10


High Pass Filter Electrical Specifications (T_{AMB} = 25°C)

STOPBAND (MHz)		fco, MHz	PASSBAND (MHz)		VSWR		NO. OF SECTIONS
(Loss>30dB)	(Loss>20dB)	Nom.	(Loss<3dB)	(Loss<5dB)	Typ.	Frequency	
Typ. DC-F1	Min. DC-F2	Typ. F3	Max. F4-F5	Max.	Stopband	1.5:1	
DC-5190	DC-5200	6010	6350-13000	6300-15000	20:1	6050-8000	5

Typical frequency response





Electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	66.62	868.59
500	44.39	868.59
1000	38.81	579.06
2000	35.11	173.72
5190	34.48	48.85
5200	35.02	52.33
5500	22.93	27.59
5725	11.59	12.35
5870	6.09	5.58
6010	2.78	2.42
6050	2.21	1.98
6300	1.12	1.31
6350	1.05	1.37
8000	1.03	1.95
10000	1.28	2.32
13000	1.20	2.07
15000	2.58	3.80



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[VHF-6010+](#)