

Coaxial


Low Pass Filter

VLFX-1350+

50Ω DC to 1350 MHz (30 dB Typ. Isolation up to 20 GHz)

The Big Deal

- Very good rejection, 30 dB typ. up to 20 GHz
- Excellent power handling, 10W
- Rugged unibody construction



Generic photo used for illustration purposes only
CASE STYLE: FF1118

Product Overview

VLFX-1350+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-1350 MHz bandwidth, these units offer good matching within the passband and high rejection in stopband, 30 dB typical up to 20 GHz. This will find its applications in harmonic rejection, transmitters / receivers and test instrumentation.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application
Fast roll-off	Provides very good adjacent band rejection
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Pass Filter

VLFX-1350+

50Ω DC to 1350 MHz (30 dB Typ. Isolation up to 20 GHz)



Generic photo used for illustration purposes only

CASE STYLE: FF1118

Connectors

Model

SMA

VLFX-1350+

Features

- Very good isolation, 30 dB typ. up to 20 GHz
- Excellent power handling, 10W
- Temperature stable LTCC internal structure
- Re-entry frequency > 20 GHz
- Protected by US patent 6,943,646
- Rugged unibody construction

Applications

- Harmonic rejection
- Transmitters/receivers
- Lab use
- Test instrumentation

Electrical Specifications⁽¹⁾ at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC-1350	—	1.3	2.0 dB
	Freq. Cut-Off	F2	2050	—	3.0	dB
	VSWR	DC-F1	DC-1350	—	1.4	:1
Stop Band	Insertion Loss	F3	2425	20	30	dB
		F4-F5	2600-20000	—	30	dB
	VSWR	F3-F5	2425-20000	—	10	:1


(1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required.

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max.

*Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.07	1.02
100	0.16	1.05
1000	0.75	1.42
1350	1.16	1.72
2050	2.53	1.46
2100	3.37	1.77
2125	4.07	2.04
2200	8.10	3.74
2300	19.29	8.20
2345	27.00	10.36
2395	38.13	12.61
2425	38.49	13.92
2600	40.05	20.90
5000	84.21	37.21
7500	63.06	35.46
10000	88.83	54.12
12500	63.02	17.76
15000	52.14	2.80
19000	32.39	14.56
20000	62.42	20.41

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

INPUT	SMA-Male
OUTPUT	SMA-Female

Outline Drawing



Outline Dimensions (^{inch}_{mm})

B	D	E	wt.
.410	2.67	.312	grams
10.41	67.82	7.92	17.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[VLFX-1350+](#)