

# Power Splitter/Combiner

4 Way-0° 50Ω 1300 to 2000 MHz

WP4G1+



Generic photo used for illustration purposes only  
CASE STYLE: DQ1225


## Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -40°C to 85°C  |
| Storage Temperature                                             | -65°C to 150°C |
| Power Input (as a splitter)                                     | 1.5W max.      |
| Internal Dissipation                                            | 0.375W max.    |
| Permanent damage may occur if any of these limits are exceeded. |                |


## Pad Connections

|          |                        |
|----------|------------------------|
| SUM PORT | 2                      |
| PORT 1   | 12                     |
| PORT 2   | 10                     |
| PORT 3   | 6                      |
| PORT 4   | 4                      |
| GROUND   | 1,3,5,7,8,9,11, paddle |

## Product Marking




## Outline Drawing



## Outline Dimensions (inch/mm)

| A    | B    | C    | D    | E    | F    | G    | H     | J    |
|------|------|------|------|------|------|------|-------|------|
| .118 | .118 | .035 | .008 | .057 | .057 | .009 | ---   | .016 |
| 3.00 | 3.00 | 0.89 | 0.20 | 1.45 | 1.45 | 0.23 | ---   | 0.41 |
| K    | L    | M    | N    | P    | Q    | R    | wt    |      |
| .020 | .127 | .127 | .049 | .010 | .020 | .049 | grams |      |
| 0.51 | 3.23 | 3.23 | 1.24 | 0.25 | 0.51 | 1.24 | 0.02  |      |

## Demo Board MCL P/N: TB-395+ Suggested PCB Layout (PL-259)



### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- SIGNAL TRACES ARE NOT ALLOWED INSIDE HATCHED AREAS (APPROX. .030 X .030) AT 4 PLACES AS SHOWN.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

## Features

- excellent isolation, 26 dB typ.
- excellent phase unbalance 1 deg. typ.
- excellent amplitude unbalance, 0.25 dB typ.
- small size, .118" x .118" x .035"
- high ESD level
- aqueous washable

## Applications

- GPS
- PCS
- DCS
- WCDMA

## Electrical Specifications




| FREQ. RANGE (MHz) | ISOLATION (dB) |      | INSERTION LOSS* (dB) ABOVE 6.0 dB |      | PHASE UNBALANCE (Degrees) | AMPLITUDE UNBALANCE (dB) | VSWR (:1) Typ. |               |
|-------------------|----------------|------|-----------------------------------|------|---------------------------|--------------------------|----------------|---------------|
| $f_L$ - $f_U$     | Typ.           | Min. | Typ.                              | Max. | Max.                      | Max.                     | Port S         | Ports 1,2,3,4 |
| 1300-2000         | 26             | 14   | 0.8                               | 1.9  | 5                         | 0.5                      | 1.5            | 1.4           |

\* Includes fixture loss, 0.12 dB typ.

## Typical Performance Data

| Freq. (MHz) | Total Loss <sup>1</sup> (dB) |      |      |      | Amp. Unbal. (dB) | Isolation (dB) |       |       | Phase Unbal. (deg.) | VSWR S | VSWR 1 | VSWR 2 | VSWR 3 | VSWR 4 |
|-------------|------------------------------|------|------|------|------------------|----------------|-------|-------|---------------------|--------|--------|--------|--------|--------|
|             | S-1                          | S-2  | S-3  | S-4  |                  | 1-2            | 2-3   | 3-4   |                     |        |        |        |        |        |
| 1300.00     | 7.18                         | 7.31 | 7.24 | 7.11 | 0.20             | 26.81          | 23.73 | 27.28 | 1.41                | 1.79   | 1.58   | 1.55   | 1.53   | 1.54   |
| 1360.00     | 6.94                         | 7.05 | 6.98 | 6.86 | 0.19             | 30.94          | 26.53 | 31.87 | 1.19                | 1.53   | 1.54   | 1.51   | 1.49   | 1.50   |
| 1400.00     | 6.82                         | 6.93 | 6.86 | 6.75 | 0.18             | 33.52          | 28.41 | 34.73 | 1.03                | 1.39   | 1.52   | 1.48   | 1.46   | 1.48   |
| 1450.00     | 6.72                         | 6.82 | 6.75 | 6.65 | 0.17             | 33.24          | 29.81 | 33.68 | 0.88                | 1.25   | 1.49   | 1.45   | 1.43   | 1.45   |
| 1500.00     | 6.66                         | 6.75 | 6.68 | 6.59 | 0.16             | 30.25          | 29.21 | 30.14 | 0.87                | 1.16   | 1.47   | 1.43   | 1.41   | 1.43   |
| 1550.00     | 6.63                         | 6.71 | 6.64 | 6.56 | 0.15             | 27.52          | 27.41 | 27.30 | 0.92                | 1.15   | 1.45   | 1.41   | 1.39   | 1.41   |
| 1570.00     | 6.63                         | 6.70 | 6.63 | 6.55 | 0.15             | 26.62          | 26.63 | 26.39 | 0.92                | 1.17   | 1.45   | 1.40   | 1.38   | 1.41   |
| 1580.00     | 6.63                         | 6.70 | 6.63 | 6.55 | 0.14             | 26.21          | 26.25 | 25.97 | 0.93                | 1.18   | 1.44   | 1.39   | 1.37   | 1.41   |
| 1590.00     | 6.62                         | 6.69 | 6.62 | 6.55 | 0.14             | 25.82          | 25.89 | 25.57 | 0.93                | 1.20   | 1.44   | 1.39   | 1.37   | 1.40   |
| 1600.00     | 6.63                         | 6.69 | 6.62 | 6.55 | 0.14             | 25.45          | 25.52 | 25.20 | 0.95                | 1.21   | 1.44   | 1.39   | 1.36   | 1.40   |
| 1650.00     | 6.64                         | 6.70 | 6.63 | 6.57 | 0.13             | 23.85          | 23.90 | 23.60 | 1.14                | 1.29   | 1.43   | 1.37   | 1.35   | 1.39   |
| 1700.00     | 6.67                         | 6.71 | 6.65 | 6.60 | 0.12             | 22.59          | 22.54 | 22.35 | 1.36                | 1.38   | 1.43   | 1.36   | 1.34   | 1.39   |
| 1800.00     | 6.75                         | 6.77 | 6.71 | 6.68 | 0.09             | 20.73          | 20.47 | 20.50 | 1.73                | 1.57   | 1.42   | 1.35   | 1.33   | 1.39   |
| 1900.00     | 6.85                         | 6.85 | 6.79 | 6.78 | 0.07             | 19.44          | 18.96 | 19.22 | 2.09                | 1.74   | 1.43   | 1.35   | 1.32   | 1.39   |
| 2000.00     | 6.95                         | 6.94 | 6.87 | 6.89 | 0.08             | 18.50          | 17.82 | 18.27 | 2.40                | 1.90   | 1.44   | 1.35   | 1.33   | 1.40   |

1. Total Loss = Insertion Loss + 6dB splitter loss.



## electrical schematic



## ESD Rating

Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with ANSI/ESD STM 5.1 - 2001  
Machine Model (MM): Class M2 (100V to < 250V) in accordance with ANSI/ESD STM 5.2 - 1999



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[WP4G1+](#)