

Diplexer

ZDPLX-2150-S+

50Ω DC-2150 MHz
(DC-10, 50-2150 MHz)



Generic photo used for illustration purposes only
CASE STYLE: FL905

The Big Deal

- Low insertion loss
- High Rejection
- Connectorized package

Product Overview

ZDPLX-2150-S+ is a low-pass + high-pass combination device. Low pass port is designed for DC to 10 MHz and high pass port is designed for 50 to 2150 MHz. This diplexer is used in satellite, CATV, set-top box, modem, video equipment and multiband radio systems.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
Extended stopband rejection	Spurious rejection and eliminates usage of additional filtering
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Diplexer

50Ω DC to 2150 MHz (DC-10, 50-2150 MHz)

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Voltage at DC Port	25V max.
Input Current	100 mA
RF Power Input	400 mW

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

HIGH PASS PORT	1
LOW PASS PORT	2
COMMON PORT	3

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37
H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0

Note: Please refer to case style drawing for details.

Features

- Low insertion loss
- 50Ω Impedance
- Combination of low pass and high pass filters
- Connectorized package

Applications

- Set-top box
- Satellite
- CATV

ZDPLX-2150-S+



Generic photo used for illustration purposes only

CASE STYLE: FL905

Connectors	Model
SMA	ZDPLX-2150-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	Low Pass	DC-10	-	0.5	1
		High Pass	50-2150	-	0.9	1.5
	Return Loss	Low Pass	DC-10	16	29	-
		High Pass	50-2150	12	16	-
		Common	DC-10	16	23	-
		Common	50-2150	12	20	-
Stop Band Isolation	Low Pass	40-2200	20	31	-	dB
		50-2150	30	44	-	dB
	High Pass	DC-18	20	33	-	dB
		DC-10	30	61	-	dB

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)			Return Loss (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
1	0.31	107.59	28.63	28.90	0.00
10	0.45	61.63	26.43	33.04	0.12
18	0.79	32.85	22.37	20.33	0.58
23	1.77	21.71	10.45	9.59	1.64
26	3.43	14.34	7.69	5.97	3.94
29	8.90	4.15	11.57	2.26	15.11
34	20.66	1.43	19.41	0.70	17.65
40	30.59	0.87	22.62	0.45	21.32
50	44.17	0.53	29.02	0.30	25.28
60	57.24	0.39	32.45	0.23	24.73
410	63.29	0.07	43.25	0.03	41.67
1300	55.33	0.14	28.45	0.06	30.12
1700	58.07	0.24	23.36	0.28	26.32
2150	55.85	0.77	29.25	0.13	18.05
2200	55.52	0.55	25.33	0.14	19.61

Functional Schematic








Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M171494
ZDPLX-2150-S+
EDU1400/1
URJ
200227
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZDPLX-2150-S+](#)