

Coaxial

# Power Splitter/Combiner

ZB4PD1-500+

4 Way-0° 50Ω 5 to 500 MHz


## Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -55°C to 100°C |
| Storage Temperature                                             | -55°C to 100°C |
| Power Input (as a splitter)                                     | 1W max.        |
| Internal Dissipation                                            | 0.250W max.    |
| Permanent damage may occur if any of these limits are exceeded. |                |

## Coaxial Connections

|          |   |
|----------|---|
| SUM PORT | S |
| PORT 1   | 1 |
| PORT 2   | 2 |
| PORT 3   | 3 |
| PORT 4   | 4 |

## Outline Drawing



## Outline Dimensions (inch)

| A     | B     | C     | D     | E     | F     |
|-------|-------|-------|-------|-------|-------|
| 3.50  | 2.13  | .88   | .150  | 3.350 | 1.06  |
| 88.90 | 54.10 | 22.35 | 3.81  | 85.09 | 26.92 |
| G     | H     | J     | K     | wt    |       |
| .125  | 1.75  | .44   | .89   | grams |       |
| 3.18  | 44.45 | 11.18 | 22.61 | 260   |       |

## Features

- wideband, 5 to 500 MHz
- high isolation, 34 dB typ.
- rugged, shielded case

## Applications

- VHF/UHF
- receivers/transmitters



| SMA version shown<br>CASE STYLE: UU188 |               |
|----------------------------------------|---------------|
| Connectors                             | Model         |
| BNC                                    | ZB4PD1-500+   |
| SMA                                    | ZB4PD1-500-S+ |
| N-TYPE                                 | ZB4PD1-500-N+ |

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications




| FREQ. RANGE (MHz) | ISOLATION (dB) |      |      |      |      |      | INSERTION LOSS (dB) ABOVE 6.0 dB |      |      |      |      |      | PHASE UNBALANCE (Degrees) |      |      | AMPLITUDE UNBALANCE (dB) |      |      |
|-------------------|----------------|------|------|------|------|------|----------------------------------|------|------|------|------|------|---------------------------|------|------|--------------------------|------|------|
|                   | L              |      | M    |      | U    |      | L                                |      | M    |      | U    |      | L                         |      | M    |                          | U    |      |
|                   | Typ.           | Min. | Typ. | Min. | Typ. | Min. | Typ.                             | Max. | Typ. | Max. | Typ. | Max. | Max.                      | Max. | Max. | Max.                     | Max. | Max. |
| 5-500             | 34             | 20   | 34   | 20   | 28   | 20   | 0.4                              | 1.0  | 0.5  | 0.9  | 0.9  | 1.5  | 1                         | 3    | 6    | 0.2                      | 0.2  | 0.4  |

L = low range [ $f_L$  to  $10 f_L$ ] M = mid range [ $10 f_L$  to  $f_U/2$ ] U = upper range [ $f_U/2$  to  $f_U$ ]

## Typical Performance Data

| Freq. (MHz) | Total Loss <sup>1</sup> (dB) |      |      |      | Amp. Unbal. (dB) | Isolation (dB) |       |       | VSWR S | VSWR 1 | VSWR 2 | VSWR 3 | VSWR 4 |
|-------------|------------------------------|------|------|------|------------------|----------------|-------|-------|--------|--------|--------|--------|--------|
|             | S-1                          | S-2  | S-3  | S-4  |                  | 1-2            | 2-3   | 3-4   |        |        |        |        |        |
| 5.00        | 6.34                         | 6.35 | 6.33 | 6.33 | 0.01             | 52.83          | 40.68 | 50.23 | 1.08   | 1.12   | 1.12   | 1.13   | 1.13   |
| 30.00       | 6.32                         | 6.32 | 6.31 | 6.32 | 0.01             | 46.48          | 40.23 | 44.89 | 1.05   | 1.09   | 1.09   | 1.09   | 1.09   |
| 50.00       | 6.34                         | 6.34 | 6.34 | 6.35 | 0.01             | 43.68          | 39.45 | 41.92 | 1.05   | 1.09   | 1.09   | 1.09   | 1.10   |
| 100.00      | 6.39                         | 6.39 | 6.39 | 6.38 | 0.01             | 38.83          | 37.13 | 36.88 | 1.07   | 1.09   | 1.10   | 1.10   | 1.10   |
| 130.00      | 6.44                         | 6.43 | 6.43 | 6.43 | 0.01             | 36.86          | 35.97 | 34.90 | 1.05   | 1.09   | 1.08   | 1.08   | 1.08   |
| 150.00      | 6.47                         | 6.46 | 6.47 | 6.46 | 0.01             | 35.87          | 35.35 | 33.83 | 1.05   | 1.08   | 1.08   | 1.08   | 1.08   |
| 180.00      | 6.44                         | 6.44 | 6.43 | 6.43 | 0.01             | 34.55          | 34.35 | 32.40 | 1.08   | 1.08   | 1.09   | 1.10   | 1.10   |
| 200.00      | 6.50                         | 6.51 | 6.49 | 6.48 | 0.03             | 33.82          | 33.88 | 31.75 | 1.08   | 1.07   | 1.07   | 1.09   | 1.09   |
| 230.00      | 6.53                         | 6.54 | 6.52 | 6.51 | 0.03             | 32.96          | 33.12 | 30.74 | 1.06   | 1.06   | 1.04   | 1.05   | 1.05   |
| 250.00      | 6.55                         | 6.56 | 6.55 | 6.53 | 0.03             | 32.54          | 32.76 | 30.22 | 1.08   | 1.06   | 1.06   | 1.06   | 1.06   |
| 290.00      | 6.59                         | 6.59 | 6.59 | 6.58 | 0.02             | 31.75          | 32.00 | 29.34 | 1.10   | 1.05   | 1.05   | 1.07   | 1.07   |
| 350.00      | 6.63                         | 6.64 | 6.62 | 6.60 | 0.04             | 31.02          | 31.24 | 28.37 | 1.11   | 1.03   | 1.04   | 1.04   | 1.04   |
| 400.00      | 6.69                         | 6.72 | 6.68 | 6.67 | 0.05             | 30.73          | 30.84 | 27.85 | 1.10   | 1.02   | 1.01   | 1.03   | 1.03   |
| 450.00      | 6.69                         | 6.72 | 6.71 | 6.67 | 0.05             | 30.66          | 30.70 | 27.53 | 1.14   | 1.01   | 1.01   | 1.03   | 1.03   |
| 500.00      | 6.77                         | 6.81 | 6.79 | 6.75 | 0.06             | 30.85          | 30.77 | 27.37 | 1.11   | 1.01   | 1.02   | 1.01   | 1.02   |

1. Total Loss = Insertion Loss + 6dB splitter loss.



## electrical schematic



## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. G  
M170634  
ZB4PD1-500+  
HY/CP/AM  
181022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZB4PD1-500-S+](#) [ZB4PD1-500+](#) [ZB4PD1-500-N+](#)