

Power Splitter/Combiner

6 Way 50Ω 800 to 2000 MHz

ZB6PD-2+


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.875W max.
DC Current	1.8A(300mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1,2,3,4,5,6	1,2,3,4,5,6

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
7.06	3.13	.88	.250	1.750	5.310	6.810	.250
179.32	79.50	22.35	6.35	44.45	134.87	172.97	6.35
J	K	L	M	N	P	wt	
2.875	.144	3.53	.44	1.31	.89	grams	
73.03	3.66	89.66	11.18	33.27	22.61	800	

Features

- wideband, 800 to 2000 MHz
- excellent VSWR, 1.1:1 typ. output
- high isolation, 27dB typ.
- rugged, shielded case
- up to 10W power input as splitter

Applications

- cellular
- PCN
- instrumentation
- satellite distribution


Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 7.8 dB		AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	S		OUT	
	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.
800-2000	27	17	0.7	1.7	0.7	1.2	1.6	1.13	1.3

Typical Performance Data


Frequency (MHz)	Total Loss ¹ (dB)	Amplitude Unbalance (dB)	Isolation (dB)		VSWR S	VSWR OUTPUTS
			Adjacent	Opposite		
801.50	8.47	0.33	39.60	23.12	1.15	1.21
887.00	8.49	0.31	32.26	24.98	1.12	1.19
986.50	8.54	0.33	27.48	26.44	1.21	1.18
1085.00	8.52	0.31	26.40	28.83	1.18	1.17
1179.50	8.53	0.31	25.53	31.14	1.03	1.11
1278.50	8.60	0.31	22.70	28.45	1.21	1.07
1377.50	8.61	0.30	22.46	26.13	1.31	1.12
1472.00	8.66	0.30	26.27	26.38	1.25	1.15
1571.00	8.69	0.27	38.21	32.21	1.19	1.15
1665.00	8.71	0.26	38.95	29.48	1.19	1.11
1764.50	8.77	0.33	31.36	27.36	1.21	1.06
1863.50	8.84	0.30	29.93	27.81	1.22	1.07
1913.00	8.89	0.32	28.17	27.62	1.23	1.07
1958.00	8.97	0.34	24.73	25.52	1.24	1.07
1998.50	9.01	0.35	21.70	23.15	1.25	1.07

ZB6PD-2+
TOTAL LOSS




1. Total Loss = Insertion Loss + 7.8dB splitter loss.


ZB6PD-2+
ISOLATION



ZB6PD-2+
VSWR



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



SMA version shown
CASE STYLE: Z259

Connectors	Model
SMA	ZB6PD-2-S+
N-TYPE	ZB6PD-2-N+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZB6PD-2-S+](#) [ZB6PD-2-N+](#)