

Coaxial Directional Coupler

50Ω

20 to 2000 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	3
OUTPUT	1
COUPLED	2

Features

- very wideband, 20 to 2000 MHz
- excellent directivity, 25 dB typ.
- excellent mainline loss, 0.7 dB typ.
- rugged shielded case

Applications

- cellular
- GPS
- instrumentation
- communication receivers & transmitters

ZFDC-20-50+



CASE STYLE: K18


Connectors Model

SMA ZFDC-20-50-S+
BRACKET (OPTION "B")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.00	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	70.0

Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING* (dB)		MAINLINE LOSS¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)	
	L	M	U	L	M	U	L	M	U	L	MU						
f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Max.
20-2000	19.5±0.5	±0.8	0.8	1.3	0.7	1.3	1.0	1.6	30	20	25	20	22	10	1.25	1.0	1.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]


1. Mainline loss includes theoretical power loss at coupled port.

* Above 1000 MHz, coupling flatness ±1 dB


Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
20.00	0.82	19.36	29.25	17.95	19.33	21.82
50.00	0.65	19.21	33.94	21.29	23.63	24.42
80.00	0.65	19.19	34.88	22.44	25.39	25.30
100.00	0.60	19.14	35.01	22.93	26.11	25.66
300.00	0.66	19.18	31.17	25.70	28.22	28.13
1000.00	0.86	19.37	23.02	24.12	32.91	28.50
1200.00	1.00	19.40	22.32	20.46	32.70	24.27
1400.00	1.09	19.40	21.99	17.71	30.28	21.55
1600.00	1.27	19.35	21.75	15.67	27.28	19.50
1800.00	1.34	19.36	21.00	14.04	24.37	17.79
2000.00	1.46	19.37	19.19	12.70	21.84	16.24


ZFDC-20-50+
MAINLINE LOSS




ZFDC-20-50+
COUPLING & DIRECTIVITY



ZFDC-20-50+
RETURN LOSS



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M151107
ZFDC-20-50+
WZ/TD/CP/AM
151007

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZFDC-20-50B-S+](#)