




### THE BIG DEAL

- Very Low Insertion Loss with Excellent Power Handling
- Fast Roll-Off with Wide Stopband
- Passbands Up to 36 GHz
- Stopband Up to 57 GHz



### PRODUCT OVERVIEW

Mini-Circuits' coaxial cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 0.5% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' coaxial cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Precise machining allows realization of cavity filters with small form factors for applications where size is critical.

### KEY FEATURES

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter.
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit



CAVITY

## Bandpass Filter

ZVBP-K22R5G+

50Ω 22 to 23 GHz 2.92mm-Female

## FEATURES

- Low Insertion Loss, 1dB Typ.
- Good Return Loss of 25dB Typ.
- Good Rejection Floor of 90 dB Typ.
- Stopband Up to 40 GHz

## APPLICATIONS

- Satellite Communications
- LTE & 5G MIMO Infrastructure



Generic photo used for illustration purposes only

Model No.	ZVBP-K22R5G+
Case Style	YJ3430
Connectors	2.92mm-FEMALE

## +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT 25°C


Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	Fc	—	22.5	—	GHz
	Insertion Loss	F1-F2	—	1.0	2.0	dB
	Return Loss	F1-F2	14	25	—	dB
Stop Band, Lower	Rejection	DC-F3	40	46	—	dB
		F3-F4	20	25	—	
Stop Band, Upper	Rejection	F5-F6	18	23	—	dB
		F6-F7	37	43	—	
		F7-F8	—	30	—	

## ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-40°C to +85°C
Storage temperature	-55°C to +100°C
RF Power Input	5W at 25°C

Permanent damage may occur if any of these limits are exceeded.  
Input and output ports are DC short to ground.

## TYPICAL FREQUENCY RESPONSE



## FUNCTIONAL DIAGRAM





CAVITY


## Bandpass Filter

ZVBP-K22R5G+

## COAXIAL CONNECTIONS

PORT 1	2.92mm-Female
PORT 2	2.92mm-Female

## OUTLINE DRAWING

OUTLINE DIMENSIONS (Inches)  
mm

A	B	C	D	E	F	G
1.03	.65	.52	.360	.730	.670	.15
26.2	16.5	13.2	9.14	18.54	17.02	3.8
H	J	K	L	M	K	Wt.
.34	.07	.074	.82	.32	.41	grams
8.5	1.9	1.88	20.8	8.1	10.4	46

Note. Please refer to case style drawing for details









CAVITY

## Bandpass Filter

ZVBP-K22R5G+

## TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	GROUP DELAY (ns)
100	99.28	0.20	22000	1.27
1000	106.30	0.42	22050	1.16
10000	99.59	0.13	22100	1.09
20800	46.84	0.48	22150	1.03
21300	30.76	0.59	22200	1.00
21400	26.57	0.61	22250	0.96
22000	0.78	40.43	22300	0.95
22200	0.67	39.40	22350	0.93
22500	0.65	34.05	22500	0.90
23000	0.73	31.87	22550	0.90
23240	3.64	4.01	22600	0.91
23600	22.53	0.41	22650	0.91
24200	43.18	0.39	22700	0.92
35000	86.07	0.42	22900	1.00
40000	72.45	0.31	23000	1.09



## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZVBP-K22R5G+](#)