

Switching Power Supply Type SPP1 35W Enclosed type

CARLO GAVAZZI



- Universal AC input full range
- Short circuit protection
- Internal input filter
- High efficiency
- High average efficiency (meets ErP)
- Low stand-by power consumption
- CE, TUV, and cURus approved

Product Description

Enclosed Switching Power Supply meets your needs for AC DC and DC DC power requirements. SPP provides the most flexible OEM system power solutions from 5V to 24V at 20W for industrial control and automation applications. All the range carries full certification and offers a wide range universal of input and screw terminal connections. It has been designed for its performance and compact dimensions.

Ordering Key

SP P1 24 35 1 X

Model _____
 Mounting (P1 = Panel) _____
 Output voltage _____
 Output power _____
 Input Type _____
 Optional features _____

Input type: 1= single phase

Approvals



Output Performance

MODEL NO.	INPUT VOLTAGE	OUTPUT POWER	OUTPUT VOLTAGE	OUTPUT CURRENT	EFF. (min.)	EFF. (typ.)	EFF. (avg.)
Single Output Models							
SPP1 05351	88~264 VAC	30 WATTS	+ 5 VDC	6000 mA	80%	82%	82%
SPP1 12351	88~264 VAC	36 WATTS	+12 VDC	3000 mA	84%	86%	85%
SPP1 15351	88~264 VAC	36 WATTS	+15 VDC	2400 mA	85%	87%	85%
SPP1 24351	88~264 VAC	36 WATTS	+24 VDC	1500 mA	85%	87%	85%

Output Data

All specifications are at nominal values, full load, 25°C unless otherwise stated

Line regulation	± 0.5%	Voltage trim range	5V Model 12V Model 15V Model 24V Model	4.5 - 5.5VDC 10.8 - 13.2VDC 13.5 - 16.5VDC 21.6 - 27.6VDC
Load regulation	± 1%	Rated continuous loading	5V Model 12V Model 15V Model 24V Model	9A@ 5VDC/8.1A @ 5.5VDC 5A@ 12VDC/4.5A @ 13.2VDC 4A @ 15VDC/3.6A @ 16.5VDC 2.5A @ 24VDC/2.15A @ 27.6VDC
Minimum load	0%	Reverse voltage	5V Model 12V Model 15V Model 24V Model	7.5VDC 18VDC 22VDC 35VDC
Turn on time (full resistive load) Vi nom, Io nom Vi nom, Io nom with 3500µF	1000ms 1500ms	Capacitor load		7000µF
Transient recovery time	2ms			
Ripple and noise	100mVpp			
Output voltage accuracy	+ 1%			
Temperature coefficient	± 0.03%/°C			
Hold up time Vi= 115VAC Vi= 230VAC	10ms 80ms			
Voltage fall time (Io nom, Vi nom)	150ms			
Voltage rise time Vi nom, Io nom (full resistive load) Vi nom, Io nom with 3500µF CAP	150ms 500ms			

Input Data All specifications are at nominal values, full load, 25°C unless otherwise stated

Rated input voltage I_{nom}	100 - 240VAC	Power dissipation (V_i : 230VAC, I_o nom)	5V Model 8W
Voltage range		12V Model 7W	
AC IN	88 - 264VAC	15V Model 6.5W	
DC IN	120 - 375VDC	24V Model 6.5W	
Rated input current		Frequency range	47- 63Hz
V_i: 115 / 230 VAC I_o nom	620/400 mA	Leakage current	
V_i: 88 VAC, I_o nom	800mA	Input-Output	0.25mA
Inrush current		Input-FG	3.5mA
V_i= 115VAC	20A		
V_i= 230VAC	40A		

Controls and Protection All specifications are at nominal values, full load, 25°C unless otherwise stated

Overload	110 – 170%	Over voltage protection	VDC	
Input fuse	T2A/250VAC internal ¹⁾		Min.	Max.
Output short circuit	Hiccup mode	5V Model	5.75	6.75
		12V Model	13.8	16.2
		15V Model	17.25	20.25
		24V Model	28.8	32.4

¹⁾ Fuse not replaceable by user

General Data All specifications are at nominal values, full load, 25°C unless otherwise stated


Ambient temperature	-40°C to +71°C	MTBF (Bellcore issue 6 @ 40°C, GB)	
Derating (+56°C to +71°C)	2.5%/°C (see curve)	5V Model	666000 Hours
Relative humidity	20 ~ 95%RH	12V Model	695000 Hours
Storage	-40°C to +85°C	15V Model	712000 Hours
Protection degree	IP20	24V Model	716000 Hours
Cooling	Free air convection	Case material	Metal
Insulation voltage		Altitude IEC 60068-2-13	4850m
Input-Output	3.000VAC/4242VDC min	Stand-by power consumption	0.3W
Input-FG	1.500VAC/2121VDC min	Dimensions LxWxD mm(inch)	78(3.07)x51(2)x28(1.1)
Insulation resistance I/O	100MΩ min (@ 500VDC)	Weight	180g
Switching Frequency	65Khz		

Norms and Standards

Vibration resistance	meets IEC 60068-2-6 (10-500Hz, 2G, along X, Y, Z each Axis, 60 min for each Axis)	CE	EN 61000-6-3, EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2, EN 55024, EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5, EN 61000-4-6, EN 61000-4-8, EN 61000-4-11, ENV 50204, EN 61204-3
Shock resistance	meets IEC 60068-2-27 (15G, 11ms, 3 Axis, 6 faces, 3 times for each face)		
UL / cUL	UL60950-1, Recognized		
TUV	EN 60950 - 1CB scheme		




Block Diagrams




Pin Assignment and Front Controls

Pin No.	Designation	Description
1	L	Input terminals (phase conductor, no polarity at DC input)
2	N	Input terminals (neutral conductor, no polarity at DC input)
3	⊕	Ground this terminal to minimize high-frequency emissions
4	-	Negative output terminal
5	+	Positive output terminal
	Vout ADJ	Trimmer-potentiometer for Vout adjustment
	DC ON	Operation indicator LED


Typ. Efficiency Curve






Derating Diagram



Typ. Current Limited Curve



Mechanical Drawings mm (inches)



Installation

Ventilation and cooling	Ventilation/Cooling Normal convection
Connector size range Spring terminal	AWG22-12 (0.2~2.5mm ²) flexible/solid cable, connector can withstand torque at maximum 0.90 Nm (8 lb/in)
Max. torque for terminal Input terminals Output terminals	0.56Nm (5.0lb-in) 0.56Nm (5.0lb-in)
General tolerances mm(in.) 0.00 (0.00) ÷ 30.00 (1.18) 30.00 (1.18) ÷ 120.00 (4.72)	±0.30 (0.01) ±0.50 (0.02)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[SPP112351](#) [SPP115351](#) [SPP105351](#) [SPP124351](#)