

CARLO GAVAZZI
Automation Components

CARLO GAVAZZI

Limit & Safety Switches

*General Purpose
Pre-wired
Safety*



Switch



Limit Switches

Carlo Gavazzi broadens its leading range of products for the industrial automation world, with the new and complete range of mechanical limit and safety switches.

These robust switches provide machine manufacturers and panel builders with a global and comprehensive solution to their switching needs. With their complete conformity to the most demanding regulations, machines are allowed to operate properly and therefore machine downtime and personnel risk are minimized.



**User
Friendly**



**Long Term
Reliability**



**Cost
Saving**



**Diagnostic
Warning**

Contact Blocks and Actuators

With ten different contact blocks, most of them with positive opening safety contacts (IEC 60947-5-1) including slide, slide overlapping, and snap acting, coupled with over 60 different actuating heads and levers, over 8,000 different combinations of limit and safety switches are possible. This covers almost every possible industrial automation application, as well as most elevator and door applications.

Housings

Four different housing sizes, with five different cable entry types (1/2" NPT, PG11, PG13.5, M16, and M20) provide the flexibility needed to address most application requirements. And where compact size and fast wiring are desired, two additional housing types with pre-wired cable are available. Most of the switches are available with a choice of double-insulated thermoplastic or metal housing.

A wide operating temperature range of -13° to $+158^{\circ}\text{F}$ (-30° to $+80^{\circ}\text{C}$), along with enclosure ratings of up to IP67, enable the use of the switches in harsh-duty environments.

Safety Switches

Safety switches are available in four categories – key interlock, shaft lever, pull wire, or manual reset. Key interlock types feature five different head positions, and allow linear or radial operation with a small pivot radius. Shaft lever switches offer two connection options (lever or pin), allowing hinge operation. Pull wire types, with and without reset for emergency stop, can be used on long distances (up to 25m), which are typically found on conveyors. Manual reset switches feature a pull button to reset the switch after it has been activated, typically used for machine over-travel detection.

Actuators

PS 21 L-N S11 PO-M 00

For Limit Switches

For Safety Switches

Plunger Type		Lever Type		Safety Type	
P0	Metal plain PLUNGER for all body types	RT	Roller LEVER for all body types	05 09	Key operated 90° adjustable head: PSxxS Fully turnable head: PS21S PS42S
P01	Metal plain PLUNGER with fixing nuts: PSxxM	BR BE	Roller internal or external bent LEVER: PS21L PS42L	HC	Zinc plated steel lever: PS21H PS42H
PH	Metal plain PLUNGER with dust protection cup: PS21L PS31L PS42L PSxxM	W0	LEVER with rubber roller Ø50 PS21L PS31L PS42L PS43L	HZ HS	Zinc plated steel shaft Stainless steel shaft: PS21H
PR1	Metal roller PLUNGER with fixing nuts: PSxxM	R1	Adjustable LEVER with nylon roller: PS21L PS31L PS42L PS43L	N6 N7 N7⁴	Pull action with ring (25N): PS21R PS42R Pull wire without reset for simple stop: PSxxR Pull wire with reset for emergency stop
PR	Roller PLUNGER for all body types	W1	Adjustable LEVER with rubber roller Ø50: PS21L PS31L PS42L PS43L	With Pull Button Reset	
P91	Metal cross roller PLUNGER with fixing nuts: PSxxM	LA² LG³	Adjustable rod LEVER (170mm): PS21L PS31L PS42L PS43L	P0	Steel plunger: PS21K PS42K
RH	Plastic roller lever on metal PLUNGER (left side): PS21L PS31L PS42L PS43L	Shaft Type		PR	Steel plunger with nylon roller: PS21K PS42K
RJ	Plastic roller lever on metal PLUNGER with dust protection cup (left side) PS21L PS31L PS42L	LS	Stainless steel spring multidirectional actuator (117mm): PS21L PS31L PS42L PS43L PSxxM	R3	Steel plunger with nylon roller: PS21K PS42K
RV	Plastic roller lever on metal PLUNGER (right side): PS21L	LP	Multidirectional nylon actuator with stainless steel spring (115mm): PS21L PS31L PS42L PS43L PSxxM	LR	Steel plunger with nylon roller: PS42K
RW	Plastic roller lever on metal PLUNGER with dust protection cup (right side): PS21L	LW	Stainless steel spring multidirectional actuator (cat whisker - 135mm): PS21L PS31L PS42L PS43L PSxxM	RT	Lever with nylon roller: PS21K PS42K
LR	Adjustable plastic roller lever on metal PLUNGER (left side): PS21L PS42L PS42K				

1 - With 0L code on options.

2 - Stainless steel rod Ø3.

3 - Fiberglass rod Ø6

4 - With K0 code on options.



Limit Switch - Limit Type Plastic Body

- Double Insulation □
- Degree of protection IP65
- Reinforced UL-V0 thermoplastic fiber-glass body
- Positive Opening Operation ⇨
- Minimum Actuation Force/Torque
- Minimum Force to achieve Positive Opening Operation
- Precise operating points (consistency)
- Immune to electromagnetic disturbances
- Zb type contact blocks
- Current $I_{th} = 10A$
- Rated insulation voltage $U_i = 500V$
- UL, CSA
- Conforms with IEC 947-5-1 (EN 60947-5-1)

Body

PS 21 L-N S11 PO-T 00



(1) L = General Purpose

Contact Block

PS 21 L-N S11 PO-T 00

For all body types

S11	1NO + 1NC Snap Action Contacts	21-22 13-14 21-22 13-14
T11	1NO + 1NC Non overlapping Slow Action Contacts	21-22 13-14
011	1NO + 1NC Overlapping Slow Action Contacts	21-22 13-14
T02	2NC Slow Action Contacts	11-12 21-22
T20	2NO Slow Action Contacts	13-14 23-24
S02	2NC Snap Action Contacts	11-12 21-22 11-12 21-22

Only for PS31

T12	1NO + 2NC Non overlapping Slow Action Contacts	21-22 13-14 11-12 21-22
T21	2NO + 1NC Non overlapping Slow Action Contacts	13-14 23-24 11-12 21-22
T03	3NC Simultaneous Slow Action Contacts	11-12 21-22 11-12 21-22
T30	3NO Simultaneous Slow Action Contacts	13-14 23-24 13-14 23-24

To instantly view a data sheet and specify products, visit www.GavazziOnline.com


Specifications are subject to change without notice.

For requests about special features and/or customization, please contact your closest sales office.



Cable Gland

PS 21 L-N S11 PO-T 00




P = cable inlet PG13.5 cable gland

B = cable inlet PG11 cable gland

M = cable inlet M20x1.5 cable gland


A = cable inlet M16x1.5 cable gland

N = cable inlet 1/2" NPT cable gland



Limit Switches


Limit Switch - Limit Type Metal Body



- High mechanical resistance
- Degree of protection IP66
- Zinc alloy (Zamack) or aluminium body
- Positive Opening Operation \odot
- Minimum Actuation Force/Torque
- Minimum Force to achieve Positive Opening Operation
- Precise operating points (consistency)
- Immune to electromagnetic disturbances
- Zb type contact blocks
- Current I_{th} = 10A
- Rated insulation voltage U_i = 500V
- UL, CSA
- Conforms with IEC 947-5-1 (EN 60947-5-1)

Body


PS 21 L-N S11 PO-M 00



(1) L = General Purpose

Cable Gland

PS 21 L-N S11 PO-M 00



- P = cable inlet PG13.5 cable gland
B = cable inlet PG11 cable gland
M = cable inlet M20x1.5 cable gland
A = cable inlet M16x1.5 cable gland
N = cable inlet 1/2" NPT cable gland

Contact Block

PS 21 L-N S11 PO-M 00



For all body types

S11	1NO + 1NC Snap Action Contacts	21-22 13-14 13-14
T11	1NO + 1NC Non overlapping Slow Action Contacts	21-22 13-14
O11	1NO + 1NC Overlapping Slow Action Contacts	21-22 13-14
T02	2NC Slow Action Contacts	11-12 21-22
T20	2NO Slow Action Contacts	13-14 23-24
S02	2NC Snap Action Contacts	11-12 21-22

Only for PS31


T12	1NO + 2NC Non overlapping Slow Action Contacts	21-22 31-32 5-14
T21	2NO + 1NC Non overlapping Slow Action Contacts	21-22 31-32 23-24
T03	3NC Simultaneous Slow Action Contacts	11-12 21-22 31-32
T30	3NO Simultaneous Slow Action Contacts	13-14 23-24 33-34

Limit Switch - Prewired Type Plastic and Metal Body

- Double Insulation  (for thermoplastic type)
- Sealed with epoxy resin at the base of the box
- Degree of protection IP67
- Thermoplastic material or diecast zinc alloy body
- Positive Opening Operation 
- Minimum Actuation Force/Torque
- Minimum Force to achieve Positive Opening Operation
- Precise operating points (consistency)
- Immune to electromagnetic disturbances
- Zb type contact blocks
- Current Ith = 10A
- Rated insulation voltage Ui = 500V
- UL, CSA
- Conforms with IEC 947-5-1 (EN 60947-5-1)

Body

PS 21 M⁽¹⁾-U S11 PO-T⁽²⁾ 00



⁽¹⁾M = Miniature

⁽²⁾M = Metal

T = Thermoplastic

Contact Block

PS 21 M-U S11 PO-T 00

For all body types

S11	1NO + 1NC Snap Action Contacts	
T11	1NO + 1NC Non overlapping Slow Action Contacts	

Options

PS 21 M-U S11 PO-T 00

00

Standard type

1m PVC cable 4x0.75mm² (Plastic Type)
1m PVC cable 5x0.75mm² (Metal Type)


Other cable lengths

02	2m	07	7m
03	3m	08	8m
04	4m	09	9m
05	5m	10	10m
06	6m		

To instantly view a data sheet and specify products, visit www.GavazziOnline.com
Specifications are subject to change without notice.

For requests about special features and/or customization, please contact your closest sales office.

Limit Switch - Safety Type Plastic and Metal Body



- Double Insulation □ (for thermoplastic type)
- High mechanical resistant
- Degree of protection IP65 (thermoplastic) IP66 (metal)
- Reinforced UL-V0 thermoplastic fiber-glass body
- Zinc alloy (Zamack) or aluminium body
- Positive Opening Operation ⊕
- Minimum Actuation Force/Torque
- Minimum Force to achieve Positive Opening Operation
- Precise operating points (consistency)
- Immune to electromagnetic disturbances
- Zb type contact blocks
- Current I_{th} = 10A
- Rated insulation voltage U_i = 500V
- UL, CSA
- Conforms with IEC 947-5-1 (EN 60947-5-1)

Body


PS 21 S⁽¹⁾-N S11 05-T⁽²⁾ 00



- (1) S = Key Actuator
R = Pull Wire (rope)
(2) Y = Metal
- H = Hinge (pin or shaft)
K = With Pull Button Reset
T = Thermoplastic

Cable Gland

PS 21 S-N S11 05-T 00



- P = cable inlet PG13.5 cable gland
B = cable inlet PG11 cable gland
M = cable inlet M20x1.5 cable gland
A = cable inlet M16x1.5 cable gland
N = cable inlet 1/2" NPT cable gland

Accessories for Head Type 05 and 09

Operating keys for 05 and 09 heads - only for PS21 and PS42

K13		Bent key 22mm	K17		Shock absorbing bent key
K14		Flat key 22mm	K18		Shock absorbing flat key
K15		Bent key 13mm	K19		Adjustable joint key
K16		Flat key 13mm			

Operating keys for 05 head - only for PS31 and PS43

K35		Bent key 22mm	K39		Adjustable joint key
K36		Flat key 22mm			

Contact Block

PS 21 S-N S11 05-T 00

For all body types

S11	1NO + 1NC Snap Action Contacts	
T11	1NO + 1NC Non overlapping Slow Action Contacts	
011	1NO + 1NC Overlapping Slow Action Contacts	
T02	2NC Slow Action Contacts	
T20	2NO Slow Action Contacts	
S02	2NC Snap Action Contacts	

Only for PS31 and PS43

T12	1NO + 2NC Non overlapping Slow Action Contacts	
T21	2NO + 1NC Non overlapping Slow Action Contacts	
T03	3NC Simultaneous Slow Action Contacts	
T30	3NO Simultaneous Slow Action Contacts	

The Complete Product Package



Sense

Inductive and Capacitive Sensors
Photoelectric Sensors
Inductive Loop Detectors
Ultrasonic Sensors
Motion/Presence Vision Sensors
Radar Sensors
Conductive Level Sensors
Limit Switches
Magnetic Switches



Switch

Solid State Relays
Hybrid Relays
Solid State Contactors
Contactors and Overloads
Manual Motor Starters/Protectors
Motor Controllers
Variable Frequency Drives
Electromechanical Relays
Push Buttons and Pilot Devices



Control

Energy Management
Solar Energy Monitoring
Switching Power Supplies
Digital Panel Meters
Timers and Counters
Monitoring Controls
Temperature Controllers



Safety

Control Modules
Interlock Switches
Magnetic Sensors
Light Curtains
Mat Systems



Fieldbus

Dupline® Field and Installation Bus
Building Automation Systems
Parking Guidance Systems
Elevator Systems
Mining Systems

A Global Force in Industrial Automation

CARLO GAVAZZI has a multitude of sales offices spanning North America (*not to mention our hundreds of distributors*). Therefore, we can be viewed as "your local automation resource" - assisting you every step of the way in finding the proper solution for your various application requirements. Naturally, our job is greatly simplified as we have such a vast range of solutions to offer you via our comprehensive *product package*.

Our worldwide sales offices make us an ideal business partner, *especially for manufacturers of exported machinery*, as our products are available locally and they are RoHS and CE marked.

USA

CARLO GAVAZZI INC.
750 Hastings Lane
Buffalo Grove, IL 60089
Tel: 847.465.6100
Fax: 800.222.2659
Sales@CarloGavazzi.com

CANADA

CARLO GAVAZZI (CANADA) INC.
2660 Meadowvale Boulevard
Mississauga, ON L5N 6M6
Tel: 888.575.2275
Fax: 905.542.2248
Gavazzi@CarloGavazzi.com

MEXICO

CARLO GAVAZZI MEXICO S.A. de C.V.
Calle La Montaña no. 18, Fracc. Los Pastores
Naucalpan de Juárez, EDOMEX CP 53340
Tel & Fax: 52.55.5373.7042
MexicoSales@CarloGavazzi.com

• Regional / Area Sales Office
• District Sales Office

Argentina • Australia • Austria • Bahrain • Belgium • Bolivia • Bosnia • Brazil • Brunei • Bulgaria • Canada
Chile • China • Columbia • Croatia • Cyprus • Czech • Denmark • Dominican Republic • Egypt • Estonia
Finland • France • Germany • Greece • Hungary • Hong Kong • Iceland • India • Indonesia • Iran • Ireland
Italy • Japan • Jordan • Kenya • Korea • Kuwait • Lebanon • Malaysia • Malta • Morocco • Mauritius • Mexico
Netherlands • New Zealand • Norway • Pakistan • Papua New Guinea • Paraguay • Peru • Philippines
Poland • Portugal • Qatar • Romania • Russia • Saudi Arabia • Serbia • Singapore • Slovakia • Slovenia
South Africa • Spain • Sultanate of Oman • Sweden • Switzerland • Taiwan • Thailand • Tunisia • Turkey
Ukraine • United Arab Emirates • United Kingdom • Uruguay • United States of America • Venezuela • Vietnam

Your Authorized Distributor:

CARLO GAVAZZI
Automation Components

USA Tel: 847.465.6100 Fax: 800.222.2659

Canada Tel: 888.575.2275 Fax: 905.542.2248

Mexico Tel & Fax: 52.55.5373.7042

Website www.GavazziOnline.com

Email Info@CarloGavazzi.com



Visit our website for downloadable data sheets,
brochures and pricing: www.GavazziOnline.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[K39](#) [K36](#) [K35](#)