

Panel Meters and Controllers

AC/DC Current and Voltage Meter/Controller

Type LDI35 AV2

CARLO GAVAZZI



- 3 1/2-dgt meter or 3-dgt + dummy zero
- For AC/DC current and voltage measurements
- Indicator or controller
- 200 VAC/DC, 500 VAC/DC and 2 AAC/DC, 5 AAC/DC
- All functions selectable by key-pad
- Password protection
- 48 x 96 mm
- Degree of protection: IP 50 (IP 65 on request)

Product Description

3 1/2-dgt or 3-dgt + dummy zero multi-range μ P-based indicator or controller for AC and DC current and voltage measurements. Selectable input range. Ensures a degree of protection (front) of IP 50 (IP 65 on request).

Ordering Key

LDI35AV2D0XXXX

Model _____
 Range code _____
 Power supply _____
 Setpoints _____
 Engineering unit _____
 Option _____

Type Selection

Range code	Power supply		Options
See Range Table	A: 24 VAC, -15% +10%, 50/60 Hz ¹⁾	E: 120 VAC, -15% +10%, 50/60 Hz ¹⁾	XX: None (standard)
	B: 48 VAC, -15% +10%, 50/60 Hz ¹⁾	F: 240 VAC, -15% +10%, 50/60 Hz ¹⁾	IX: Degree of protection IP 65
Setpoints	C: 115 VAC, -15% +10%, 50/60 Hz ¹⁾	3: 9 to 32 VDC with galvanic insulation ¹⁾	AX: Excitation output
0: 0 setpoints	D: 230 VAC, -15% +10%, 50/60 Hz (standard)	6: 40 to 150 VDC with galvanic insulation ¹⁾	XT: Tropicalization
1: 1 setpoint ¹⁾			

¹⁾ Power supply on request

Input Specifications

Rated input Current:	2 AAC/DC, 5 AAC/DC, 40 to 400 Hz	AC Measurement	Measurement of the average value resulting from the sine half-wave rectification of the input current/voltage by rms calibration
Voltage:	200 VAC/DC, 500 VAC/DC, 40 to 400 Hz	Sampling rate	4 times/s, dual slope 16 bits A/D converter
Overload protection Continuous For 1s	1.2 x rated input 2 x rated input	Indication 3 1/2 dgt:	Max. 1999 (AC/DC) Min. -1999 (DC), 0 (AC)
Accuracy DC: (@ 25°C \pm 5°C, R.H. \leq 60%) AC: (@ 25°C \pm 5°C, R.H. \leq 60%, 50/60 Hz, 5 to 100% f.s.)	\pm 0.3% f.s., \pm 1 dgt \pm 0.5% f.s., \pm 1 dgt	3 + 0 dgt:	Max. 9990 (AC/DC) Min. -1990 (DC), 0 (AC)
Temperature drift	\pm 200 ppm/°C	Key-pad 3 keys:	"S" for menu selection. "UP" and "DOWN" for value programming/function selection.
Display	7-segment LED, h 14.2 mm, 3 1/2 digits or 3 digits + dummy zero selectable by means of the front key-pad		

Output Specifications

Excitation output	
Voltage	15 VDC non-stabilized/ 40 mA max. (on request)
Insulation	100 V _{rms} output to measuring input 4000 V _{rms} output to AC supply input 500 V _{rms} output to DC supply input
Alarms	
Number of setpoints	0 (1 on request)
Alarm types	Over range, up alarm, down alarm, down alarm with dis- abling at power-on, up alarm with latch, down alarm with latch
Setpoint adjustment	0 to 100% of the displayed range
Hysteresis	0 to 100% of the displayed range
On-time delay	0 to 255 s
Off-time delay	0 to 255 s
Relay status	Normally energized/de-ener- gized
Output type	
Contact	1 x SPDT
Rating	5A, 250 VAC/VDC 40 W/ 1200 VA, 130.000 cycles.
Min. response time	≤ 500 ms, filter excluded, set- point on-time delay: "0"
Insulation	2000 V _{rms} output to measuring inputs 2000 V _{rms} output to excitation output

Software Functions

Password	Numeric code of max. 3 di- gits; 2 protection levels of the programming data
1st level	Password "0", no protection
2nd level	Password from 1 to 255, all data protected
Scaling factor	
Operating mode	Electrical scale compression, compression/expansion of the displayed scale (max. 2 without digital filter, > 2 with digital filter)
Electrical scale	Programmable within the whole measuring range
Decimal point position	Programmable within the displaying range
Displayed scale	Programmable within the whole displaying range
Diagnostics	The display flashes when the limits of the displayed range are exceeded, the data are updated up to the maximum read-out
Over range	EEE (AC/DC)
Under range	- EE (DC)
Filter	
Filter operating range	From 0 to 1999/9990
Filtering coefficient	From 1 to 255
Max. data hold	Automatic storage (RAM only) of the max. value measured after the last reset

Supply Specifications

AC supply	230 VAC, -15% +10%, 50/60 Hz (standard)
Insulation	24 VAC, 48 VAC, 115 VAC, 120 VAC, 240 VAC, -15% +10%, 50/60 Hz (on request)
DC supply	9 to 32 VDC, G.I. max. inrush current: ≤ 1.2 A/200 ms
Insulation	40 to 150 VDC, G.I., max. inrush current: ≤ 0.6 A/200 ms
Power consumption	500 V _{rms} supply input to all other inputs/outputs
	6.5 VA

General Specifications


Operating temperature	0° to 50°C (32° to 122°F) (R.H. < 90% non-condensing)
Storage temperature	-10° to 60°C (14° to 140°F) (R.H. < 90% non-condensing)
Insulation reference voltage	300 V _{rms} to ground
Dielectric strength	4000 V _{rms} for 1 minute
Noise rejection	
NMRR	40 dB, 40 to 60 Hz
CMRR	100 dB, 40 to 60 Hz
EMC	IEC 60801-2, IEC 60801-3, IEC 60801-4 (level 3), EN 50 081-1, EN 50 082-1
Safety standards	EN 61 010-1, IEC 61010-1, VDE 0411
Connector	Screw-type
Housing	
Dimensions	1/8 DIN, 48 x 96 x 83 mm
Material	ABS, self-extinguishing: UL 94 V-0
Degree of protection	IP 50 (IP 65 on request)
Weight	340 g approx.
Approvals	CE, CSA

Range Table


Rated inputs	Ranges (3 1/2 dgt)	Impedances
200 VDC	- 199.9 V to 199.9 VDC	$\geq 1 \text{ M}\Omega$
500 VDC	- 500 V to 500 VDC	$\geq 1 \text{ M}\Omega$
2 ADC	- 1.999 A to 1.999 ADC	$\leq 0.05 \Omega$
5 ADC	- 5.00 A to 5.00 ADC	$\leq 0.05 \Omega$
200 VAC	- 0 V to 199.9 VAC	$\geq 1 \text{ M}\Omega$
500 VAC	- 0 V to 500 VAC	$\geq 1 \text{ M}\Omega$
2 AAC	- 0 A to 1.999 AAC	$\leq 0.05 \Omega$
5 AAC	- 0 A to 5.00 AAC	$\leq 0.05 \Omega$

Rated inputs	Ranges (3 + 0 dgt)	Impedances
100 VDC	- 19.99 V to 99.90 VDC	$\geq 1 \text{ M}\Omega$
500 VDC	- 50.0 V to 500.0 VDC	$\geq 1 \text{ M}\Omega$
1 ADC	- 199.0 mA to 999.0 mA	$\leq 0.05 \Omega$
5 ADC	- 1.99 A to 5.000 ADC	$\leq 0.05 \Omega$
100 VAC	- 0 V to 99.90 VAC	$\geq 1 \text{ M}\Omega$
500 VAC	- 0 V to 500.0 VAC	$\geq 1 \text{ M}\Omega$
1 AAC	- 0 mA to 999.0 mAAC	$\leq 0.05 \Omega$
5 AAC	- 0 A to 5.000 AAC	$\leq 0.05 \Omega$

Dimensions



Front Panel Description



1. Key-pad

Set-up and programming procedures are easily controlled by the 3 pushbuttons.

“S”

- Selection key to select programming function (instrument configuration) or measurement and alarm detection.

“▲” and “▼”

- Up and down keys for increasing or decreasing programming values.

2. Display

3 1/2-digit or 3-digit + dummy zero (maximum read-out 1999/9990).

Alphanumeric indication by means of 7-segment display for:


- Displaying of the measured value, over-range, burn-out and programming indications.
- Indication of programming parameters.

3. Engineering unit


Screen for interchangeable unit label. The symbols in the shaded areas are those available on the set of engineering unit labels supplied with the LDI35 (engineering unit label to be inserted by customer).

W = 08	MΩ = 16	% = 24	mm HG = 32	cm = 40
mV = 01	kW = 09	Hz = 17	mbar = 25	l/min = 33
V = 02	MW = 10	kHz = 18	bar = 26	l/h = 34
kV = 03	var = 11	RPM = 19	psi = 27	kg/min = 35
μA = 04	kvar = 12	m/s = 20	ata = 28	ton/h = 36
mA = 05	Mvar = 13	m/min = 21	atm = 29	m³/min = 37
A = 06	Ω = 14	°C = 22	kg/cm² = 30	m³/h = 38
mW = 07	kΩ = 15	°F = 23	mm H₂O = 31	mm = 39
				μs = 47

Terminal Board



Excitation Output



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[LDI35AV2C0XX02](#) [LDI35AV2C1XXIX](#) [LDI35AV230XXXX](#) [LDI35AV260XXXX](#) [LDI35AV2C0XXXX](#)
[LDI35AV2A1XXXX](#) [LDI35AV2D1XXXX](#) [LDI35AV2C1XXXX](#) [LDI35AV2C0XXIX](#)