


Type PC50CND10RP



- Range: 1 m
- Adjustable sensitivity
- Modulated, infrared light
- Supply voltage:
12 to 240 VDC and 24 to 240 VAC, 50/60 Hz
- Output: Relay 3 A, 30 VDC, 240 VAC
- Make and break switching function
- LED-indication for output ON, signal stability and supply ON
- Protection: reverse polarity, transients
- High degree of EMC



Product Description

The PC50CND. is a general purpose diffuse-reflective sensor in a compact squared 17 x 50 x 50 mm reinforced PC/ABS-housing. It is useful in applications where basic sensors provide adequate

sensing performance. The long sensing range in addition to sensitivity adjustment gives a very flexible sensor. Light and dark operation is switch selectable.

Ordering Key

PC50CND10RP

Type _____
Housing style _____
Housing size _____
Housing material _____
Housing length _____
Detection principle _____
Sensing distance _____
Output type _____
Output configuration _____

Type Selection


Housing W x H x D	Range (S _n)	Ordering no. Make and break switching
17 x 50 x 50 mm	1 m	PC 50 CND 10 RP

Specifications


Rated operating distance (S_n)	Up to 1 m, reference target Kodak test card R 27, white, 90% reflectivity, 200 x 200 mm	Power ON delay (t_v)	≤ 300 ms
Blind zone	Max. 10 cm	Output function	Light and dark operation is switch selectable
Sensitivity	Adj. by single-turn pot. meter	Indication function	
Temperature drift	≤ 0.5%/°C	Output ON	LED, yellow
Hysteresis (H)		Supply ON, signal stability	LED, green
Differential travel	3-20%	Environment	
Rated operational volt. (U_B)	12 to 240 VDC 24 to 240 VAC, 50 to 60 Hz	Overvoltage category	II (IEC 60664/60664A; 60947-1)
Rated operational power	≤ 2.0 VA (relay ON)	Pollution degree	3 (IEC 60664/60664A; 60947-1)
Output		Degree of protection	IP 67 (IEC 60529; 60947-1)
Contact ratings		Temperature	
Resistive loads AC 1	3 A/250 VAC	Operating	-20° to +60°C (-4° to +140°F)
DC 1	3 A/30 VDC (> 10 mA/5 VDC)	Storage	-25° to +80°C (-13° to +176°F)
Mechanical life (typical)	≥ 15 x 10 ⁶ operations	Vibration	10 to 150 Hz, 0.5 mm/7.5 g (IEC 68-2-6)
Electrical life (typical)	≥ 1 x 10 ⁵ operations at 3 A/240 VAC	Shock	2 x 1 m & 100 x 0.5 m (IEC 68-2-32)
Protection	Reverse polarity, transients	Rated insulation voltage	250 VAC (rms)
Light source	GaAlAs, LED, 880 nm	Housing material	
Light type	Infrared, modulated	Body	PC/ABS, grey, reinforced
Sensing angle	± 2° at 1/2 range	Front glass	PC black
Ambient light	Max. 5'000 lux	Mounting bracket	Steel, galvanized
Operating frequency	20 Hz	Connection	
Response time		Cable	PVC, grey, 2 m, 5 x 0.34 mm ²
OFF-ON (t _{ON})	≤ 25 ms	Weight	130 g
ON-OFF (t _{OFF})	≤ 25 ms	Approvals	UL, CSA
		CE-marking	Yes




Operation Diagram




Dimensions




Wiring Diagram




Detection Diagram







Signal Stability



Excess Gain



Installation Hints

<p>To avoid interference from inductive voltage/current peaks, separate the prox. switch power cables from any other power cables, e.g. motor, contactor or solenoid cables</p> 	<p>Relief of cable strain</p>  <p>The cable should not be pulled</p>	<p>Protection of the sensing face</p>  <p>A proximity switch should not serve as mechanical stop</p>	<p>Switch mounted on mobile carrier</p>  <p>Any repetitive flexing of the cable should be avoided</p>
---	---	--	--


Delivery Contents

- Photoelectric switch: PC50CND..
- Installation instruction
- Mounting bracket APC50-1
- **Packaging:** Cardboard box

Accessories

- Screwdriver for adjustment: 77-001

For further information refer to "Accessories"



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[PC50CND20BA](#) [PC50CND20RP](#)