
## **Photoelectrics** Retro-reflective, Polarized, Relay Output Type PC50CNP06RP





- Range: 6 m
- · Adjustable sensitivity
- · Modulated, visible red light, polarized
- High immunity to shiny surfaces
- Supply voltage:
  - 12 to 240 VDC and 24 to 240 VAC, 50/60 Hz
- Output: Relay 3 A, 30 VDC, 250 VAC
- Make or break switching function
- LED-indication for output ON, signal stability and supply ON
- High degree of EMC







#### **Product Description**

The PC50CNP. is a general purpose polarized retro-reflective sensor in a compact squared 17 x 50 x 50 mm reinforced PC/ABS-housing. It is useful in applications where basic sensors provide adequate sensing performance. The long sensing range in addition to sensitivity adjustment gives a very flexible sensor. Light and dark operation is switch selectable.

# **Ordering Key**

PC50CNP06RP

Туре	
Housing style —————	
Housing size ——————	
Housing material ——————	
Housing length —	
Detection principle ————————————————————————————————————	
Sensing distance ————————	
Output type	╛
Output configuration —	

#### Type Selection

Housing	Range	Ordering no.	
W x H x D	(S <sub>n</sub> )	Make and break switching	
17 x 50 x 50 mm	6 m	PC 50 CNP 06 RP	

Note: Reflectors to be ordered separately

## **Specifications**

Rated operating distance $(S_n)$	Up to 6 m, with reflector type ER 4, ref. target	
Blind zone	Max. 20 cm	
Sensitivity	Adj. by single-turn. pot.	
Temperature drift	≤ 0.5%/°C	
Hysteresis (H) Differential travel	3-20%	
Rated operational volt. (U <sub>B</sub> )	12-240 VDC 24-240 VAC, 50 to 60 Hz	
Rated operational power	≤ 2.5 VA (relay ON)	
Output Contact ratings Resistive loads AC 1 DC 1 Mechanical life (typical) Electrical life (typical)	3 A/250 VAC 3 A/30 VDC (>10 mA/5 VDC) ≥ 15 x 10 <sup>6</sup> operations ≥ 1 x 10 <sup>5</sup> operations at 3 A/240 VAC	
Protection	Reverse polarity, transients	
Light source Light type Sensing angle Ambient light	GaAlAs, LED, 660 nm Visible red, modulated ± 2° at 1/2 range Max. 10'000 lux	


Operating frequency	20 Hz	
Response time		
OFF-ON (ton)	≤ 25 ms	
ON-OFF (t <sub>OFF</sub> )	≤ 25 ms	
Power ON delay (t <sub>v</sub> )	≤ 300 ms	
Output function	Light or dark operation	
	is switch selectable	
Indication function		
Output ON	LED, yellow	
Supply ON, signal stability	LED, green	
Environment		
Overvoltage category	II (IEC 60664/60664A; 60947-1)	
Pollution degree	3 (IEC 60664/60664A; 60947-1)	
Degree of protection	IP 67 (IEC 60529; 60947-1)	
Temperature		
Operating	-20° to +60°C (-4° to +140°F)	
Storage	-25° to +70°C (-13° to +158°F)	
Vibration	10 to 150 Hz, 0.5 mm/7.5 g	
	(IEC 60068-2-6)	
Shock	2 x 1 m & 100 x 0.5 m	
	(IEC 60068-2-32)	




# Specifications (cont.)

Rated insulation voltage	250 VAC (rms)	Cable gland	Nickel-plated brass
Housing material		Weight	130 g
Body	PC/ABS, grey reinforced Red PMMA Steel, galvanized	Approvals	UL, CSA
Front glass Mounting bracket		CE-marking	Yes
Connection			
Cable	Grey, 2 m, 4 x 0.25 mm <sup>2</sup>		


## **Operation Diagram**




#### **Dimensions**



## **Wiring Diagram**




## **Detection Diagram**




# CARLO GAVAZZI


## **Signal Stability**



#### **Excess Gain**




#### **Installation Hints**



## **Delivery Contents**

- Photoelectric switch: PC50CNP..
- Installation instruction
- Mounting bracket APC50-1
- Packaging: Cardboard box



#### **Accessories**

- Reflectors:
- Screwdriver for adjustment:

ER-series 77-001

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carlo Gavazzi: PC50CNP06RP