

RP1A..D10, RP1B..D10



1-phase PCB mount solid state relays



Main features

- AC Solid State Relay for PCB mounting
- Zero switching or instant-on
- Rated operational current: 10 AACrms (25 AACrms with forced air cooling)
- Rated operational voltage: Up to 480 VACrms
- Surface mount technology
- Control voltage: 4 to 32 VDC
- Opto-isolation: > 4000 VACrms
- Blocking voltage: Up to 1000 Vp
- Non-repetitive surge current: Up to 250 Ap

Description

The RP1..D10 is an SSR series for socket- or PCB-mounting, providing an ideal interface between logic controls and AC loads.

The RP1..D10 is designed for resistive and inductive loads up to 480VACrms.

The integral heatsink allows switching of a high current in this compact package. Opto-isolation and load switching are performed by individual components, providing higher reliability. This relay can also drive high AC53a loads up to 7 AACrms.

The Solid State technology used can withstand peak voltages of 1000V, making the RP1..D10 series suitable to drive AC loads such as loaded induction motors.

Applications

These relays can be used to switch heaters, motors, lights, valves or solenoids.

Main functions

- Zero cross or Instant on AC switching
- Ratings up to 480 VACrms, 10 AACrms (25 AACrms with forced air cooling)
- 4-32 VDC control voltage (3-32 VDC for RP1.23D10)

References

Order code



RP1 D10

Enter the code entering the corresponding option instead of

Code	Option	Description	Notes
R	-	Solid State Relay (PCB)	
P	-		
1	-	Number of poles	
<input type="checkbox"/>	A	Switching mode: zero switching	
	B	Switching mode: instant-On switching	
<input type="checkbox"/>	23	Rated operational voltage: 230 VACrms	
	40	Rated operational voltage: 400 VACrms	
	48	Rated operational voltage: 480 VACrms	
D	-	Control voltage: 4 to 32 VDC	3 to 32 VDC for RP1.23D10
10	-	Rated operational current: 10AACrms	

Selection guide

Rated operational voltage	Blocking voltage	Control voltage	Rated operational current 10 AACrms
230 VACrms	650 Vp	3 to 32 VDC	RP1A23D10
400 VACrms	850 Vp	4 to 32 VDC	RP1A40D10
480 VACrms	1000 Vp	4 to 32 VDC	RP1A48D10

CARLO GAVAZZI compatible components


Purpose	Component name/code	Notes
DIN adaptors	RPM2	DIN adaptor 600V with LED Note that when the RP..10 is mounted on DIN rail (vertical mounting), a derating factor has to be applied.

Features

General

Material	Black Epoxy coating
Weight	Approx. 40 g
Isolation: input to output	4 kVACrms

Dimensions



M = 2.54 mm = 1/10 "

Performance

Mains supply

	RP1.23D10	RP1.40D10	RP1.48D10
Operational voltage range RP1A RP1B	12 - 265 VACrms 12 - 265 VACrms	20 - 440 VACrms 12 - 440 VACrms	20 - 530 VACrms 12 - 530 VACrms
Operational frequency range	45 - 65 Hz		
Blocking voltage	< 650 Vp	< 850 Vp	< 1000 Vp
Zero voltage turn-on	< 10 VACrms		

Outputs

Rated operational current AC 51 @ $T_a = 25^\circ\text{C}$ AC 53a @ $T_a = 25^\circ\text{C}$	10 AACrms 7 AACrms
Min. operational load current	10 mAACrms
Power factor	> 0.5
Rep. overload current $t=1$ s	16 AACrms
Non-rep. surge current $t=20$ ms	250 Ap
Off-state leakage current @ rated voltage and frequency	< 3 mAACrms
I^2t for fusing $t=10$ ms	340 A ² s
Critical dV/dt off state min.	1000 V/ μ s
On-state voltage drop @ rated current	< 1.5 VACrms

Inputs

Control voltage RP1.23D10 RP1.40D10, RP1.48D10	3-32 VDC 4-32 VDC
Pick-up voltage RP1.23D10 RP1.40D10, RP1.48D10	2.8 VDC 3.8 VDC
Drop-out voltage	1.2 VDC
Max. input current RP1A..D10 RP1B..D10	10 mA 17 mA
Max. reverse voltage	32 VDC
Response time pick-up RP1A..D10 RP1A..D10 @ V_{in} 5VDC	$\leq 1/2$ cycle $\leq 200 \mu$ s
Response time drop-out RP1B..D10 RP1B..D10 @ V_{in} 5VDC	$\leq 1/2$ cycle $\leq 1/2$ cycle

Derating curve




Fig. 1 Convection cooling




Fig. 2 Forced air cooling at 15m³/h



Derating curve is used for finding max. load current at an elevated ambient temperature.

Note: the above indicated current ratings apply only for the RP..10 mounted with fins in the vertical orientation to allow airflow through the heatsink fins. For other mounting orientations please consult your Carlo Gavazzi Sales representative.

Thermal data

Operating temperature	-30° to +80°C (-22° to +176°F)
Storage temperature	-40° to +100°C (-40° to +212°F)

Compatibility and conformity

Standards compliance	LVD: EN 60947-4-3 EMCD: EN 61000-6-2, EN 61000-6-4 UL508 C22.2 No. 14-13
Approvals	CE  




Electromagnetic compatibility (EMC) - immunity	
Electrostatic discharge (ESD)	EN/IEC 61000-4-2 8 kV air discharge, 4 kV contact (PC1)
Radiated radio frequency	EN/IEC 61000-4-3 10 V/m, from 80 MHz to 1 GHz (PC1) 10 V/m, from 1.4 to 2 GHz (PC1) 10 V/m, from 2 to 2.7 GHz (PC1)
Electrical fast transient (burst)	EN/IEC 61000-4-4 Output: 2 kV, 5 kHz (PC2) Input: 1 kV, 5 kHz (PC2)
Conducted radio frequency	EN/IEC 61000-4-6 10V/m, from 0.15 to 80 MHz (PC1)
Electrical surge	EN/IEC 61000-4-5 Output, line to line: 1 kV (PC2) Output, line to earth: 1 kV (PC2) ¹ Input, line to line: 500 V (PC2) ² Input, line to earth: 500 V (PC2) ²
Voltage dips	EN/IEC 61000-4-11 0% for 0.5, 1 cycle (PC2) 40% for 10 cycles (PC2) 70% for 25 cycles (PC2)
Voltage Interruptions	EN/IEC 61000-4-11 0% for 5000ms (PC2)
Electromagnetic compatibility (EMC) - emissions	
Radio interference field emission (radiated)	EN/IEC 55011 Class A: from 30 to 1000 MHz
Radio interference voltage emissions (conducted)	From 0.15 to 30 MHz EN/IEC 55011 Class A (industrial) with filter capacitor across the Mains supply EN/IEC 60947-4-3 Class A (no filtering needed)

Note:

- Performance Criteria 1 (PC1): no degradation of performance or loss of function is allowed when the product is operated as intended.
- Performance Criteria 2 (PC2): during the test, degradation of performance or partial loss of function is allowed. However when the test is complete the product should return operating as intended by itself.
- Performance Criteria 3 (PC3): temporary loss of function is allowed, provided the function can be restored by manual operation of the controls.
- Control input lines must be installed together to maintain products' susceptibility to Radio Frequency interference.
- ¹ A suppression device, such as a varistor, needs to be connected across the output terminals L1, T1 for immunity against higher voltage levels.
- ² A suppression device, such as a transil, needs to be connected across the control terminals A1, A2 for immunity against higher voltage levels.


Functional diagram



* The varistor is not included in the solid state relay. Connecting a varistor across terminals 1-2 helps protect the solid state relay against damages by over-voltage

Connection specifications

Terminals	Copper alloy, tin-plated
Terminals soldering temperature	max. 300°C for 5 seconds



COPYRIGHT ©2017
Content subject to change. Download the PDF: www.productselection.net

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[RP1A23D10](#) [RP1A48D10](#) [RP1A40D10](#) [RP1B23D10](#) [RP1A23A6](#) [RP1B40D10](#)