




Overview

PV monitoring

PV monitoring diagram

SOFTWARE Eos-Server - PV multisites management



Overview

PV monitoring

Web server and datalogger



VMU-C PV (Eos-Web)

- Dimensions: 2 DIN modules
- Micro PC with web server and web service capability
- Data and event logging capability
- Internal 4GB memory and 16GB SDHC card back-up memory (on request)
- Variables shown as graphs and numbers in formatted tables
- All data exports on HTML format compatible with Excel or other spread sheets
- Management up to 11 Eos-Array, 11 inverters and 11 energy meters

MAIN FEATURES

- Efficiency calculation and control on different levels: string, BOS and Performance ratio and Yield indices
- Alarms control with automatic e-mailing and SMS management by means of VMU-D

Embedded aggregation server



VMU-Y PV

- 2-DIN size; DIN-rail mounting
- Multi-site PV monitoring management
- Power supply from 24 VDC (+/- 20%)
- 2 USB ports (for data backup and connection backup)
- 1 SD port (for backup)
- UL approved

MAIN FEATURES

- Photovoltaic plant/portfolio management
- Data analysis and benchmark
- Data and event logging
- Data aggregation in plants and virtual plants
- All data exported in format compatible with Excel or other spread sheets
- Alarms management
- Database replication up to 10 VMU-C PV

Cloud multi-site aggregation server



Eos-Server

- Software solution for photovoltaic plant management
- Multi-site PV monitoring management
- Flexible and scalable architecture
- VMware® Technology compatibility - inhouse or cloud installation

MAIN FEATURES

- Photovoltaic plant/portfolio management
- Data analysis and benchmark
- Data and event logging
- Data aggregation in plants and virtual plants
- All data exported in format compatible with Excel or other spread sheets
- Alarms management
- Database replication up to 100 VMU-C PV

Solar monitoring solution



Eos-Array / Eos-Array Lite

- Modular local monitoring system for PV plant
- Up to 16 DIN module configuration
- Eos-ArraySoft, freeware configuration software
- Eos-Array can manage in addition to VMU-M unit up to: 1 VMU-P, up to 15 VMU-S and up to 7 VMU-O for a total of maximum 15 units

MAIN FEATURES

- The Eos-Array solution can be composed of: VMU-M, the master unit and data logger; VMU-S, the string controller; VMU-P, the environment variable unit and VMU-O, the I/O unit
- Eos-Array Lite is the answer to those photovoltaic applications where a less sophisticated monitoring solution is needed

USB dongle connection modules



VMU-D

- Dimensions: 2 DIN modules
- Compatible with Carlo Gavazzi approved 3G/4G USB modems
- Power supply 24 VDC (+/- 20%)
- Suitable for use with VMU-C and VMU-Y

MAIN FEATURES

- 3G or 4G Mobile Internet connectivity
- SMS alerting
- SMS commands

PV monitoring

Surge arresters



DSB / DSF

- Dimensions: 90 x 36 x 72 mm
- Class II
- Available for PV and AC installations
- Models for communication lines
- Optional remote monitoring
- For DIN rail mounting

MAIN FEATURES

- NO backup fuse required
- Appr. Acc. to IEC61643-11 and UTE C61-740-51
- Complies with prEN50539-11

Surge arresters



DSC

- Dimensions: 90 x 72 x 70 mm
- Class I and II
- Protective element: High Energy MOV
- High surge discharge rating: $I_{imp} = 12.5$ kA per pole
- Housing: compact design

MAIN FEATURES

- Specifically designed for PV installations with or without LPS (Lightning Protection System)
- Location of use: photovoltaic system - PV module side

Surge arresters



DSB51XXDP

- Dimensions: 90 x 12 x 71.5 mm DIN-rail housing
- 15 VDC nominal voltage
- 10 kA I_{nom} , 20 kA I_{max}
- Rated spark overvoltage 184V to 276V
- C1/C2/C3 according to IEC 61643-21

MAIN FEATURES

- Designed for Dupline® communication lines
- Three stage topology with dual GDT
- Socket with replaceable cartridge

Switching power supply



SPM3

- DIN rail housing
- Universal input 90-264 VAC / 120-370 VDC
- Single phase and battery charger versions available
- Approvals/Marks: UL, cUL listed and TÜV/CE approved

MAIN FEATURES

- Operating temperature w/o derating -25°C to +60°C
- Short circuit and Overload protection
- High efficiency (up to 89%)

DIN rail DC/DC converter



DCC 24151K-D

- DIN rail mounting
- Ultra wide input: 100 ~ 1000 VDC
- 24VDC output 15W
- High efficiency up to 80%
- Wide temperature range -40 to +70° C
- Output over voltage and short circuit protection
- Reverse input protection

MAIN FEATURES

- Widely used in Photovoltaic power generation with high voltage inverters
- It provides stable operating voltage to low voltage DC equipment

3-phase energy analysers



EM24 DIN

- Dimensions: 4 DIN modules
- 3-phase energy analyser with direct connection
- Current input for direct connection up to 65A or external CT connection
- Class 1 (kWh) acc. to EN62053-1
- Pulse open collector output
- Modbus communication port

MAIN FEATURES

- Direct or external CT measurement in a very compact housing to save space
- Suitable for measuring generated and consumed energy
- MID Annex D certification available

PV monitoring

Irradiation sensors



PVS-1

- Dimensions: 57 x 48 x 15 mm (not including clamp)
- Sensor type: crystalline silicon cell
- No need for external power supply (self-powered)
- Long lasting 3% accuracy, thanks to a special antiageing treatment
- Calibration process according to IEC 60904-2 and 60904-4
- Two available versions: 4-20 mA output / 0-80 mV output

MAIN FEATURES

- Long life rugged aluminium case
- UV resistant resin encapsulation
- Fast installation, thanks to the clamping system designed to easily fit the photovoltaic module's frame

Pyranometers



PVS-2A

- Dimensions: 162 x 215 x 40 mm (not including clamp)
- 2nd class thermopile pyranometer
- 4-20 mA output for reliable connections
- Calibration certificate according to ISO 9847

MAIN FEATURES

- Compact and rugged IP67 aluminium case
- Compliant with WMO (World Meteorological Organization) for environmental monitoring
- Compliant with ISO9060 and IEC17025 for photovoltaic monitoring

Temperature sensors



TEMPSOL / IKE20001K

- Temperature Pt100 or Pt1000 (TEMPSOL)
- Temperature Pt1000 (IKE20001K)
- $\pm 0.3^{\circ}\text{C}$ connection type
- 2 wire connection type

MAIN FEATURES

- Specifically design to measure the temperature of PV panels (TEMPSOL)
- For air temperature measurement in PV plants (IKE20001K)

Anemometers



DWS-V

- Opto-electronic detection
- Rotor diameter: 145 mm
- Rotor: black painted stainless steel
- PNP & NPN open collector output in one unit
- Measuring range 2 to 30 m/s
- Current source output 10 to 28 VDC supply

MAIN FEATURES

- All inputs and outputs are protected against reverse polarity and transients
- Dust sealed stainless steel ball bearing

OUR SALES NETWORK IN EUROPE

AUSTRIA

Carlo Gavazzi GmbH
Ketzergergasse 374,
A-1230 Wien
Tel: +43 1 888 4112
Fax: +43 1 889 10 53
office@carlogavazzi.at

BELGIUM

Carlo Gavazzi NV/SA
Mechelsesteenweg 311,
B-1800 Vilvoorde
Tel: +32 2 257 4120
Fax: +32 2 257 41 25
sales@carlogavazzi.be

DENMARK

Carlo Gavazzi Handel A/S
Over Hadstenvej 40,
DK-8370 Hadsten
Tel: +45 89 60 6100
Fax: +45 86 98 15 30
handel@gavazzi.dk

FINLAND

Carlo Gavazzi OY AB
Petaksentie 2-4,
FI-00630 Helsinki
Tel: +358 9 756 2000
Fax: +358 9 756 20010
myynti@gavazzi.fi

FRANCE

Carlo Gavazzi Sarl
Zac de Paris Nord II, 69, rue de la Belle Etoile,
F-95956 Roissy CDG Cedex
Tel: +33 1 49 38 98 60
Fax: +33 1 48 63 27 43
french.team@carlogavazzi.fr

GERMANY

Carlo Gavazzi GmbH
Pfnorstr. 10-14
D-64293 Darmstadt
Tel: +49 6151 81000
Fax: +49 6151 81 00 40
info@gavazzi.de

GREAT BRITAIN

Carlo Gavazzi UK Ltd
4.4 Frimley Business Park,
Frimley, Camberley, Surrey GU16 7SG
Tel: +44 1 276 854 110
Fax: +44 1 276 682 140
sales@carlogavazzi.co.uk

ITALY

Carlo Gavazzi SpA
Via Milano 13,
I-20020 Lainate
Tel: +39 02 931 761
Fax: +39 02 931 763 01
info@gavazziacbu.it

NETHERLANDS

Carlo Gavazzi BV
Wijkermeerweg 23,
NL-1948 NT Beverwijk
Tel: +31 251 22 9345
Fax: +31 251 22 60 55
info@carlogavazzi.nl

NORWAY

Carlo Gavazzi AS
Melkeveien 13,
N-3919 Porsgrunn
Tel: +47 35 93 0800
Fax: +47 35 93 08 01
post@gavazzi.no

PORTUGAL

Carlo Gavazzi Lda
Rua dos Jerónimos 38-B,
P-1400-212 Lisboa
Tel: +351 21 361 7060
Fax: +351 21 362 13 73
carlogavazzi@carlogavazzi.pt

SPAIN

Carlo Gavazzi SA
Avda. Iparraguirre, 80-82,
E-48940 Leioa (Bizkaia)
Tel: +34 94 480 4037
Fax: +34 94 431 6081
gavazzi@gavazzi.es

SWEDEN

Carlo Gavazzi AB
V:a Kyrkogatan 1,
S-652 24 Karlstad
Tel: +46 54 85 1125
Fax: +46 54 85 11 77
info@carlogavazzi.se

SWITZERLAND

Carlo Gavazzi AG
Verkauf Schweiz/Vente Suisse
Sumpfstrasse 3,
CH-6312 Steinhausen
Tel: +41 41 747 4535
Fax: +41 41 740 45 40
info@carlogavazzi.ch

OUR SALES NETWORK IN THE AMERICAS

USA

Carlo Gavazzi Inc.
750 Hastings Lane,
Buffalo Grove, IL 60089, USA
Tel: +1 847 465 6100
Fax: +1 847 465 7373
sales@carlogavazzi.com

CANADA

Carlo Gavazzi Inc.
2660 Meadowvale Boulevard,
Mississauga, ON L5N 6M6, Canada
Tel: +1 905 542 0979
Fax: +1 905 542 22 48
gavazzi@carlogavazzi.com

MEXICO

Carlo Gavazzi Mexico S.A. de C.V.
Calle La Montaña no. 28, Fracc. Los Pastores
Naucalpan de Juárez, EDOMEX CP 53340
Tel & Fax: +52.55.5373.7042
mexicosales@carlogavazzi.com

BRAZIL

Carlo Gavazzi Automação Ltda. Av.
Francisco Matarazzo, 1752
Conj 2108 - Barra Funda - São Paulo/SP
Tel: +55 11 3052 0832
Fax: +55 11 3057 1753
info@carlogavazzi.com.br

OUR SALES NETWORK IN ASIA AND PACIFIC

SINGAPORE

Carlo Gavazzi Automation Singapore Pte. Ltd.
61 Tai Seng Avenue
#05-06 UE Print Media Hub
Singapore 534167
Tel: +65 67 466 990
Fax: +65 67 461 980
info@carlogavazzi.com.sg

MALAYSIA

Carlo Gavazzi Automation (M) SDN. BHD.
D12-06-G, Block D12,
Pusat Perdagangan Dana 1,
Jalan PJU 1A/46, 47301 Petaling Jaya,
Selangor, Malaysia.
Tel: +60 3 7842 7299
Fax: +60 3 7842 7399
sales@gavazzi-asia.com

CHINA

Carlo Gavazzi Automation
(China) Co. Ltd.
Unit 2308, 23/F.,
News Building, Block 1, 1002
Middle Shennan Zhong Road,
Shenzhen, China
Tel: +86 755 83699500
Fax: +86 755 83699300
sales@carlogavazzi.cn

HONG KONG

Carlo Gavazzi Automation
Hong Kong Ltd.
Unit 3 12/F Crown Industrial Bldg.,
106 How Ming St., Kwun Tong,
Kowloon, Hong Kong
Tel: +852 23041228
Fax: +852 23443689

OUR COMPETENCE CENTRES AND PRODUCTION SITES

DENMARK

Carlo Gavazzi Industri A/S
Hadsten

MALTA

Carlo Gavazzi Ltd
Zejtun

ITALY

Carlo Gavazzi Controls SpA
Belluno

LITHUANIA

Uab Carlo Gavazzi Industri Kaunas
Kaunas

CHINA

Carlo Gavazzi Automation (Kunshan) Co., Ltd.
Kunshan

HEADQUARTERS

Carlo Gavazzi Automation SpA
Via Milano, 13
I-20020 - Lainate (MI) - ITALY
Tel: +39 02 931 761
info@gavazziautomation.com



CARLO GAVAZZI
Automation Components

Energy to Components!

www.gavazziautomation.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[IKE20001K](#)