

THREE PHASE DIODE+THYRISTOR

DFA50BA80/160



SanRex Power Module, DFA50BA, is complex isolated module which is designed for rash current circuit.

It contains six diodes connected in a three phase bridge configuration, and a thyristor connected to a direct current line.

- This Module is designed very compactly. Because diode module and thyristor put together.
- This Module is also isolated type between electorode terminal and mounting base. So you can put this Module and other one together in a same fin.

(Application)

- Inverter for AC or DC motor control, Current stabilized power supply, Switching power supply.



● DIODE

■ Maximum Ratings

(T_j=25°C unless otherwise specified)

Symbol	Item	Ratings		Unit
		DFA50BA80	DFA50BA160	
V _{RRM}	Repetitive Peak Reverse Voltage	800	1600	V
V _{RSM}	Non-Repetitive Peak Reverse Voltage	960	1700	V

Symbol	Item		Conditions	Ratings	Unit
I _D	Output Current (D.C.)		Three phase full wave, T _c =117°C	50	A
I _{FSM}	Surge forward current		1cycle, 50/60Hz, peak value, non-repetitive	730/800	A
T _j	Operating Junction Temperature			-40 to +150	°C
T _{stg}	Storage Temperature			-40 to +125	°C
V _{ISO}	Isolation Breakdown Voltage (R.M.S.)		A.C. 1minute	2500	V
	Mounting Torque	Mounting (M5)	Recommended Value 1.5-2.5 (15-25)	2.7 (28)	N·m
		Terminal (M5)	Recommended Value 1.5-2.5 (15-25)	2.7 (28)	(kgf·cm)
	Mass		Typical Value	150	g

■ Electrical Characteristics

Symbol	Item	Conditions	Ratings	Unit
I _{RRM}	Repetitive Peak Reverse Current,max.	T _j =150°C, V _R =V _{RRM}	8	mA
V _{FM}	Forward Voltage Drop,max.	T _j =25°C, I _F =50A Inst. measurement	1.30	V
R _{th(j-c)}	Thermal Impedance, max.	Junction to Case (TOTAL)	0.25	°C/W
R _{th(c-f)}	Thermal Impedance, max.	Case to Fin	0.10	°C/W

● THYRISTOR

■ Maximum Ratings



(T_j=25°C unless otherwise specified)

Symbol	Item	Ratings		Unit
		DFA50BA80	DFA50BA160	
V _{RRM}	Repetitive Peak Reverse Voltage	800	1600	V
V _{RSM}	Non-Repetitive Peak Reverse Voltage	960	1700	V
V _{DRM}	Repetitive Peak off-State Voltage	800	1600	V


Symbol	Item		Conditions	Ratings	Unit
I _{T(AV)}	Average On-State Current		Singl phase half wave. 180° conduction, T _c =85°C	50	A
I _{TSM}	Surge On-State Current		1 cycle, 50/60Hz, peak value, non-repetitive	730/800	A
I ² t	I ² t			2660	A ² S
di/dt	Critical Rate of Rise of On-State Current		I _G =100mA, V _D =½V _{DRM} , di _G /dt=0.1A/μs	150	A/μs
V _{ISO}	Isolation Breakdown Voltage (R.M.S.)		A.C. 1minute	2500	V
T _j	Operating Junction Temperature			-40 to +135	°C
T _{stg}	Storage Temperature			-40 to +125	°C
	Mounting Torque	Mounting (M5)	Recommended Value 1.5-2.5 (15-25)	2.7 (28)	N·m (kgf·cm)
		Terminal (M5)	Recommended Value 1.5-2.5 (15-25)	2.7 (28)	
	Mass		Typical Value	150	g

■ Electrical Characteristics


Symbol	Item	Conditions	Ratings	Unit
I _{DRM}	Repetitive Peak Off-State Current,max.	T _j =135°C, V _D =V _{DRM}	50	mA
I _{RRM}	Repetitive Peak Reverse Current,max.	T _j =135°C, V _D =V _{RRM}	50	mA
V _{TM}	Peak On-State Voltage,max.	T _j =25°C, I _{TM} =50A, Inst. measurement	1.25	V
I _{GT}	Gate Trigger Current,max.	V _D =6V, I _T =1A	70	mA
V _{GT}	Gate Trigger Voltage,max.	V _D =6V, I _T =1A	3	V
dv/dt	Critical Rate of Rise of Off-State Voltage,min.	T _j =125°C, V _D =⅔V _{DRM}	500	V/μs
R _{th(j-c)}	Thermal Impedance, max.	Junction to Case	0.80	°C/W
R _{th(c-f)}	Thermal Impedance, max.	Case to Fin	0.10	°C/W




DIODE Output Current vs. Allowable case Temperature




Surge Forward Current Rating (Non-Repetitive)




DIODE Transient Thermal Impedance




Gate Characteristics




SCR Maximum Forward Characteristics




SCR Output Current vs. Power Dissipation



SCR Output Current vs. Maximum Allowable case Temperature



SCR Transient Thermal Impedance



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SanRex:

[DFA50BA160](#) [DFA50BA80](#)