

DELPHI


TEMPERATURE SENSOR PRODUCT DATA

COOLANT TEMPERATURE SENSOR

PART NUMBER 15425529

FEATURES:

- Design for Manufacturability
- Cost Effective
- Robust Design
- Few Components
- Few Assembly Processes
- Thermistor Technology
- 100% Calibration Certified




THERMAL & ELECTRICAL PROPERTIES

Typical Voltage Supply: **5V DC**
Operating Temperature: **-40 C to 185 C**
Resistive Range (Ohms): **See Table**
Dissipation Constant: *
Thermal Time Constant: ** **< 10 seconds**
Accuracy: **See Table**


MECHANICAL PROPERTIES

Sensor Body Material: **Brass**
Connector: **PBT 30% GF**
O-Ring: **Flouorocarbon**
Hex Size: **5/8"**
Thread Size: **M10 x 1.5**
Mating Connector & Seal: **1-967644-1 AMP**
Installation Torque: **10-14 N-m**
Overall Weight: **16.3 grams**

THERMAL TIME CONSTANT



CIRCUIT SCHEMATIC



* The ratio, at a specified ambient temperature, of the change in the power dissipation of the sensor to the resultant temperature change of the thermistor. Test medium: silicone oil

** The time required for the sensor to achieve 63.2% of its steady state value when subjected to a step change in ambient temperature $T_c = (T_f - T_i) * 63.2\% + T_i$. Test medium: silicone oil.


Part Revision Level: **002**
Data Sheet Revision Date: **4/22/2004**

DELPHI


TEMPERATURE SENSOR PRODUCT DATA

PART NUMBER 15425529

UNLOADED RESISTANCE vs TEMPERATURE
CHARACTERISTIC CHART



TEMPERATURE ACCURACY CHART



Note: Temperature Sensor Calibration Resistance Guaranteed by 100% Automated Calibration Certification.

Temp (°C)	Res (Ohms)	Res (±%)	Ref Acc (±°C)	Temp (°C)	Res (Ohms)	Res (±%)	Ref Acc (±°C)	Temp (°C)	Res (Ohms)	Res (±%)	Ref Acc (±°C)
-40	332776	6.63	1.00	25	10000	4.38	1.00	90	916.4	3.09	1.00
-35	240264	6.40	1.00	30	8060	4.25	1.00	95	786.9	3.01	1.00
-30	175427	6.18	1.00	35	6536	4.13	1.00	100	678.1	2.94	1.00
-25	129449	5.98	1.00	40	5331	4.02	1.00	105	586.5	2.87	1.00
-20	96481	5.78	1.00	45	4373	3.91	1.00	110	509.1	2.80	1.00
-15	72592	5.60	1.00	50	3606	3.81	1.00	115	443.3	2.73	1.00
-10	55109	5.43	1.00	55	2989	3.70	1.00	120	387.3	2.67	1.00
-5	42193	5.26	1.00	60	2490	3.60	1.00	125	339.5	2.61	1.00
0	32566	5.10	1.00	65	2085	3.51	1.00	130	298.4	2.55	1.00
5	25338	4.94	1.00	70	1754	3.42	1.00	135	263.1	2.49	1.00
10	19869	4.79	1.00	75	1482	3.33	1.00	140	232.6	2.44	1.00
15	15695	4.65	1.00	80	1257	3.24	1.00	145	206.1	2.39	1.00
20	12486	4.51	1.00	85	1071	3.16	1.00	150	183.2	2.33	1.00

Important: The values above are for the unloaded thermistor, as shipped from Delphi Packard Electric, and does not reflect the effects of application system errors and aging.

Notes: Please contact Delphi Packard Engineering for the resistance vs temperature curve for your temperature sensor application. Due to self-heating effects of the thermistor, the resistance is dependant upon the application.

Since thermistors are "continuous function devices", resistance vs temperature data is available for numbers beyond those specified above.

For more information contact:

Delphi Packard Electric Systems
Sensor Business Segment M/S 93B
North River Road
Warren, OH 44483

Phone: (330) 373-3689

Fax: (330) 373-4147

Temperature (°C)	Resistance (Ohms)	Resistance (±%)	Temperature Accuracy	
			(+°C)	(-°C)
-40	332,776	6.63	1.0	-1.0
-35	240,264	6.40	1.0	-1.0
-30	175,427	6.18	1.0	-1.0
-25	129,449	5.98	1.0	-1.0
-20	96,481	5.78	1.0	-1.0
-15	72,592	5.60	1.0	-1.0
-10	55,109	5.43	1.0	-1.0
-5	42,193	5.26	1.0	-1.0
0	32,566	5.10	1.0	-1.0
5	25,338	4.94	1.0	-1.0
10	19,869	4.79	1.0	-1.0
15	15,695	4.65	1.0	-1.0
20	12,486	4.51	1.0	-1.0
25	10,000	4.38	1.0	-1.0
30	8,060	4.25	1.0	-1.0
35	6,536	4.13	1.0	-1.0
40	5,331	4.02	1.0	-1.0
45	4,373	3.91	1.0	-1.0
50	3,606	3.81	1.0	-1.0
55	2,989	3.70	1.0	-1.0
60	2,490	3.60	1.0	-1.0
65	2,085	3.51	1.0	-1.0
70	1,754	3.42	1.0	-1.0
75	1,482	3.33	1.0	-1.0
80	1,257	3.24	1.0	-1.0
85	1,071	3.16	1.0	-1.0
90	916.4	3.09	1.0	-1.0
95	786.9	3.01	1.0	-1.0
100	678.1	2.94	1.0	-1.0
105	586.5	2.87	1.0	-1.0
110	509.1	2.80	1.0	-1.0
115	443.3	2.73	1.0	-1.0
120	387.3	2.67	1.0	-1.0
125	339.5	2.61	1.0	-1.0
130	298.4	2.55	1.0	-1.0
135	263.1	2.49	1.0	-1.0
140	232.6	2.44	1.0	-1.0
145	206.1	2.39	1.0	-1.0
150	183.2	2.33	1.0	-1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15425529](#)