












COMPONENT FOR STRAP MOUNTING

REMARK:
- MAX STRAP WIDTH 4.8MM

COMPONENT FOR STRAP MOUNTING




POSITION	1								2		3
NAME	HOUSING STRAP MOUNT								SECONDARY LOCK		SL SEAL
MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN
PART-NO.:	33308619	33308620	33308622	33308625	33346509	33347328	33347332	33347335	33308630	33346468	33283927
AL / SHT	-	---	---	---	---	---	---	---	---	---	---
	1	---	---	---	---	---	---	---	1	---	1
TS / 6	-	---	1	---	---	---	---	---	1	---	1
	-	---	---	1	---	---	---	---	1	---	1
	-	---	---	1	---	---	---	---	1	---	1
	-	---	---	---	1	---	---	---	---	1	1
LS / 1	-	---	---	---	---	1	---	---	---	1	1
	-	---	---	---	---	---	1	---	---	1	1
	-	---	---	---	---	---	---	1	---	1	1

ASSEMBLY-NO.	PART-REV	CODING	MATERIAL WEIGHT
33308978	01	CODE A	ALL PARTS NVO / 16,6
33308979	01	CODE B	
33308980	01	CODE C	
33308981	01	CODE D	
33346866	01	CODE A	ALL PARTS NVO / 16,1
33347795	01	CODE B	
33347798	01	CODE C	
33347799	01	CODE D	

DWG STATUS						ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG							
250C18	R	01					INITIAL RELEASE		P.NAJ	M.ZYR	M.GRU
29MR19	R	01	AA			B7 A7	REFERENCE HELLERMANN TYTON DWG-NO., ADDED CLIP REFERENCE CHANGED		K.FAR	M.GRU	K.PIT
150C19	R	01	AB			B7 610	PROTECTION CAP ACTIV DWG-NO.: 35391874 NAS 35274875 PART AVAILABILITY FOR PART NUMBERS 33346866, 33347795, 33347798, 33347799 UPDATED		P.NAJ	M.GRU	M.SKR
280C20	R	01	AC			B7	HT DWG-NO: 18-0195-001-CSG WAS 17-0195-001-CSG		P.NAJ	M.GRU	

SCALE:
1 : 1



• **A P T I V** •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POUFNE
 INFORMACJE. POWIĘLNIENIE, ROZPOWSZECZANIE I WYKORZYSTYWANIE TEGO
 DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE
 INNYM JAKIEKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAZNYCH
 UPRAWNIENI, JEST ZABRONIONE

	DATE
DR P. NAJDUCH	240C18
APVD1 M. ZYROMSKI	250C18
APVD2 M. GRUDZEWSKI	260C18
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIE PRZETWORZONE OKREŚLA
APTIV 10949001

SEE CHART

4 WAY 2.8
CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER							
35096188							
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P	
A1	2:1	1 OF 1	1 OF 1	R	01	AC	

DWG TYP PART DRAWING		DISTR CODE D
WEIGHT (GR) SEE CHART		
VOLUME (CM ³) ---		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE
PRESENT INDICATE THAT PHYSICAL PARTS
ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE
AVAILABILITY OF PARTS.

[illegible]

R 0.2 MAX

1000000

SHARP CORNER TOLER.

> 70	> 100	> 150	> 200	>
------	-------	-------	-------	---

100	150	200	250
LESS OTHERWISE SPECIFIED			

±0.4	±0.5	±0.6	±0.8
------	------	------	------

ANGULAR TOLERANCE $\pm 2^\circ$

☐ DIM TO CHECK ☐ DIM FOR HELP ☐ THEORETIC DIM	DIMENSIONAL RANGE (MM)				SHARP CORNER TOLERANCE						CHART E
	FROM TO	> 0 20	> 20 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400		
	TOLERANCE UNLESS OTHERWISE SPECIFIED										
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
	ANGULAR TOLERANCE ±2°										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33308980](#)