






SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	12
	LAST NO. USED	10

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APPROV	APPROV 2
DATE	STG	N/P	CHG						
23MY02	R	10	-	-	ALL PARTS - CLEARED REV COLUMN & REVISED MATERIAL SPECS: 12048074 - UPDATED PDM ATTRIBUTES	222820	HAM	HAM	DLB
22AU02	R	11	-	-	15366078, 15326396, 15326225, 12160223, 12160222, 12084200 & 12048074 - REVISED MAT'L SIZE AND MAT'L SPEC	211578	ESF	EAR	CMC
06FE03	R	12	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	236349	MAC	MAC	JMP
14OC03	R	13	-	-	15366078 - MAT'L SPEC WAS M3620 HCN4	245588	AKD	TLB	B6
17FE04	-	14	-	-	12048074, 12084200, 12092702, 12160222, 12160223, 15326225, 15326396 & 15366078 - T.O.D. UPDATED	250621	JS	JS	B6
19OC04	R	15	-	-	ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE	260108	RTV	JAA	NKM
09MR06	R	16	-	-	12084200 & 15326396 - UPDATED PDM ATTRIBUTES	276509	JBD	AJO	JES
24MY06	R	17	-	-	12092702 - OBSOLETE	280889	GLS	JAA	BDG
16JN06	R	18	-	-	ALL ACTIVE PARTS - PSD WAS #4	281799	JTZ	JJM	BDG
27JL02	R	19	-	-	12160222-23 - UPDATED MATERIAL CALLOUT AND ADDED TYPE 203	418959	AJP	AJP	MAA
02JA13	R	20	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	420897	IMF	JAA	MAA
24JA13	R	21	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	421210	AGC	JAA	MAA
19FE15	R	22	-	-	12160222-23 - ADDED TARNISH NOTE	428876	JVR	JVM	JSM
15OC18	R	23	-	-	ALL ACTIVE PARTS - ADDED "SEALED" COLUMN ON CHART	441102	GCO	GCO	LES
25FE20	R	24	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	551096	GJO	JAA	OMS



TYPE 202
SAME AS TYPE 10
EXCEPT AS SHOWN



TYPE 203
SAME AS TYPE 202
EXCEPT AS SHOWN

NOTES:

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. RECOMMENDED MATING BLADE - WIDTH : 1.64/1.4
THICKNESS : 0.86/0.79
LENGTH : 7.1/6.9
3. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES
NUMBER (P01, P02, P03, ETC.).
4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
5. FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER,
TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE
PERFORMANCE OF THE PART.

-	-	-	0.254 X 30.96	-	15366078	05	AC	0.254 X 29.8	AU PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	15326396	03	AD	0.254 X 29.8	AU PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	15326225	03	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	12160223	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	1-0.8	17	2.65-1.85	203	3	X
-	-	-	0.254 X 30.96	-	12160222	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	203	2.1	X
12092702	O3	AB	0.254 X 30.96	METAL COPPER ALLOY	12084200	06	AD	0.254 X 29.8	SN PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	12059611	C1	-	0.254 X 30.96	SN PLATED COPPER ALLOY	0.35	22	2.1-1.7	201	2.2	-
12092667	B1	-	0.254 X 30.96	METAL COPPER ALLOY	12048074	11	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM ²)	ID	DIA	TYPE	G	SEALED
			UNPLATED					UNPLATED				CABLE			

THIS LINE DRAWING THROUGH A PART NUMBER INDICATES THAT THE PART NUMBER IS NOT AVAILABLE FOR ORDERING.

CONNECTION SYSTEMS
WARREN, OH
COPYRIGHT 1996 APV INC. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APV INC. AND CONTAINS ACTIVE CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS REUSE FOR ANY DATA, AS WELL AS COMMUNICATION OF THIS INFORMATION TO ANY OTHER PARTY WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AND IS INDEXED BY THE U.S. GOVERNMENT/DEFENSE DRAWING AND MANUFACTURING ADOPTING - 1997. ALL GEOMETRIC TOLERANCES ARE UNLESS OTHERWISE SPECIFIED ON THE DRAWING. FORM A TOLERANCE DOES NOT IMPLY A RELATIONSHIP BETWEEN FEATURES ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALCULATIONS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

THIRD ANGLE
PROJECTION

DO NOT
SCALE

USE MATH
DATA

NX

DRAWING NAME

TAXI TERM F M/P I50 LOCKING LANCE

DRAWING NUMBER

12047884

SIZE	SCALE	FRAME	NO	SHEET	STG	REV	TVP
A0	1:1	1	OF 1	2	1	R	24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15326225](#)